

DESCRIPTION

4.3" round recessed fixed glass dome trim for showerlight applications. For use with 12V GY6.35 lamp 50W max.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A Trim

Fixed position showerlight trim. 4.3" o.d. trim face. Includes frosted glass dome for ambient illumination.

B Lamp

For use with 12V GY6.35 lamp 50W max. Lamp not included.

C Socket


GU5.3 bi-pin socket for 12V GY6.35. (Included with Microgem housing sold separately)

D Lens

Includes clear protective glass lens. Can hold up to 2 optical accessories total.

E Finish

MLV2033 Powder coated white trim with frosted dome glass lens.



**MICROGEM
RECESSED**

**MLV2033
4.3" O.D.
Round Die Cast
Showerlight Trim
w/ Dome Glass for
Wet Location**

FOR 12V GY6.35 50W max.

Compatible Housings:

C500 / C500-SH

C600 / C600-EL

C700

C800

C900

SH2A



ORDERING INFORMATION

MLV2033

Fixture
MLV2033

White Trim w/ Frosted Dome Glass Lens