

HALO

RL Recessed Baffle Canless Downlights 4-inch and 6-inch



NEW

FLIP-N-KLIP™
LOCKING SPRINGS



These canless LED downlights deliver fast, efficient installation without the need for a recessed housing, mounting directly into the ceiling for both remodel and new construction to save time and reduce labor costs; now featuring patented Flip-N-Klip™ Locking Springs, they lock upright during installation and removal to help prevent painful snap-back while improving control and safety; the low-profile design fits tight spaces without sacrificing performance, providing bright, crisp 90+ CRI light with field-selectable color temperature and Dim-to-Warm capability to fine-tune any environment; with long-life performance, flexible configuration, and installer-focused innovation, RL remains a reliable, cost-effective lighting solution.

Product Features

- Round 4" and 6" Baffle Trim with regressed lens
- **Flip-N-Klip Locking Springs prevent painful spring snap**
- No housing required - for remodel and new construction installations
- For new construction, use with canless mounting frames/plates (sold separately)
- Fixture and remote driver / junction box are suitable for IC (insulation contact) or non-IC applications
- Can be installed in 1/2" to 1-1/4" thick ceilings
- **Lens & Trim:** Recessed baffle trim and curved diffuse lens
- **Color Temperature (CCT):** 5-color Field-SeleCCTable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K); 90+ CRI
- **Selectable Lumen:** RL4 695/955 lm; RL6 750 lm (static); RL6 1050/1300 lm
- **Dimming:** Dims to 5% (phase cut LE/TE); 120V input
- AIR-TITE, wet location-listed, and ENERGY STAR®
- 50,000 hrs of maintenance-free operation in damp or wet locations
- 5-year warranty



LEARN MORE




SAFER & SIMPLER

Springs lock upright during installation and removal, automatically clamping securely to the ceiling.

NO PINCH. NO PATCH.

- Locks open for one-hand installs
- Releases in the ceiling to clamp tight
- Re-locks upright for clean removal—no drywall repair

FLIP-N-KLIP™ LOCKING SPRINGS



LEARN MORE
ABOUT
FLIP-N-KLIP™



ADJUSTABLE WHITE

2700K 3000K 3500K 4000K 5000K



DIM-TO-WARM

3000K - 1800K

Select the perfect color temperature for your space with 5 color temperatures between warm (2700K) to daylight (5000K) or a dim-to-warm setting.

SELECTABLE LUMENS

Choose between 2 lumen options depending on your ceiling height or desired light level.

Catalog Number	Description	Lumens (@3000K)	CRI/CCT	Driver	UPC
RL4LS9FSD2W1EWHDM	4-inch Round Canless LED Downlight	695/955 Selectable Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258901
RL6069FSD2W1EWHDM	6-inch Round Canless LED Downlight	750 Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258963
RL6LS9FSD2W1EWHDM	6-inch Round Canless LED Downlight	1050/1300 Selectable Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258987

Catalog Number	Accessories			
	Decorative Overlays	New Construction Mounting Frames	New Construction Smash Plate	Extension Cables
RL4LS9FSD2W1EWHDM	RL4TRMWHB Matte White, Baffle RL4TRMWBB Matte Black, Baffle RL4TRMSNB Satin Nickel, Baffle RL4TRMTBZB Tuscan Bronze, Baffle RL4TRMWH Matte White, Splay RL4TRMMB Matte Black, Splay RL4TRMSN Satin Nickel, Splay RL4TRMTBZ Tuscan Bronze, Splay	HL4RSMF 4" round and square mounting frame	SP346RS 3"/4"/6" Round/ Square Smash Plate	HLB06FSEC 6 ft. cable HLB12FSEC 12 ft. extension cable HLB20FSEC 20 ft. extension cable
RL6069FSD2W1EWHDM	N/A	HL6RSMF 6" round and square mounting frame		
RL6LS9FSD2W1EWHDM				

