HALO

RL Recessed Baffle Canless Downlights

4-inch and 6-inch





These canless LED downlights deliver fast, efficient installation without the need for a recessed housing, mounting directly into the ceiling for both remodel and new construction to save time and reduce labor costs; now featuring Flip-N-Klip™ Locking Springs, they lock upright during installation and removal to help prevent painful snap-back while improving control and safety; the low-profile design fits tight spaces without sacrificing performance, providing bright, crisp 90+ CRI light with field-selectable color temperature and Dim-to-Warm capability to fine-tune any environment; with long-life performance, flexible configuration, and installer-focused innovation, RL remains a reliable, cost-effective lighting solution.

Product Features

- Round 4" and 6" Baffle Trim with regressed lens
- **Flip-N-Klip Locking Springs prevent painful spring snap**
- No housing required - for remodel and new construction installations
- For new construction, use with canless mounting frames/plates (sold separately)
- Fixture and remote driver / junction box are suitable for IC (insulation contact) or non-IC applications
- Can be installed in 1/2" to 1-1/4" thick ceilings
- **Lens & Trim:** Recessed baffle trim and curved diffuse lens
- **Color Temperature (CCT):** 5-color Field-SeleCCTable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K); 90+ CRI
- **Selectable Lumen:** RL4 695/955 lm; RL6 750 lm (static); RL6 1050/1300 lm
- **Dimming:** Dims to 5% (phase cut LE/TE); 120V input
- AIR-TITE, wet location-listed, and ENERGY STAR®
- 50,000 hrs of maintenance-free operation in damp or wet locations
- 5-year warranty

LEARN MORE






SAFER & SIMPLER

Springs lock upright during installation and removal, automatically clamping securely to the ceiling.

NO PINCH. NO PATCH.

- Locks open for one-hand installs
- Releases in the ceiling to clamp tight
- Re-locks upright for clean removal—no drywall repair

FLIP-N-KLIP™ LOCKING SPRINGS



LEARN MORE ABOUT FLIP-N-KLIP™



ADJUSTABLE WHITE 2700K 3000K 3500K 4000K 5000K + DIM-TO-WARM 3000K - 1800K


Select the perfect color temperature for your space with 5 color temperatures between warm (2700K) to daylight (5000K) or a dim-to-warm setting.

SELECTABLE LUMENS

Choose between 2 lumen options depending on your ceiling height or desired light level.

Catalog Number	Description	Lumens (@3000K)	CRI/CCT	Driver	UPC
RL4LS9FSD2W1EWHDM	4-inch Round Canless LED Downlight	695/955 Selectable Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258901
RL6069FSD2W1EWHDM	6-inch Round Canless LED Downlight	750 Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258963
RL6LS9FSD2W1EWHDM	6-inch Round Canless LED Downlight	1050/1300 Selectable Lumens	90+ CRI, 6-Color Field-SeleCCTable: 2700K / 3000K / 3500K / 4000K / 5000K / Dim-to-Warm	5% Phase Cut LE/TE Dimming, 120V 60Hz	080083258987

Catalog Number	Accessories			
	Decorative Overlays	New Construction Mounting Frames	New Construction Smash Plate	Extension Cables
RL4LS9FSD2W1EWHDM	**RL4TRMWHB** Matte White, Baffle **RL4TRMWBB** Matte Black, Baffle **RL4TRMSNB** Satin Nickel, Baffle **RL4TRMTBZB** Tuscan Bronze, Baffle **RL4TRMWH** Matte White, Splay **RL4TRMMB** Matte Black, Splay **RL4TRMSN** Satin Nickel, Splay **RL4TRMTBZ** Tuscan Bronze, Splay	**HL4RSMF** 4" round and square mounting frame	**SP346RS** 3"/4"/6" Round/ Square Smash Plate	**HLB06FSEC** 6 ft. cable **HLB12FSEC** 12 ft. extension cable **HLB20FSEC** 20 ft. extension cable
RL6069FSD2W1EWHDM	N/A	**HL6RSMF** 6" round and square mounting frame		
RL6LS9FSD2W1EWHDM				



COOPER Lighting Solutions
a signify business

Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2026 Cooper Lighting Solutions
All Rights Reserved
Publication No. BR51816826
October 14, 2026 2:53 PM

Product availability, specifications, and compliances are subject to change without notice.