



Save Money



Save Time



Peace of Mind

The HALO FM is an Energy Star LED flushmount that comes with a field selectable CCT switch. The FM with selectable CCT provides light color options (from warm to bright white) to suit any decor and space. Typical surface mount applications include bedrooms, closets, corridors, stairways, and utility rooms.



8" Round LED Flushmount



11" Round LED Flushmount



15" Round LED Flushmount



8" only



11" & 15"





Features		Benefits	Result
Performance	8" - Field Selectable CCT (3000K, 4000K, 5000K) 11" & 15" - Field Selectable CCT (2700K, 3000K, 3500K, 4000K, 5000K)	Less inventory to stock	💰
		Customize color temperature to match any space	✓
		Simple and easy to order	🕒
	50K rated life-hours, up to 80 lm/W	Long life, no lamp changes needed	✓
		Energy savings up to 80% vs. incandescent or fluorescent	💰
	Energy Star certification	Eligible for energy rebates	💰
5-year warranty	Certified and guaranteed performance	✓	
Construction	J-Box mountable, hardware included	Easy and simple installation	🕒
	Opal white lens for 360-degrees of light	Even illumination and light for safety	✓

Round

Performance Data

(Performance is measured at 3000K CCT)

Catalog Number	Lumens	Watts	CRI
FM89S1EWHR	920	10.5	93
FM119S1EWHR	1250	14.5	93
FM159S1EWHR	1510	18	93

WARM
0-2900K

BRIGHT
WHITE
3000K-4900K

COOL
WHITE
5000K-ABOVE



Understanding Color Temperature

From crisp and invigorating to cozy and inviting, finding the right color temperature influences the look and feel of any room.



2700K • 3000K • 3500K
4000K • 5000K

