


Accessory Snoot



Description

White, Black and Aluminum Haze Snoot to be used as an accessory with the HALO 808 High Performance.

- 808MHS3P**=808 Media Snoot, 3" White
- 808MHS3MB**=808 Media Snoot, 3" Matte Black
- 808MHS3AH**=808 Media Snoot, 3" Aluminum Haze
- 808MHS4P**=808 Media Snoot, 4" White
- 808MHS4MB**=808 Media Snoot, 4" Matte Black
- 808MHS4AH**=808 Media Snoot, 4" Aluminum Haze

Lens Media



Description

The Diffuse soft focus lens provides an additional even beam spread. The Linear Spread Lens fans out the beam to produce a wide rectangular smooth pattern. The Prismatic Diffuse lens Broadens the beam to create a wide uniform distribution. The Hex Cell Louver controls the light beam and prevents unwanted spill light providing a 45 deg cut off.

- LND-DSL3** = Diffuse Soft Focus Lens 3"
- LND-LSL3** = Linear Spread Lens 3"
- LND-HCL3** = Hexcell Louver 3"
- LND-DSL4** = Diffuse Soft Focus Lens 4"
- LND-LSL4** = Linear Spread Lens 4"
- LND-HCL4** = Hexcell Louver 4"

Interchangeable Reflector Optics



Description

The interchangeable HALO 808 High Performance optic accessories can be used to achieve a Spot distribution for the 3000 lumen package and a flood and narrow flood beam for all lumen packages.

- 808OPK3FL** = 3" Flood Optic
- 808OPK3NF** = 3" Narrow Flood Optic
- 808OPK4FL** = 4" Flood Optic
- 808OPK4NF** = 4" Narrow Flood Optic
- 808OPK4SP** = 4" Spot Optic

Monopoint Canopy Adapter



Description

Mounts permanently to an outlet box.

L973-4 1/2" sq allows a lampholder to a 500W maximum to be converted to a canopy installation.

LZR209- 5" diameter, Mounts directly to junction box, 500W maximum.

- L973PN** = Halo PowerTrac square canopy adapter, matte white
- L973MB** = Halo PowerTrac square canopy adapter, matte black
- LZR209P** = LazerTrack round monopoint, matte white
- LZR209MB** = LazerTrack round monopoint, matte black