

HALO[®]

Remodel Solutions

Go Faster!

IMPROVED
HALO Canless EZ-Trim

(1) Downlight | (1) Lamp*



LOWER
INSTALLED COST**

* Sold by others.

** Less installation steps = less labor cost.



TRADITIONAL
HALO Remodel Housing

(1) Downlight | (1) Trim | (1) Lamp*



SAME
HEIGHT

SAME
GREAT
LOOK

Top 3 Reasons to Buy Canless EZ-Trim

1

FASTER
INSTALLATION

Less Steps
to Install



2


FEWER
COMPONENTS

Easier Ordering
Less Boxes

3

COMPLETE
SELECTION

3, 4, 6-inch and
shallow options



Canless EZ-Trim Series



CEZ3125GU10WBICAT

3-inch, shallow
GU10 lamp



CEZ4125GU10WBICAT

4-inch, shallow
GU10 lamp



CEZ6126GU24WBICAT

6-inch, shallow
GU24 lamp



CEZ6125GU24WBICAT

6-inch
GU24 lamp



CEZ4125E26WBICAT

4-inch, shallow
E26 lamp



CEZ6126E26WBICAT

6-inch, shallow
E26 lamp



CEZ6125E26WBICAT

6-inch
E26 lamp



Scan Here to
Learn More!

Product Features

- Durable metal baffle trim with attached j-box
- No housing required for installation
- Compatible with LED GU10, GU24 or E26 lamps
- Maximum lamp wattage: 15W
- IC rated, for direct contact with insulation
- Spring clips firmly secure fixture in ceiling

Traditional Housing Features Minus the Housing

- A. Air-Tite** pre-installed gasket
- B. Quick Connect** pre-installed push-in wiring connectors
- C. Slide-N-Side** pre-installed tool-less strain reliefs eliminate need for additional non-metallic cable connectors



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2022 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR51838422
November 18, 2022 8:55 AM



All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.