

Good

Better

Best

Click on products  
to learn more

		Panels						Retrofit Kit	Troffers		
		Backlit CGT	Backlit CGTS <sup>2</sup>	Edgelit FP	Edgelit FPS	Backlit CGTX	Edgelit FPX	Center Basket CBRK	Flat Lens GR	Center Basket Achieva ARS	Center Basket Cruze CZS
APPLICABILITY <sup>1</sup>	Education	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★
	Office	★★	★★	★★	★★★	★★★	★★★	★★	★★	★★	★★★
	Healthcare	★	★★	★	★	★★	★★	★	★★	★★	★★
	Retail	★★	★★	★★★	★★★	★★★	★★★	★	★★	★★	★★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	lm/W (Max)	115	159	136	120	137	130	168	140	146	156
	Lum (Max)	5,300	6,900	7,000	6,500	10,000	6,400	4,700	18,000	8,000	6,500
	Life (@60K)	L84	L86	L86	L87	L88	L87	L85	L89	L90	L90
	Lens	Frost, Smooth	Frost, Smooth	Frost, Smooth	Frost, Smooth	Frost - Smooth, Prismatic	Frost, Smooth	Frost, Ribbed	Frost, Prismatic	Round, Ribbed	Round or Square, Frost - Ribbed or Smooth, Perf Inlays
	Emergency	Remote	Remote	Remote	Remote	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80+	80+ / 90+	80+	80+ / 90+	80+	80+	80+	80+	80+
	Sensor Location	Tile Mount	Tile Mount	Tile Mount	Tile Mount	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	DLC	Standard	Standard	Standard	Standard	Premium	Premium	Premium	Standard / Premium	Standard / Premium	Standard / Premium
	Door	No	No	No	No	No	No	None	Yes	No	No - see Cruze SB
	Lumen / CCT Select	No	 Yes 	No	 Yes 	No	No	No	No	 Yes 	 Yes 
	VividTune™	No	No	No	No	No	No	No	Tunable White	No	No
INTEGRATED CONTROLS	WaveLinX Lite					✓	✓	✓	✓	✓	✓
	WaveLinX					✓	✓	✓	✓	✓	✓
	DLVP					✓	✓		✓		✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable. 2. CGTS-NUV also available (Canadian market only).