


Good

Better

Best

Click on products to learn more



| | | Panels | | | | | | Retrofit Kit | Troffers | | |
|----------------------------|--------------------|---------------|---------------------------|---------------|---------------|---------------------------|---------------|--------------------|--------------------|---------------------------|--|
| | | Backlit CGT | Backlit CGTS ² | Edgelit FP | Edgelit FPS | Backlit CGTX | Edgelit FPX | Center Basket CBRK | Flat Lens GR | Center Basket Achieva ARS | Center Basket Cruze CZS |
| APPLICABILITY ¹ | Education | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★★★ |
| | Office | ★★ | ★★ | ★★ | ★★★ | ★★★ | ★★★ | ★★ | ★★ | ★★ | ★★★ |
| | Healthcare | ★ | ★★ | ★ | ★ | ★★ | ★★ | ★ | ★★ | ★★ | ★★ |
| | Retail | ★★ | ★★ | ★★★ | ★★★ | ★★★ | ★★★ | ★ | ★★ | ★★ | ★★★ |
| FEATURES / PERFORMANCE | Sizes | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 | 1x4, 2x2, 2x4 |
| | lm/W (Max) | 115 | 159 | 136 | 120 | 137 | 130 | 168 | 140 | 146 | 156 |
| | Lum (Max) | 5,300 | 6,900 | 7,000 | 6,500 | 10,000 | 6,400 | 4,700 | 18,000 | 8,000 | 6,500 |
| | Life (@60K) | L84 | L86 | L86 | L87 | L88 | L87 | L85 | L89 | L90 | L90 |
| | Lens | Frost, Smooth | Frost, Smooth | Frost, Smooth | Frost, Smooth | Frost - Smooth, Prismatic | Frost, Smooth | Frost, Ribbed | Frost, Prismatic | Round, Ribbed | Round or Square, Frost - Ribbed or Smooth, Perf Inlays |
| | Emergency | Remote | Remote | Remote | Remote | Integrated | Integrated | Integrated | Integrated | Integrated | Integrated |
| | CRI | 80+ | 80+ | 80+ / 90+ | 80+ | 80+ / 90+ | 80+ | 80+ | 80+ | 80+ | 80+ |
| | Sensor Location | Tile Mount | Tile Mount | Tile Mount | Tile Mount | Integrated | Integrated | Integrated | Integrated | Integrated | Integrated |
| | DLC | Standard | Standard | Standard | Standard | Premium | Premium | Premium | Standard / Premium | Standard / Premium | Standard / Premium |
| | Door | No | No | No | No | No | No | None | Yes | No | No - see Cruze SB |
| | Lumen / CCT Select | No | Yes | No | Yes | No | No | No | No | Yes | Yes |
| VividTune™ | No | No | No | No | No | No | No | Tunable White | No | No | |
| INTEGRATED CONTROLS | WaveLinX Lite | | | | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| | WaveLinX | | | | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| | DLVP | | | | | ✓ | ✓ | | ✓ | | ✓ |

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable. 2. CGTS-NUV also available (Canadian market only).