

McGraw-Edison

GALN Galleon II

Features and Benefits

PERFORMANCE, DELIVERED

Galleon II area and site provides industry-leading, specification-defining outdoor lighting you could only expect from McGraw-Edison. With best-in-class optical distributions and virtually unlimited configurability, Galleon II sets the standard for ultra-high performance in outdoor lighting solutions.

PRODUCT FEATURES

- Lumen packages range from 3,300 – 102,700 (33W – 658W)
- Efficacy up to 178 lumens per watt
- 22 optical distributions
- Available in 4, 6 and 9 square housings

PRODUCT BENEFITS



Unmatched Configurability

Broad range of CCT/CRI combinations, optics and mounting options provide the most flexible platform available.



Superior Backlight Control

Five new backlight control optics eliminate spill light while maintaining high output and best-in-industry efficiency.




Controls

From stand-alone to connected systems, WaveLinx leads the way toward energy savings and perceived safety.



Sustainability

Replaceable light squares, drivers and other electronics ensure full serviceability, reducing waste and expense.



GALN Galleon II



QUICK FACTS

- 0-10V dimming driver standard
- IK10 rated
- 3G vibration rated
- 10kV surge standard
- Five year limited warranty

