



Save Money



Save Time



Peace of Mind

The NWS Selectable LED wrap is a commercial grade solution suitable for ceiling, wall, or suspension mounting. NWS is offered in both 2' and 4' lengths along with selectable color options of 3500K, 4000K, or 5000K and selectable light output with up to 5,000 lumens. NWS delivers increased energy savings with up to 143 lm/W efficiency and offers an integrated sensor option for even more savings and code compliance. NWS is designed to provide soft diffused lines of light in corridors, hallways, stairwells, in addition to other ambient office, education, and healthcare spaces.



Features		Benefits	Result
Construction	Lightweight robust housing design	Easy installation and lower maintenance	✓
	Smooth frosted lens	Blends seamlessly into any ceiling design with balanced visual comfort	✓
	Suitable for ceiling, wall, or suspension mounting	Ultimate design flexibility	⌚ ✓
Performance	Selectable color in 3500K, 4000K or 5000K and selectable lumens up to 5,000 with up to 143 lm/W efficiency	Inventory friendly, increases turns, and a fit for any lighting application	💰 ⌚
	Sensor Integrated options	Increased energy savings and code compliance for stairwells and other commercial spaces requiring basic controls	✓
	DLC®, 5-year warranty, 50K life hours at L70	Eligible for energy rebates; certified and guaranteed performance	💰 ✓

Energy and Performance Data by Catalog Number

Size	Catalog Number	UPC	Volt	OCC	Lumen Setting	Nominal CCT	CRI	Delivered Nominal Lumens	Watts	Efficacy (lm/W)	Wt.	Units per Pallet
2 ft	2NWS3C3-UNV	080083257485	120-277V	NO	High	3500K	82	2,522	21.8	116	3.1 lbs.	224
						4000K	82	2,679	21.0	128		
						5000K	82	2,574	21.7	119		
					Medium	3500K	82	2,266	18.0	126		
						4000K	82	2,366	17.5	135		
						5000K	82	2,294	18.1	127		
					Low	3500K	82	2,009	15.8	127		
						4000K	82	2,087	15.3	136		
						5000K	82	2,032	15.8	128		
4ft	4NWS3C3-UNV	080083257522	120-277V	NO	High	3500K	82	4,937	40.6	122	4.6 lbs.	112
						4000K	82	5,272	38.9	136		
						5000K	82	5,010	40.7	123		
					Medium	3500K	82	4,324	33.1	130		
						4000K	82	4,498	31.8	141		
						5000K	82	4,357	33.2	131		
					Low	3500K	82	3,800	28.5	133		
						4000K	82	3,930	27.5	143		
						5000K	82	3,822	28.5	134		
4ft	4NWS3C3MS-UNV	080083257607	120-277V	YES	High	3500K	82	4,851	38.9	125	4.6 lbs.	112
						4000K	82	5,016	37.7	133		
						5000K	82	4,872	38.8	126		
					Medium	3500K	82	4,145	32.7	127		
						4000K	82	4,285	31.7	135		
						5000K	82	4,216	32.5	130		
					Low	3500K	82	3,675	28.7	128		
						4000K	82	3,766	27.8	135		
						5000K	82	3,729	28.5	131		
4ft	4NW35C3R	080083257447	120V	NO	3500L	3000K	82	3,830	35.8	107	4.6 lbs.	112
						3500K	82	4,124	34.0	121		
						4000K	82	3,954	35.5	111		