

VAULTA
Linear Series

Corelite





Vaulta Linear Series

With an open aperture design the Vaulta creates a striking presence with a weightless feel enhanced by the clean edge design.

Featuring multiple optic options you can customize the fixture to meet your lighting needs.



Unravel Seamless Illumination

Say goodbye to lens gaps and breaks in illumination common in traditional linear runs. Seamless illumination and high performance is possible with a proprietary flexible continuous roll lens that won't ripple or bow over long lengths and high efficacies that provide significant energy savings. The result is high quality uniform illumination along the entire run length for a truly unique aesthetic.



Go Easy on the Eyes


Say hello to a space that is more comfortable on the eyes. The black or white louvered baffles use an engineered optical system to reduce light glare while providing efficient lighting where needed in a space. The result is superior visual comfort with ultra low UGR values to go along with its unique aesthetic..





Ditch the Bulk

Embrace an open aperture design with clean striking lines that make the Vaulta look weightless.




Installation versatility


Get piece of mind with the use of Corelite's modular section design, through wiring, and simple yet robust joining features.

- 4', 6', 8', 12' simple building blocks to create longer runs.
- Joining fixtures is quick and provides a ridged and tight connection.
- Navigate existing ceiling obstructions with variable mounting locations.
- The 12 ft. unit advantage – Reduce time and labor costs during installation with 33% fewer fixtures, joint connections, and mounting points compared to 8 ft. unit max.

Adjustable Mounting



Rigid alignment and joining



Connected lighting enabled solution

Corelite Vaulta luminaires are designed to support integrated sensors providing code compliance and energy savings. The Vaulta’s unique sensor integration simplifies the control design without impacting the seamless illumination aesthetic. With sensors factory-installed in every fixture, the fixture layout enables optimal sensor coverage and controllability. With connected lighting, Vaulta makes your facility smarter so you can make smarter decisions.

Lighting fixture with sensor

Wireless Area Controller

Mobile Applications

Energy Savings



WaveLinx

Wireless Connected Lighting System


- Adjustable occupancy detection and daylight harvesting control
- Simple, secure wireless connectivity with out-of-the-box code compliance
- Easy to use mobile application allows for fast set up and unlocks advanced control capabilities

Lighting fixture with sensor

Wall Station

Mobile Applications


Energy Savings +




WaveLinx Lite

Simple. Secure. Scalable.

Building upon known motion sensor solutions, the WaveLinx Lite solution eliminates all the hassles associated with a complex lighting controls solution making the commissioning process intuitive and flexible, giving more power to installers/owners



Vaulta Suspended with Integrated Sensor - Endcap



Vaulta Suspended with Integrated Sensor - Side Mount


Technical specifications

SERIES VLT, Vaulta Linear Suspended and Surface	
SHIELDING Continuous Seamless Roll Lens Black Glare Reducing Baffle White Glare Reducing Baffle	
LUMEN PACKAGE UP No Uplight 250 Lumens/ft Up 500 Lumens/ft Up 750 Lumens/ft Up 1000 Lumens/ft Up 1250 Lumens/ft Up 1500 Lumens/ft Up	LUMEN PACKAGE DOWN No Downlight 500 Lumens/ft Down 750 Lumens/ft Down 1000 Lumens/ft Down 1250 Lumens/ft Down
COLOR TEMPERATURE 3000K 3500K 4000K	80+ or 90+ CRI 3000K-5000K (90+ CRI) 2700K-6500K (90+ CRI)
VOLTAGE Universal 120-277 VAC 347 VAC	
FINISH White Silver	Black Custom Color
RUN LENGTH 2' 4' 6'	8' 12' Continuous
OPTIONS Optional Batwing or Asymmetric direct distribution with continuous roll lens Independent Up/Down Circuits Emergency Circuit 0-10V (1%), DALI 2.0, Lutron Dimming Control Integral Emergency Battery Pack & UL924 Relay Integral WaveLinx Sensor	
ADDITIONAL INFORMATION: Warranty: 5 year standard cULus: Damp Location Listed Tested to IESNA LM79 and LM80 RoHS: Compliant Rated Life L84 @ 60,000 hours	

Compliance and approvals



Dimensional details



Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Shaper Prentalux
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
HALO Home
iLumin Plus
Enlighted
WaveLinx
Trellix



Cooper Lighting Solutions
18001 East Colfax Avenue
Aurora, CO 80011
P: 303-393-1522
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2023 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR52463523EN
January 6, 2023 8:26 AM

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.