



	HU11 Under Cabinet	HU30M Modular High Performance Under Cabinet	HALO Flexible Linear LED Tape (HFL)
Lumens/ft	380	300	200 & 400
CRI/CCT	3-color SeleCCTable™ (27/30/4000K) 90+ CRI	5-color SeleCCTable™ (27/30/35/40/5000K) 90+ CRI	5-color SeleCCTable™ (27/30/35/40/5000K) 90+ CRI
Dim-To-Warm(@ 120V)		Yes (D2W 2700K-1800K)	
Dimmable (@ 120V)	ELV down to 5%	ELV down to 5%	ELV and 0-10 down to 5%
Thickness	0.9"	0.75"	0.05" (LED on tape)
Available Lengths	9", 18", 24", 36", 48"	9", 18", 24", 36", 48"	Tape: 24' & 96' rolls-Field cuttable every 2.5", Channels & Lenses - 4' & 8'- Field cuttable
Linkable	Yes	Yes	Yes
Direct Wire	Yes	Yes	Yes
Plug-In Cord Available	Yes	Yes	
Finishes	Matte Black, White	Matte Black, White	Raw Aluminum channels
Dry/Wet/Damp Rating	Damp	Damp	Damp
Energy Compliance	ENERGY STAR®, T24(JA8)	ENERGY STAR®, T24(JA8)	T24(JA8)
Voltage	120V	120V - 277V (UNV)	Tape: 24V Triac Driver: 120V /0-10V Driver: 120V - 277V (UNV)
Motion Sensor/USB accessory		Yes	
Compatible with Existing Connectors	Yes	Yes	N/A
Specialized Low Glare Optics	No	Yes	Diffuse lens