


Project		Catalog #		Type	
Prepared by		Notes		Date	

Interactive Menu

- Halo Brand Page
- Halo Commercial Brand Page
- Portfolio Brand Page


HALO HALO Commercial Portfolio

Oversize "Goof" Rings & Accessory Trim Rings




OT400P

- Metal ring with 5.875" ID opening, 9.5" OD flange, matte white




OT403P

- Plastic ring with 6.0" ID opening, 8" OD flange, matte white




OT450P

- Metal ring with 5.5" ID opening, 8" OD flange, matte white




OT460P

- Metal ring with 7.5" ID opening, 11.25" OD flange, matte white




OT999P

- Metal ring with 4.0" ID opening, 5.75" OD flange, matte white




OT500P

- Plastic ring with 6.0" ID opening, 7.25" OD straight-sided flange, matte white
- Straight side flange also matches Halo H5 trims




ABR6P

- Metal ring with 6.40" ID opening, 7.25" OD flange, matte white




ABR7P

- Metal ring with 6.40" ID opening, 8.30" OD flange, matte white



ABR8P

- Metal ring with 6.40" ID opening, 9.30" OD flange, matte white
- Recommended max 8-9/16" ceiling opening



ABR10P

- Metal ring with 8.78" ID opening, 11.30" OD flange, matte white
- Recommended max 10" ceiling opening



TRM6P

- Die formed 0.05" thick aluminum trim ring, with 6.0" ID opening, 7.25" OD tapered flange, Matte White

TRM6SN

- Die formed 0.05" thick aluminum trim ring, with 6.0" ID opening, 7.25" OD tapered flange, Satin Nickel

TRM6TBZ

- Die formed 0.05" thick aluminum trim ring, with 6.0" ID opening, 7.25" OD tapered flange, Tuscan Bronze

TRM6MB

- Die formed 0.05" thick aluminum trim ring, with 6.0" ID opening, 7.25" OD tapered flange, Matte Black

- Compatible with Halo trims: 310*, 312*, 353*, 376, 378, 400, 404, 405, 406SC, 409, 410, 416, 419, 420, 424, 425, 426*, 429*, 446, 448, 455*, 456*, 477, 478, 1412, 1416, 1475

