

Vandal Resistant LED Wall Packs

Selection Guide



Fail-Safe

Good

Better

Best

Click on products
to learn more



		B95	H12	G12	TR11	TR15
APPLICABILITY ¹	Behavioral Health	★★	★★	★★	★★★	
	Outdoor Vandal Resistant	★★★	★★★	★★★	★★★	
	Indoor Vandal Resistant	★★	★★	★★	★★★	
	Industrial High Abuse	★★★	★★★	★★★	★★★	
	Multifamily homes	★★	★★	★★	★★★	
MOUNTING	Wall	✓	✓	✓	✓	
	Ceiling	✓	✓	✓	✓	
FEATURES	Size	5" x 9" Rectangle	12" x 12" Square	12" x 12" Square	11" Round	15" Round
	Maximum Lumen Output	1,975	4,703	3,750	2,630	4,875
	Lens Thickness	0.130"	0.156"	0.130"	0.125"	
	Emergency	N/A	Optional	Optional	Optional	
	Occupancy	N/A	Optional	Optional	Optional	
	Photocell	Optional	Optional	Optional	Optional	
CERTIFICATIONS	IP	IP65	IP65	IP65	IP65	
	Wet Location	Standard	Standard	Standard	Standard	

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable