



The new **Revolve™** LED outdoor security product line by **ALL-PRO™** combines advanced LED technology and industry-leading optic design to bring you a low profile fixture with uncompromising performance. Available in Motion Activated, Dusk to Dawn and Flood versions, this innovative solution comes in 3500K or 5000K CCT to meet the requirements of any installation.

270° Motion Sensor - Triple Head

- Sleek, contoured design optimized for low profile applications
- Motion sensor coverage of 270°, range up to 50'
- Integral dusk to dawn sensor ensures lights only come on after dark
- Optics rotate 360° for maximum adjustability
- Eave mount only



Model #	Description	UPC	Unit Carton Dimensions	Master Carton	Master Carton Dimensions
REV32735M	270° Triple Head LED Floodlight, 3500K - Bronze	0 80083 72191 7	9.3" W x 10.6" H x 3.6" D	2 Pk	9.8" W x 11.1" H x 7.7" D
REV32735MW	270° Triple Head LED Floodlight, 3500K - White	0 80083 72190 0	9.3" W x 10.6" H x 3.6" D	2 Pk	9.8" W x 11.1" H x 7.7" D
REV32750M	270° Triple Head LED Floodlight, 5000K - Bronze	0 80083 72185 6	9.3" W x 10.6" H x 3.6" D	2 Pk	9.8" W x 11.1" H x 7.7" D
REV32750MW	270° Triple Head LED Floodlight, 5000K - White	0 80083 72184 9	9.3" W x 10.6" H x 3.6" D	2 Pk	9.8" W x 11.1" H x 7.7" D

180° Motion Sensor - Twin Head

- Sleek, contoured design optimized for low profile applications
- Motion sensor coverage of 180°, range up to 50'
- Integral dusk to dawn sensor ensures lights only come on after dark
- Optics rotate 360° for maximum adjustability
- Eave mount only



Model #	Description	UPC	Unit Carton Dimensions	Master Carton	Master Carton Dimensions
REV21835M	180° Twin Head LED Floodlight, 3500K - Bronze	0 80083 72203 7	12" W x 7.2" H x 3.8" D	2 Pk	12.5" W x 8.1" H x 7.8" D
REV21835MW	180° Twin Head LED Floodlight, 3500K - White	0 80083 72202 0	12" W x 7.2" H x 3.8" D	2 Pk	12.5" W x 8.1" H x 7.8" D
REV21850M	180° Twin Head LED Floodlight, 5000K - Bronze	0 80083 72197 9	12" W x 7.2" H x 3.8" D	2 Pk	12.5" W x 8.1" H x 7.8" D
REV21850MW	180° Twin Head LED Floodlight, 5000K - White	0 80083 72196 2	12" W x 7.2" H x 3.8" D	2 Pk	12.5" W x 8.1" H x 7.8" D

Flood and Dusk to Dawn - Triple Head

- Dusk to dawn versions feature integrated photocell
- Perfect for wall or eave mount

Dusk to Dawn

Model #	Description
REV335PCW	Triple Head LED D2D Floodlight, 3500K - White
REV350PCW	Triple Head LED D2D Floodlight, 5000K - White

Flood

Model #	Description
REV335F	Triple Head LED Floodlight, 3500K - Bronze
REV335FW	Triple Head LED Floodlight, 3500K - White
REV350FW	Triple Head LED Floodlight, 5000K - White



Eave Mount



Wall Mount

Flood and Dusk to Dawn - Twin Head

- Dusk to dawn versions feature integrated photocell
- Perfect for wall or eave mount

Dusk to Dawn

Model #	Description
REV235PCW	Twin Head LED D2D Floodlight, 3500K - White
REV250PC	Twin Head LED D2D Floodlight, 5000K - Bronze
REV250PCW	Twin Head LED D2D Floodlight, 5000K - White

Flood

Model #	Description
REV235F	Twin Head LED Floodlight, 3500K - Bronze
REV235FW	Twin Head LED Floodlight, 3500K - White
REV250F	Twin Head LED Floodlight, 5000K - Bronze
REV250FW	Twin Head LED Floodlight, 5000K - White




Eave Mount



Wall Mount

Coverage Area



For more information
download the QR
code reader for your
smartphone and scan.

Features

Maintenance-free LEDs with
70,000 hours of life

Durable, die-cast
aluminum housing

Mounts easily to
recessed junction box;
cover plate included



Optics rotate 360° for
maximum adjustability

Patents pending optics,
mounting bracket and design

Timing and sensitivity
adjustments (Motion
Activated versions)