

Project		Catalog #		Type	
Prepared by		Notes		Date	



# AtLite

## Marathon Series - Surface Mount

### Architectural Edge Lit Exit Sign

#### Typical Applications

Office • Education • Healthcare • Hospitality • Retail

#### Product Certification



#### Product Features



**Interactive Menu**

- Dimensions and Mounting Details [page 2](#)
- Product Specifications [page 2](#)
- Energy Data [page 2](#)
- Product Warranty

### Top Product Features

- Dual 120/277 VAC 60Hz input
- Solid-state battery charger and switching in self-powered version
- Brownout circuit; test switch/power indicator light
- Long-life, energy-efficient LED lamps
- High-impact, clear acrylic panel
- Options to meet Buy American and other domestic preference requirements


### Ordering Information

SAMPLE ORDER NUMBER: **SCM-A16GCBKAL, SCM-A18RCPA-INVERTED**


Domestic Preferences	Mounting	Operation	Number of Faces	Letter Size	Letter/Panel Color	Trim Finish	Arrow Direction
<b>Domestic Preferences</b> <sup>(1)</sup> <b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act	<b>Mounting</b> <sup>(2)</sup> <b>SBM</b> =Back Wall <b>SCM</b> =Ceiling <b>SEM</b> =End Wall <b>SPM</b> =Pendant <b>SCM ___-Inverted</b> =Mullion Mount <sup>(2)</sup>	<b>Operation</b> <b>A</b> =AC-Only <b>S</b> =Self-Powered	<b>Number of Faces</b> <b>1</b> =Single <b>2</b> =Double	<b>Letter Size</b> <b>6-6</b> <b>8-8</b> (Red Only)	<b>Letter/Panel Color</b> <b>GC</b> =Green on Clear (Single Face Only) <b>GW</b> =Green on White <b>GM</b> =Green on Mirror Mylar <b>RC</b> =Red on Clear (Single Face Only) <b>RM</b> =Red on Mirror Mylar <b>RW</b> =Red on White	<b>Trim Finish</b> <sup>(3)</sup> <b>BK</b> =Polished Black <b>BZ</b> =Bronze <b>PA</b> =Polished Aluminum <b>SA</b> =Satin Aluminum <b>WH</b> =White	<b>Arrow Direction</b> <b>[Blank]</b> =No Arrow <b>AL</b> =Arrow Left <b>AR</b> =Arrow Right <b>DH</b> =Double Headed Arrows <b>LR</b> =Double Face Arrows
<b>Notes</b> (1) Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to <a href="#">DOMESTIC PREFERENCES</a> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	<b>Notes</b> (2) Mullion Mount, or Inverted mounting available. Cat logic has "Inverted" as last section. For example: SCM-A18RCPA-INVERTED.					<b>Notes</b> (3) Limited custom finishes available, contact factory for details.	

Dimensional Details


SURFACE, WALL MOUNT




SURFACE, CEILING MOUNT




SURFACE, END MOUNT



SURFACE, PENDANT MOUNT



SURFACE, BOTTOM MOUNT



Product Specifications

General Features

- Dual 120/277 VAC 60Hz input
- Solid-state battery charger and switching in self-powered version
- Brownout circuit; test switch/power indicator light
- Long-life, energy-efficient LED lamps
- High-impact, clear acrylic panel
- Long life nickel cadmium battery
- 5 year product warranty
- Options to meet Buy American and other domestic preference requirements

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

**COMPLIANCES:** UL924 Listed; NFPA 101 Compliant, NYC Code Compliant

Energy Data

Maximum power consumption under all charge conditions:

LED Exits – Red Letters, AC Only

Input Power	Input Current (Max):	Power Factor:
120V = 3.8W	120V = .03	120V = .93
277V = 3.9W	277V = .02	277V = .93

LED Exits – Red Letters, Self-Self-Powered

Input Power	Input Current (Max):	Power Factor:
120V = 4.6W	120V = .04	120V = .90
277V = 4.8W	277V = .02	277V = .89