DESCRIPTION

The HLA4 is a 4-inch ultra-thin round or square LED directional with remote driver / junction box suitable for new construction and remodel applications. Field selectable color temperature and high color rendering provide excellent color performance. Simplified installation in drywall or suspended ceilings eliminates recessed cans saving time and money. Installs from below the ceiling in as little as 1-1/2" plenum height, can be used in direct contact with insulation and is airtight. Use for accent or task lighting in low to medium height ceilings where energy savings, long life and economy are required.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

HOUSING

- Die cast aluminum mounting frame with round or square flange
- Gimbal rotates 360° and tilts ± 30° holding any aiming angle
- Aluminum heat sink provides passive thermal cooling achieving L70 at 50,000 hours in IC and non-IC applications

GASKET

 Closed cell gasket achieves restrictive airflow and wet location listing without additional gaskets or caulking

OPTIONAL MOUNTING FRAME

- Pre-galvanized steel mounting frame locates fixture fittings during electrical rough in and provides cutout guidance for drywall contractor
- Provides tool-less attachment of remote driver / junction box

OPTICS

- Flood FL
 Optical design creates a clean, uniform 40-degree beam distribution
- Very Wide Flood VWFL
 Reflector organizes source flux
 into VWFL distribution, useful for
 accent and task lighting

LED ARRAY

- Plurality of mid power LED's provides a uniform source with high efficiency and long life
- Available in 90 CRI minimum, R9 greater than 50 provides high color rendering
- Field selectable color temperature, select 2700, 3000, 3500, 4000 or 5000 K CCT, color accuracy within 4 SDCM
- Meets ENERGY STAR® color angular uniformity requirements, deviation is less than 0.006 u' v'

REMOTE DRIVER / JUNCTION BOX

- Pre-galvanized steel driver / junction box with captive hinged junction box cover
- Listed for (6) #12 AWG 90° C splice conductors, 2-in, 2-out plus (2) ground
- (2) 1/2" conduit pry-outs
- (2) Slide-N-Side[™] non-metallic (NM) wire traps allows wiring outside the box
- Accepts 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts with clear caps for quick and reliable mains voltage connections
- Integral mounting slots facilitate direct mounting to building structure or mounting frame

DRIVER

- 120V 60 Hz constant current driver provides noise free operation
- Continuous, flicker-free dimming from 100% to 5% with select leading or trailing edge 120V phase cut dimmers
- Plenum rated inline electrical quick connect provides low voltage connection to fixture fitting

INSTALLATION

- Can be installed in 1/2" to 1-1/4" thick ceilings
- Cutout utilizes standard round hole saw sizes, cutout template provided
- Heat treated springs hold fixture fitting securely in the ceiling eliminating light leaks
- Can be removed from below the ceiling for service or replacement

COMPLIANCE

- cULus certified type IC suitable for direct contact with air permeable insulation
- Not recommended for use in direct contact with spray foam insulation, reference NEMA LSD57-2013
- Wet location listed and IP44 ingress protection
- Airtight per ASTM-E283-04
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy LED compliance under JA8, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2016 JA8 High Efficacy Lighting
- ENERGY STAR® certified, reference "Certified Light Fixtures" database

WARRANTY

Lumens

Input Voltage

Input Current

Input Power

Efficiency

Inrush (A)

T Ambient

Sound Rating

THD

PF

 Five year limited warranty, consult website for details. www.eaton.com/lighting/legal

ENERGY DATA

600 Series

120V

90 (mA)

10.5 (W)

60 (LPW)

1.9 A @ 54mS

≤ 20%

≥ 0.90

-30° - +40°C

≤ 22 dba










HLA4

4-Inch LED Directional with Remote Driver / Junction Box

Flood (FL) or Very Wide Flood (VWFL)

Round or Square Flange

Up to 700 Lumens Field Selectable CCT







Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24
















High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.

TD518340EN
February 27, 2023 10:53 AM

DIMENSIONS



ORDERING INFORMATION

SAMPLE NUMBER: HLA406VWFL9FS1EMWR

Models	Lumens	Distribution	CRI / CCT	Driver	Finish	Packaging
HLA4 = 4-Inch LED round directional with remote driver / junction box	06 =600 lumens (nominal)	FL=40° flood distribution VWFL=80° very wide flood distribution	9FS =90 CRI minimum, field selectable 2700, 3000, 3500, 4000 or 5000 K CCT	1E= 120V 50-60Hz, LE &TE phase cut 5% dimming	MW= matte white flange	R= recyclable 4-color unit carton suitable for point of purchase merchandizing display
Accessories						

Oversized Trim Ring
HLB4ROTMW = 4" round oversized trim, matte white

Designer Trims
HLB4RTRMMW = 4" round decorative overlay, matte white
HLB4RTRMSN = 4" round decorative overlay, satin nickel
HLB4RTRMTBZ = 4" round decorative overlay, tuscan bronze
HLB4RTRMMB = 4" round decorative overlay, matte black

Mounting Frame
HL4RSMF = 4" round and square mounting frame

Extension Cables

HLB06FSEC - 6 ft. extension cable HLB12FSEC - 12 ft. extension cable HLB20FSEC - 20 ft. extension cable

SAMPLE NUMBER: HLA4S06FL9FS1EMWR

Models	Lumens	Distribution	CRI / CCT	Driver	Finish	Packaging
HLA4S = 4-Inch LED square directional with remote driver / junction box	06=600 lumens (nominal)	FL=40° flood distribution VWFL=80° very wide flood distribution	9FS =90 CRI minimum, field selectable 2700, 3000, 3500, 4000 or 5000 K CCT	1E= 120V 50-60Hz, LE &TE phase cut 5% dimming	MW= matte white flange	R= recyclable 4-color unit carton suitable for point of purchase merchandizing display
Accessories						

Oversized Trim Ring HLB4SOTMW = 4" square oversized trim, matte white

Designer Trims
HLA45TRMMW = 4" square decorative overlay, matte white
HLA45TRMSN = 4" square decorative overlay, satin nickel
HLA45TRMTBZ = 4" square decorative overlay, tuscan bronze
HLA45TRMMB = 4" square decorative overlay, matte black

Extension Cables
HLB06FSEC - 6 ft. extension cable
HLB12FSEC - 12 ft. extension cable HLB20FSEC - 20 ft. extension cable




HALO

PHOTOMETRIC DATA


HLA406VWFL9FS1EMWR					
Luminair	670				
Input	10.1				
LER (66.34				
	0-180	1.18			
Spacing Criteria	90-270	1.18			
Ontona	Diagonal	1.28			
Beam angl	Beam angle (degrees)				
Field angle	156.7				
Zonal lumen	Lumens	% Lumens			
0-30	238.1	35.53			
0-40	361.4	53.94			
		85.04			
0-60	569.8	85.04			
0-60 0-90	569.8 670.0	85.04 100			

^{*} Tested in accordance with IES LM63. Field results may vary.

Color Metric Summary - 3000K




Product Specifications



HLA4 4-inch VWFL	ССТ	Lumens	Power (W)	LPW
Field Selectable CCT	2700K	704	10.1	69.7
	3000K	670	10.1	66.4
	3500K	673	10.1	66.6
	4000K	671	10.1	66.4
	5000K	656	10.1	65.0

HLA406FL9FS1EMWR Luminaire lumens 711 Input watts 10.2 LER (LPW) 69.71 0-180 0.66 **Spacing** 90-270 0.66 Criteria Diagonal 0.64 Beam angle (degrees) 39.4 Field angle (degrees) 69.3 **Zonal lumen** Lumens % Lumens 0-30 546.8 76.9 0-40 625.7 88 96.4 0-60 685.4 711 0-90 100




^{*} Tested in accordance with IES LM63. Field results may vary.

Color Metric Summary - 3000K

TM-30-15	Rf = 90	
1101-30-15	R _g = 100	
CRI/CIE	Ra = 92	
	R9 = 59	40°
CCT - Ran	ne of 2700K- 5000K	

Product Specifications



HLA4 4-inch VWFL	ССТ	Lumens	Power (W)	LPW
Field Selectable CCT	2700K	689	10.2	67.5
	3000K	711	10.2	69.72
	3500K	730	10.2	71.58
	4000K	745	10.2	73.04
	5000K	759	10.2	74.39

^{*}Additional photometric ies files available online.

