



Troffer



High Bay



Wraparound



Striplight



Parabolic



Low Bay



Vaportite

- Troffer
- High Bay
- Wraparound
- Striplight
- Parabolic
- Low Bay
- Vaportite

Product Reference Guide

Distributor's Stock - March, 2012

All-Pro™ Product Reference Guide

	All Pro Catalog Number	UPC	Product Description	Ballast Type	NEMA	CEE	Weight (lbs)	Pallet Qty
COMMERCIAL Troffers (APT) 	APT-432	080083621934	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	20.5	28
	APT-332	080083621941	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	20.5	28
	APT-432-L741	080083621965	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/741 LAMPS	Instant Start	Yes	Yes	21.9	28
	APT-432-L735	080083621972	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM UNV ELECTRONIC BALLAST, T8 W/735 LAMPS	Instant Start	Yes	Yes	21.9	28
	APT-432-L735F	080083621989	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS & FLEX	Instant Start	Yes	Yes	21.9	28
	APT-332-L735F	080083621996	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS & FLEX	Instant Start	Yes	Yes	21.55	28
	APT-232	080083622009	2 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	20.5	28
	APT-332-L735	080083622016	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS	Instant Start	Yes	Yes	21.55	28
	APT-332-2EB	080083622023	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, TWO NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	20.5	28
	APT-432-2EB	080083622030	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, TWO NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	20.5	28
	APT-432-L741F	080083622047	4 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/741 LAMPS & FLEX	Instant Start	Yes	Yes	23.88	28
	APT-332-L741	080083622054	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/741 LAMPS	Instant Start	Yes	Yes	21.9	28
	APT-332-L741F	080083622061	3 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/741 LAMPS & FLEX	Instant Start	Yes	Yes	23.88	28
	APT-232-L735F	080083622078	2 LAMP, 2'X4' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS & FLEX	Instant Start	Yes	Yes	23.53	28
	APT-2U6T8	080083621958	2 LAMP, 2'X2' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM U6T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	12.2	56
	APP-332	080083621866	3 LAMP, 2'X4' PARABOLIC, 18 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	24	20
	APP-332-2EB	080083621927	3 LAMP, 2'X4' PARABOLIC, 18 CELL, SEMI SPECULAR LOUVER, TWO NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	25.3	20
	APP-332-L735	080083621910	3 LAMP, 2'X4' PARABOLIC, 18 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS	Instant Start	Yes	Yes	25.1	20
	APP-332-L735F	080083621903	3 LAMP, 2'X4' PARABOLIC, 18 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST W/735 LAMPS & FLEX	Instant Start	Yes	Yes	26.4	16
Parabolics (APP/APPV) 	APPV-332	080083621873	3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, 18 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	23.7	20
	APP-2U6T8	080083621880	2 U-LAMP, 2'X2' PARABOLIC, 9 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	13.7	36
	APPV-2U6T8	080083621897	2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC, 9 CELL, SEMI SPECULAR LOUVER, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	13.5	36
NOTE: Specification sheets provided via Cooper website. Subject to change without notice.								

All-Pro™ Product Reference Guide

	All Pro Catalog Number	UPC	Product Description	Ballast Type	NEMA	CEE	Weight (lbs)	Pallet Qty
Wraps (APW-GPW) 	APW-GPW217	080083622146	2 LAMP, 2' GENERAL PURPOSE WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	5.02	90
	APW-GPW232	080083622115	2 LAMP, 4' GENERAL PURPOSE WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	10.03	54
	APW-GPW332	080083622122	3 LAMP, 4' GENERAL PURPOSE WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	11.38	54
	APW-GPW432	080083622139	4 LAMP, 4' GENERAL PURPOSE WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	11.41	180
Wraps (APW-SW) 	APW-SW232	080083622153	2 LAMP, 4' SPECIFICATION WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	8.91	48
	APW-SW332	080083622160	3 LAMP, 4' SPECIFICATION WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	12.38	24
	APW-SW432	080083622177	4 LAMP, 4' SPECIFICATION WRAP, PRISMATIC LENS, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	12.41	24
Striplights (APS-NS) 	APS-NS120-R	080083622283	1 LAMP, 24" NARROW STRIPLIGHT, T12 120V ELECTRONIC BALLAST	Rapid Start	No	No	4.2	168
	APS-NS117	080083622313	1 LAMP, 24" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	4.2	168
	APS-NS217	080083622320	2 LAMP, 24" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	No	No	4.2	168
	APS-NS130-R	080083622290	1 LAMP, 36" NARROW STRIPLIGHT, T12 120V ELECTRONIC BALLAST	Rapid Start	No	No	4.56	84
	APS-NS125	080083622337	1 LAMP, 36" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	No	No	4.56	84
	APS-NS225	080083622344	2 LAMP, 36" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	4.56	84
	APS-NS140-R	080083622306	1 LAMP, 48" NARROW STRIPLIGHT, T12 120V ELECTRONIC BALLAST	Rapid Start	No	No	4.67	84
	APS-NS132	080083622351	1 LAMP, 48" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	No	No	4.67	84
	APS-NS232	080083622382	2 LAMP, 48" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	4.67	84
	APS-8NS132	080083622368	2 LAMP, 96" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	9.34	126
Striplights (APS-WS) 	APS-8NS232	080083622399	4 LAMP, 96" NARROW STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	9.34	126
	APS-WS232	080083622412	2 LAMP, 48" WIDE STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	6.43	90
	APS-WS248HO-T12	080083622443	2 LAMP, 48" WIDE STRIPLIGHT, T12HO 120V ELECTRONIC BALLAST	Rapid Start	No	No	6.43	90
	APS-8WS232	080083622405	4 LAMP, 96" WIDE STRIPLIGHT, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	12.09	72
	APS-WS296HO-T12	080083622450	2 LAMP, 96" WIDE STRIPLIGHT, T12HO 120V ELECTRONIC BALLAST	Rapid Start	No	No	12.09	72
INDUSTRIAL High Bays (APHL) 								
	APHL-432-SN-UPL	080083622191	4 LAMP, 48" HIGH BAY, NARROW SPECULAR REFLECTOR WITH UPLIGHT, HIGH OUTPUT T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	15.44	34
	APHL-432-SW-UPL	080083622207	4 LAMP, 48" HIGH BAY, WIDE WHITE REFLECTOR WITH UPLIGHT, HIGH OUTPUT T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	15.44	34
	APHL-454-SN-UPL	080083622238	4 LAMP, 48" HIGH BAY, NARROW SPECULAR REFLECTOR WITH UPLIGHT, T5HO UNV ELECTRONIC BALLAST	Program Start	No	No	15.44	34
	APHL-454-SW-UPL-L850	080083622245	4 LAMP, 48" HIGH BAY, WIDE WHITE REFLECTOR WITH UPLIGHT, T5HO UNV ELECTRONIC BALLAST WITH 850 LAMPS	Program Start	No	No	16.82	34
	APHL-632-SN-UPL	080083622214	6 LAMP, 48" HIGH BAY, NARROW SPECULAR REFLECTOR WITH UPLIGHT, HIGH OUTPUT T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	15.48	34
	APHL-632-SW-UPL	080083622221	6 LAMP, 48" HIGH BAY, WIDE WHITE REFLECTOR WITH UPLIGHT, HIGH OUTPUT T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	15.48	34
	APHL-654-SN-UPL	080083622252	6 LAMP, 48" HIGH BAY, NARROW SPECULAR REFLECTOR WITH UPLIGHT, T5HO UNV ELECTRONIC BALLAST	Program Start	No	No	15.48	34
	APHL-654-SW-UPL-L850	080083622269	6 LAMP, 48" HIGH BAY, WIDE WHITE REFLECTOR WITH UPLIGHT, T5HO UNV ELECTRONIC BALLAST WITH 850 LAMPS	Program Start	No	No	16.86	34
NOTE: Specification sheets provided via Cooper website. Subject to change without notice.								

All-Pro™ Product Reference Guide

	All Pro Catalog Number	UPC	Product Description	Ballast Type	NEMA	CEE	Weight (lbs)	Pallet Qty
Low Bays (APLBC and APLBA) 	APLBA-232	080083622085	2 LAMP, 48" LOW BAY INDUSTRIAL, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST WITH 8% UPLIGHT	Instant Start	Yes	Yes	9.33	48
	APLBC-232	080083622092	2 LAMP, 48" LOW BAY INDUSTRIAL, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	9.33	48
	AP8LBC-232	080083622108	4 LAMP, 96" LOW BAY INDUSTRIAL, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	18.97	48
Vaportites (APHDVT) 	APHDVT-232	080083623563	2 LAMP, 48" HEAVY DUTY VAPORTITE, NEMA PREMIUM T8 UNV ELECTRONIC BALLAST	Instant Start	Yes	Yes	11.77	35
NOTE: Specification sheets provided via Cooper website. Subject to change without notice.								