

Good

Better

Best

Click on products to learn more



		FPX	Cruze ST	Cruze SB	RLN	Ovation	Accord	SkyRidge	Encounter
APPLICABILITY ¹	Education	★★★	★★★	★★★	★★	★★	★	★	★★
	Office	★★★	★★★	★★	★★★	★★★	★★★	★★★	★★★
	Healthcare	★★	★★	★★★	★★	★	★★	★★	★★★
	Retail	★★★	★★★	★★	★★	★★★	★★	★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4, Metric
	lm/W (Max)	130	157	157	139	109	127	150	141
	Lumens (Max)	6,400	17,000	7,500	8,000	5,000	7,300	6,400	7,400
	Life (@60K)	L87	L90	L84	L93	L89	L89	L92	L92
	Lens	Frost, Smooth	Round or Square, Frost - Ribbed or Smooth, Perf Inlays	Round, Frost - Ribbed or Smooth	Frosted Acrylic	Metal Perforated	Frosted Acrylic	Acrylic (WaveStream)	Acrylic (WaveStream)
	Service from Below	No	Yes	Yes	Yes	No	Yes	No	No
	Emergency	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80+ / 90	80+ / 90	80+ / 90	80+	80+	80+	80+ / 90
	Sensor Location	Integrated	Integrated	Integrated	Integrated	Tile Mount	Integrated	Integrated	Integrated
	DLC	Premium	Standard / Premium	Premium	Premium	Standard	Premium	Premium	Premium
	Air Venting	None	None	None	None	Yes	Yes	Yes	Yes
VividTune™	No	Tunable White	Tunable White	Tunable White	No	No	No	Tunable White	
INTEGRATED CONTROLS	WaveLinX Lite	✓	✓	✓	✓			✓	✓
	WaveLinX Pro	✓	✓	✓	✓	✓	✓	✓	✓
	DLVP	✓	✓	✓	✓		✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable