

Good

Better

Best

Click on products to learn more



		FPX	Cruze SB	SkyRidge	RLN	Ovation	Accord	Encounter	Perceive	InDepth
APPLICABILITY	Education	★★★	★★★	★	★★	★★	★	★★	★★★	★★★
	Office	★★★	★★	★★★	★★★	★★★	★★★	★★★	★★★	★★★
	Healthcare	★★	★★★	★★	★★	★	★★	★★★	★★★	★★★
	Retail	★★★	★★	★★	★★	★★★	★★	★★	★★	★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x2, 1x4, 2x2, 2x4, Metric	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	lm/W (Max)	130	157	150	139	109	127	141	137	127
	Lumens (Max)	6,400	7,500	6,400	8,000	5,000	7,300	7,400	9,000	8,000
	Life (@60K)	L87	L84	L92	L93	L89	L89	L92	L85	L86
	Lens	Frost, Smooth	Round, Frost - Ribbed or Smooth	Acrylic (WaveStream)	Frosted Acrylic	Metal Perforated	Frosted Acrylic	Acrylic (WaveStream)	Acrylic (Perceive Optics)	1", 2" Cube Regress 1", 2" Cube Drop 2" Single & Double Curve Regress & Drop
	Service from Below	No	Yes	No	Yes	No	Yes	No	Yes	No
	Emergency	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated, Indicator is Remote
	CRI	80+	80+ / 90	80+	80+ / 90	80+	80+	80+ / 90	80+ / 90	80+
	Sensor Location	Integrated	Integrated	Integrated	Integrated	Tile Mount	Integrated	Integrated	Integrated	Tile Mount
	DLC	Premium	Premium	Premium	Premium	Standard	Premium	Premium	Premium	Premium
	Air Venting	None	None	Yes	None	Yes	Yes	Yes	None	No
VividTune™	No	Tunable White	No	Tunable White	No	No	Tunable White	Yes	No	
INTEGRATED CONTROLS	WaveLinx Lite	✓	✓	✓	✓			✓	✓	✓
	WaveLinx Pro	✓	✓	✓	✓	✓	✓	✓	✓	✓
	DLVP	✓	✓	✓	✓		✓	✓	✓	✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable