



Save Money



Save Time



Peace of Mind

The Metalux AP Shoplight is an extruded aluminum integrated LED fixture that comes with a 120V grounded cord and plug. The APSHP replaces 2 or 3-lamp fluorescent shoplights or strips, and is well suited for work benches, counters, work-shops, studios, and storage areas where task lighting is needed. The APSHP includes mounting hardware and on/off pull chain for easy installation and operation.



APSHP LED Utility Shoplight

Metalux



Feature		Benefit	Result
Performance	Uniform illumination	Safe work area	✓
	50 K rated life-hours	Long life	💰
	5-year limited warranty	Guaranteed quality	✓
Construction	Long life LED source	No costly lamp replacements	💰
	5 foot cord & plug	Easy to transport from project to project	🕒
	Extruded aluminum housing	Rugged long life fixture	✓

Catalog Number	UPC	CCT (K)	CRI (Min.)	Delivered lumens	Watts (W)	Efficacy (lm/W)	Controls	Input current (A)	
								120V	277V
4APSH4040R	080083834594	4000	80	4300	40	110	Non-Dimming	.33	

		APSHP	Competitor A	Competitor B	Competitor C	Competitor D
Performance	Lumens 1000/FT	✓	4 ft. only	625	✓	
	Efficacy up to 110 lm/W (MAX)	✓				
	L70 Lumen Maintenance (50,000 HRS)	✓	✓	✓	✓	✓
Electrical	0°F - 40°F Operating Temp.	✓	✓	✓	✓	✓
	120V Cord and Plug	✓	✓	✓	✓	✓
	Suspended Mount	✓	✓	✓	✓	✓
Construction	On/Off Pull Chain	✓		✓	✓	✓
	Extruded Housing and Lens	✓	✓			
Compliance	UL/cUL	✓	CSA	✓	✓	ETL
	Warranty	5 Year	1 Year	5 Year	5 Year	5 Year