

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO HOME™

Standalone Motion Sensor

Battery-powered Bluetooth wireless motion-sensing controller for HALO Home Smart Devices

Typical Applications

Residential

- Interactive Menu
- Order Information page 2
 - Product Warranty

Product Certification




Product Features



Top Product Features

- Wireless motion and daylight sensor (Battery included - CR123A)
- Install on- or in-wall anywhere (bracket and hardware included)
- Easily trigger HALO Home devices through secure Bluetooth network with the free app
- 110° field of view
- 16-ft motion detection range
- Indoor use only
- 1-year estimated battery life

Dimensional and Mounting Details



Order Information

ORDER NUMBER: HIWMSB1BLE40AWH

Device	Power Source	Generation	Protocol	Finish
HIWMS = HALO Home In-Wall or Surface Mount Motion Sensor	B = Battery Powered	1 = 1st Generation	BLE40A = Bluetooth Mesh wireless control, 4.0	WH = Matte white

Product Specifications

Wireless System

- For use with the Halo Home mobile app
- Bluetooth low energy (BLE) mesh enables wireless commands to be repeated by each HALO Home device in an account extending the range and strength of the system's network.
- Setup Groups, Scenes and Schedules to automate lighting with the HALO Home mobile app

Wireless Range

- Wireless range of up to 100 feet line-of-sight between HALO Home products.
- Up to 30-feet from Smartphone/tablet to closest product

Wireless Pairing

- See HALO Home Quick Start Guide for wireless setup, guidance and troubleshooting: BringHaloHome.com

Installation

- SURFACE MOUNT: Wall mounting bracket, screws, anchors along with adhesive tape are included for mounting the sensor on-wall, in a corner or ceiling.
- FLUSH MOUNT: The included low-voltage junction box can be used to install the dimmer into an existing junction box or installed directly into a wall (wall plate not included)
- Install indoors only

Detection Range

- 16-feet motion detection range
- 110-degree field of view

Compliance

- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits

Warranty

- Five-year limited warranty, visit website for details: www.cooperlighting.com