

Cooper Poles - Direct Burial Steel

SSS, RSS, & RTS

Cooper Poles

RTS - - - - -



RSS - - - - -



SSS - - - - -



ROUND TAPERED

8'-45' Mounting Height
5.2" to 12" base OD shafts
11ga & 7ga

ROUND STRAIGHT

5'-35' Mounting Height
3" to 6-5/8" OD shafts
11ga, 7ga, 3ga, & 2ga

SQUARE STRAIGHT

5'-39' Mounting Height
4" to 6" SQ shafts
11ga, 7ga, & 3ga



SUPERIOR POLE PERFORMANCE,
FROM THE GROUND UP

Rated performances up to 180MPH per the latest AASHTO & Florida Building standards



RTS, RSS, AND SSS INCLUDE:

Metal Handhole Assembly
with Hardware



Anti-Rotation device,
grounding provision, and pole
top cap included (not shown)

THE POSSIBILITIES ARE LIMITLESS WITH OUR REFRESHED POLE OFFERING

Standard Features:

- Metal Handhole Cover
- Grounding Provision
- Anti-Rotation Device
- Pole top cap

Options Include:

- GFCI Outlet
- Welded Couplings
- Extra Handholes
- Interior Coatings
- Galvanized Pre-finish
- and Many More

Mounting Types:

- Drill Patterns
- Tenons
- Simplex Fitting