


LUMARK^{AP}

XAS180



XAS300



Selectability
Switches

selectable
CCT colors

selectable
lumens

SELECTABLE
OPTICS

MARKETPRO[™]
STOCK PROGRAM

XAS - ALL SELECTABLE AREA SITE

72 configurations in 1 fixture

STOCK CATALOG NUMBERS:

XAS180-SFPM-BZ = 180W, Slipfitter & Pole Mount Arm, 120-347V, PC, Bronze

XAS300-SFPM-BZ = 300W, Slipfitter & Pole Mount Arm, 120-347V, PC, Bronze

XAS180-SFPM-BK = 180W, Slipfitter & Pole Mount Arm, 120-347V, PC, Black

XAS300-SFPM-BK = 300W, Slipfitter & Pole Mount Arm, 120-347V, PC, Black

FEATURES

- 2 housing sizes (180W & 300W) with 4 selectable lumen levels
- 3 Color Selectable CCT – 3000K/4000K/5000
- 3 Field Selectable distribution – T3, T4, T5; no lens change is required
- 2 color options (bronze and black)
- 2 mounts included (Pole mount and adjustable slipfitter mounting arm included with fixture)
- 3 pin Twist-lock NEMA photocontrol for dusk-to-dawn operation included
- Additional accessories: House side shields, other mounts (wall mount, yoke mount, adjustable pole mount)

