

4-INCH INCANDESCENT NEW CONSTRUCTION ICAT




H99ICAT

FEATURES

- Got Nail!™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- Slide-N-Side™ wire traps
- Quick Connect wiring connectors included in junction box
- AIR-TITE™
- Thermally protected
- Die-formed housing and plaster frame
- Housing may be removed from plaster frame for junction box access

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Wet Location, UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, UL/cUL Listed for Insulation Contact, AIR-TITE™ Certified ASTM E283



ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY^A

SAMPLE NUMBER: H99ICAT - 993W

Housing	Trims	Accessories
H99ICAT =4" Aperture, Shallow Ceiling, IC AIR-TITE™, 120V Line Voltage	Adjustables 996 Adjustable Eyeball - 15° Tilt, 50W PAR20, OD: 5-1/16" [129mm] 996P=White Trim with White Eyeball 996SN=Satin Nickel Trim with Satin Nickel Eyeball 996TBZ=Tuscan Bronze Trim with Tuscan Bronze Eyeball 998 Adjustable Eyeball - 30° Tilt, 40W R16, OD: 5-1/16" [129mm] 998P=White Trim with White Eyeball 998PB=Polished Brass Trim with Polished Brass Eyeball 998SN=Satin Nickel Trim with Satin Nickel Eyeball 998TBZ=Tuscan Bronze Trim with Tuscan Bronze Eyeball Baffles 953 Metal Baffle, 30W R20, 35W PAR20, With H1999 Socket Extender 50W PAR20, OD: 5-1/16" [129mm] 953P=White Trim with Black Baffle 953SN=Satin Nickel Trim with Satin Nickel Baffle 953TBZ=Tuscan Bronze Trim with Tuscan Bronze Baffle 953W=White Trim with White Baffle 993 Coilex® Baffle, 30W R20, 35W PAR20, With H1999 Socket Extender 50W PAR20, 50W R20, OD: 5-1/16" [129mm] 993P=White Trim with Black Baffle 993PB=Polished Brass Trim with Black Baffle 993SN=Satin Nickel Trim with Black Baffle 993TBZ=Tuscan Bronze Trim with Black Baffle 993W=White Trim with White Baffle ERT413 Metal Baffle, 40W A19, 50W R20 (ERT413WHT only), 45W R20, 50W PAR 20, OD: 5-1/16" [129mm] ERT413=High Gloss Appliance White Trim Ring with Black Baffle ERT413WHT=High Gloss Appliance White Trim Ring with White Baffle Decorative 945 Metropolitan Ice Lite, 30W R20, OD: 5-1/16" [129mm] 945=Frosted Glass 945BLUE=Frosted Blue Glass 946 Metropolitan Deco, 30W R20, OD: 5-5/8" [143mm] 946BC=Black Chrome Accent with Translucent Rings 946PB=Polished Brass Accent with Translucent Rings Reflectors 999 Reflector, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm] 999H=White Trim with Haze Reflector 999MB=White Trim with Specular Black Reflector 999P=White Trim with Specular Clear Reflector 999RG=White Trim with Residential Gold Reflector 999SN=Satin Nickel Trim with Satin Nickel Reflector 999TBZ=Tuscan Bronze Trim with Tuscan Bronze Reflector 999W=White Trim with White Reflector Showerlight 952 Frosted Dome Lens Showerlight, 30W R20, 35W PAR20, With H1999 Socket Extender 50W PAR20, OD: 5-1/16" [129mm] 952PS=White Trim Ring, Frost Dome Glass Lens Showerlight 955 Showerlight, 30W R20, 35W PAR20, OD: 5-1/16" [129mm] 955PS=White Trim Ring, Prismatic Glass Lens Showerlight	Socket Extender H1999=Socket Extender, for Use with Select Trims and Housings, Extends Lamp 1" (25mm)

NOTES: ^A Not to be used in direct contact with spray foam insulation. ^Δ UL/cUL Listed for Wet Location with select trims.


Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

FEATURES

- Quick Connect wiring connectors included in junction box
- AIR-TITE™
- Thermally protected
- Die-formed housing
- Remodel springs accommodate 1/2" and 5/8" ceiling material
- NM cable pryouts and conduit knockouts in junction box

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Wet Location, UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, IP Rated, AIR-TITE™ Certified ASTM E283



H99RTAT

ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY^A

SAMPLE NUMBER: H99RTAT - 993W

Housing	Trims
H99RTAT=4" Aperture, Shallow Ceiling, Remodel, Non-IC AIR-TITE™, 120V Line Voltage	Adjustables 998 Adjustable Eyeball - 30° Tilt, 40W R16, 60W PAR16, OD: 5-1/16" [129mm] 998P =White Trim with White Eyeball 998PB =Polished Brass Trim with Polished Brass Eyeball 998SN =Satin Nickel Trim with Satin Nickel Eyeball 998TBZ =Tuscan Bronze Trim with Tuscan Bronze Eyeball
	Baffles 953 Metal Baffle, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm] 953P =White Trim with Black Baffle 953SN =Satin Nickel Trim with Satin Nickel Baffle 953TBZ =Tuscan Bronze Trim with Tuscan Bronze Baffle 953W =White Trim with White Baffle
	990 Pinhole Trim, 40W A19, 40W R16, 50W PAR20, 50W R20, OD: 5-1/16" [129mm] 990P =White Pinhole Trim 990SN =Satin Nickel Pinhole Trim 990TBZ =Tuscan Bronze Pinhole Trim
	993 Coilex® Baffle, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm] 993P =White Trim with Black Baffle 993PB =Polished Brass Trim with Black Baffle 993SN =Satin Nickel Trim with Black Baffle 993TBZ =Tuscan Bronze Trim with Black Baffle 993W =White Trim with White Baffle
	ERT413 Metal Baffle, 40W A19, 50W R20 (ERT413WHT only), 50W PAR 20, OD: 5-1/16" [129mm] ERT413 =High Gloss Appliance White Trim Ring with Black Baffle ERT413WHT =High Gloss Appliance White Trim Ring with White Baffle
	Decorative 945 Metropolitan Ice Lite, 50W PAR20, 50W R20, OD: 5-1/16" [129mm] 945 =Frosted Glass 945BLUE =Frosted Blue Glass
	946 Metropolitan Deco, 50W PAR20, 50W R20, OD: 5-5/8" [143mm] 946BC =Black Chrome Accent with Translucent Rings 946PB =Polished Brass Accent with Translucent Rings
	Reflectors 999 Reflector, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm] 999H =White Trim with Haze Reflector 999MB =White Trim with Specular Black Reflector 999P =White Trim with Specular Clear Reflector 999RG =White Trim with Residential Gold Reflector 999SN =Satin Nickel Trim with Satin Nickel Reflector 999TBZ =Tuscan Bronze Trim with Tuscan Bronze Reflector 999W =White Trim with White Reflector
	Showerlight 951 Showerlight, 40W A19, 50W PAR20, 50W R20, OD: 5-1/16" [129mm] 951PS =White Trim with Full Reflector and Prismatic Glass Lens 951SNS =Satin Nickel Trim with Full Reflector and Prismatic Glass Lens 951TBZS =Tuscan Bronze Trim with Full Reflector and Prismatic Glass Lens
	952 Frosted Dome Lens Showerlight, 40W A19, 50W PAR20, 50W R20, OD: 5-1/16" [129mm] 952PS =White Trim Ring, Frost Dome Glass Lens Showerlight
	955 Showerlight, 50W PAR20, OD: 5-1/16" [129mm] 955PS =White Trim Ring, Prismatic Glass Lens Showerlight
	Wall Wash 992 Wall Wash with Baffle, 40W R16, 40W A19, 50W R20, 50W PAR20, OD: 5-1/16" [129mm] 992P =White Trim and Eyelid, Black Baffle 992SN =Satin Nickel Trim and Eyelid, Satin Nickel Baffle 992TBZ =Tuscan Bronze Trim and Eyelid, Tuscan Bronze Baffle 992W =White Trim and Eyelid, White Baffle

NOTES: ^A UL/cUL Listed for Wet Location with select trims.

4-INCH INCANDESCENT NEW CONSTRUCTION NON - IC




H99TAT

FEATURES

- Got Nail!™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- Slide-N-Side™ wire traps
- Quick Connect wiring connectors included in junction box
- AIR-TITE™
- Thermally protected
- Die-formed housing and plaster frame
- Housing may be removed from plaster frame for junction box access

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Wet Location, UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, IP Rated, AIR-TITE™ Certified ASTM E283



ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY^A


SAMPLE NUMBER: H99TAT - 993W

Housing	Trims
H99TAT=4" Aperture, Shallow Ceiling, Non-IC AIR-TITE™, 120V Line Voltage	Adjustables
	996 Adjustable Eyeball - 15° Tilt, 50W PAR20, OD: 5-1/16" [129mm]
	996P=White Trim with White Eyeball
	996SN=Satin Nickel Trim with Satin Nickel Eyeball
	996TBZ=Tuscan Bronze Trim with Tuscan Bronze Eyeball
	998 Adjustable Eyeball - 30° Tilt, 40W R16, 60W PAR16, OD: 5-1/16" [129mm]
	998P=White Trim with White Eyeball
	998PB=Polished Brass Trim with Polished Brass Eyeball
	998SN=Satin Nickel Trim with Satin Nickel Eyeball
	998TBZ=Tuscan Bronze Trim with Tuscan Bronze Eyeball
	Baffles
	953 Metal Baffle, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm]
	953P=White Trim with Black Baffle
	953SN=Satin Nickel Trim with Satin Nickel Baffle
	953TBZ=Tuscan Bronze Trim with Tuscan Bronze Baffle
	953W=White Trim with White Baffle
	990 Pinhole Trim, 40W A19, 40W R16, 50W PAR20, 50W R20, OD: 5-1/16" [129mm]
	990P=White Pinhole Trim
	990SN=Satin Nickel Pinhole Trim
	990TBZ=Tuscan Bronze Pinhole Trim
	993 Coilex® Baffle, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm]
	993P=White Trim with Black Baffle
	993PB=Polished Brass Trim with Black Baffle
	993SN=Satin Nickel Trim with Black Baffle
	993TBZ=Tuscan Bronze Trim with Black Baffle
	993W=White Trim with White Baffle
	ERT413 Metal Baffle, 40W A19, 50W R20 (ERT413WHT only), 50W PAR 20, OD: 5-1/16" [129mm]
	ERT413=High Gloss Appliance White Trim Ring with Black Baffle
	ERT413WHT=High Gloss Appliance White Trim Ring with White Baffle
	Decorative
	945 Metropolitan Ice Lite, 50W PAR20, 50W R20, OD: 5-1/16" [129mm]
	945=Frosted Glass
	945BLUE=Frosted Blue Glass
	946 Metropolitan Deco, 50W PAR20, 50W R20, OD: 5-5/8" [143mm]
	946BC=Black Chrome Accent with Translucent Rings
	946PB=Polished Brass Accent with Translucent Rings
	Reflectors
	999 Reflector, 40W R16, 50W R20, 50W PAR20, OD: 5-1/16" [129mm]
	999H=White Trim with Haze Reflector
	999MB=White Trim with Specular Black Reflector
	999P=White Trim with Specular Clear Reflector
	999RG=White Trim with Residential Gold Reflector
	999SN=Satin Nickel Trim with Satin Nickel Reflector
	999TBZ=Tuscan Bronze Trim with Tuscan Bronze Reflector
	999W=White Trim with White Reflector
	Showerlight
	951 Showerlight, 40W A19, 50W PAR20, 50W R20, OD: 5-1/16" [129mm]
	951PS=White Trim with Full Reflector and Prismatic Glass Lens
	951SNS=Satin Nickel Trim with Full Reflector and Prismatic Glass Lens
	951TBZS=Tuscan Bronze Trim with Full Reflector and Prismatic Glass Lens
	952 Frosted Dome Lens Showerlight, 40W A19, 50W PAR20, 50W R20, OD: 5-1/16" [129mm]
	952PS=White Trim Ring, Frost Dome Glass Lens Showerlight
	955 Showerlight, 40W A19, 50W PAR20, 50W R20, OD: 5-1/16" [129mm]
	955PS=White Trim Ring, Prismatic Glass Lens Showerlight
	Wall Wash
	992 Wall Wash with Baffle, 40W R16, 40W A19, 50W R20, OD: 5-1/16" [129mm]
	992P=White Trim and Eyelid, Black Baffle
	992SN=Satin Nickel Trim and Eyelid, Satin Nickel Baffle
	992TBZ=Tuscan Bronze Trim and Eyelid, Tuscan Bronze Baffle
	992W=White Trim and Eyelid, White Baffle

NOTES: ^A UL/cUL Listed for Wet Location with select trims.

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

945 4" Metropolitan Ice Lite





HOUSING / LAMP:

H99ICAT: 30W R20
H99RTAT: 50W PAR20, 50W R20
H99TAT: 50W PAR20, 50W R20

DIMENSIONS: Aperture: 2-1/8" [54mm],
Outside Dimensions: 5-5/16" [135mm]

946 4" Metropolitan Deco




HOUSING / LAMP:

H99ICAT: 30W R20
H99RTAT: 50W PAR20, 50W R20
H99TAT: 50W PAR20, 50W R20

DIMENSIONS: Height: 1-5/8" [41mm],
Outside Diameter: 5-5/8" [143mm]

951 4" Showerlight





HOUSING / LAMP:

H99ICAT: 30W R20, 35W PAR20
H99ICAT: 50W PAR20 with H1999 Socket Extender
H99RTAT: 40W A19, 50W PAR20, 50W R20
H99TAT: 40W A19, 50W PAR20, 50W R20

DIMENSIONS: Height: 4-1/2" [114mm],
Outside Diameter: 5-1/16" [129mm]

ACCESSORIES: H1999 Socket Extender

952 4" Frosted Dome Lens Showerlight





HOUSING / LAMP:

H99ICAT: 30W R20, 35W PAR20
H99ICAT: 50W PAR20 with H1999 Socket Extender
H99RTAT: 40W A19, 50W PAR20, 50W R20
H99TAT: 40W A19, 50W PAR20, 50W R20

DIMENSIONS: Height: 2-5/8" [66mm],
Outside Diameter: 5-1/16" [129mm]

ACCESSORIES: H1999 Socket Extender

953 4" Metal Baffle





HOUSING / LAMP:

H99ICAT: 30W R20, 35W PAR20
H99ICAT: 50W PAR20 with H1999 Socket Extender
H99RTAT: 40W R16, 50W R20, 50W PAR20
H99TAT: 40W R16, 50W R20, 50W PAR20

DIMENSIONS: Height: 2-5/8" [67mm], OD: 5-1/16" [129mm]

ACCESSORIES: H1999 Socket Extender

955 4" Showerlight




HOUSING / LAMP:

H99ICAT: 30W R20, 35W PAR20
H99RTAT: 40W A19, 50W PAR20, 50W R20
H99TAT: 40W A19, 50W PAR20, 50W R20

DIMENSIONS: Height: 2-5/8" [67mm], OD: 5-1/16" [129mm]

990 4" Pinhole Trim



HOUSING / LAMP:


H99RTAT: 40W A19, 40W R16, 50W PAR20, 50W R20
H99TAT: 40W A19, 40W R16, 50W PAR20, 50W R20

DIMENSIONS: Height: 1-3/4" [44mm], OD: 5-1/16" [129mm]

992 4" Wall Wash with Baffle



- 992W White Trim and Eyelid, White Baffle
- 992P White Trim and Eyelid, Black Baffle
- 992SN Satin Nickel Trim and Eyelid, Satin Nickel Baffle
- 992TBZ Tuscan Bronze Trim and Eyelid, Tuscan Bronze Baffle



HOUSING / LAMP:


H99RTAT: 40W R16, 40W A19, 50W R20, 50W PAR20
H99TAT: 40W R16, 40W A19, 50W R20

DIMENSIONS: Height: 1-1/4" [32mm], OD: 5-1/16" [129mm]

993 4" Coilex® Baffle



- 993P White Trim with Black Baffle
- 993W White Trim with White Baffle
- 993SN Satin Nickel Trim with Black Baffle
- 993TBZ Tuscan Bronze Trim with Black Baffle
- 993PB Polished Brass Trim with Black Baffle



HOUSING / LAMP:

H99ICAT: 30W R20, 35W PAR20
H99ICAT: 50W PAR20, 50W R20 with H1999 Socket Extender
H99TAT: 40W R16, 50W R20, 50W PAR20
H99RTAT: 40W R16, 50W R20, 50W PAR20


DIMENSIONS: Height: 2-1/2" [63mm], OD: 5-1/16" [129mm]

ACCESSORIES: H1999 Socket Extender

996 4" Adjustable Eyeball 15° Tilt



- 996P White Trim with White Eyeball
- 996SN Satin Nickel Trim with Satin Nickel Eyeball
- 996TBZ Tuscan Bronze Trim with Tuscan Bronze Eyeball



HOUSING / LAMP:


H99ICAT: 50W PAR20
H99TAT: 50W PAR20

DIMENSIONS: Aperture: 3-11/16 [94mm], Height: 3-7/16" [88mm], OD: 5-1/16" [129mm]

998 4" Adjustable Eyeball 30° Tilt



- 998P White Trim with White Eyeball
- 998SN Satin Nickel Trim with Satin Nickel Eyeball
- 998PB Polished Brass Trim with Polished Brass Eyeball
- 998TBZ Tuscan Bronze Trim with Tuscan Bronze Eyeball



HOUSING / LAMP:


H99ICAT: 40W R16
H99RTAT: 40W R16, 60W PAR16
H99TAT: 40W R16, 60W PAR16

DIMENSIONS: Aperture: 2-3/16" [56mm], Height: 3-1/4" [83mm], OD: 5-1/16" [129mm]

999 4" Reflector



- 999W White Trim with White Reflector
- 999MB White Trim with Specular Black Reflector
- 999P White Trim with Specular Clear Reflector
- 999H White Trim with Haze Reflector
- 999RG White Trim with Residential Gold Reflector
- 999SN Satin Nickel Trim with Satin Nickel Reflector
- 999TBZ Tuscan Bronze Trim with Tuscan Bronze Reflector



HOUSING / LAMP:


H99ICAT: 40W R16, 50W R20, 50W PAR20
H99RTAT: 40W R16, 50W R20, 50W PAR20
H99TAT: 40W R16, 50W R20, 50W PAR20

DIMENSIONS: Height: 2-5/8" [67mm], OD: 5-1/16" [129mm]

ERT413 Metal Baffle



- ERT413WHT High Gloss Appliance White Trim Ring with White Baffle
- ERT413 High Gloss Appliance White Trim Ring with Black Baffle



HOUSING / LAMP:

H99ICAT: 40W A19, 50W R20 (ERT413WHT only), 45W R20, 50W PAR 20
H99RTAT: 40W A19, 50W R20 (ERT413WHT only), 50W PAR 20
H99TAT: 40W A19, 50W R20 (ERT413WHT only), 50W PAR 20

DIMENSIONS: Height: 4-1/2" [114mm], OD: 5-1/6" [129mm]



H1999

Description

SOCKET EXTENDER

For use with selected trims and housings. Extends lamp 1" (25mm).