

DESCRIPTION

The Classic pendants family from Halo include 5 different styles with glass or metal shades. Clean simple lines blend with a variety of interior spaces and provide effective task or accent lighting. The shapes include soft cones, cylinders and tall cones of cased glass in white, amber or blue. These line voltage Cylinder Pendants use 60W A15 and G16.5 medium base lamps.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Flexible Track

Die Cast housing. Attaches electrically and mechanically anywhere along Flexible track.

B ... Electrical Quick Lock Adapter - Power-Trac

Polycarbonate housing. Attaches electrically and mechanically anywhere along track Halo Power Trac and Lazer Track.

C ... Canopy - Surface Mount

Aluminum canopy. Attaches to standard junction box.

D ... Shade

White, Amber or Blue cased glass. The white inner glass casing provides an even diffusion of light throughout the shade.

E ... Finial



Machined brass.

F ... Cord

Field adjustable 6' long 18AWG clear-jacketed cord.

Labels

UL/c-UL Listed for use with Halo Flexible Track, Halo Power-Trac, and Lazer.



LF1CYL
L1CYL
H1CYL

**Classic Line Voltage
Cylinder Pendant**
60W A15/G16.5

**Architectural Flexible Track
Power-Trac
Surface**

Track L1=Halo Power-Trac LF1=Flexible Track H1=Surface Mount	CYL Style CYL=Cylinder	Finial Finish AH=Aluminum Haze BRZ=Bronze (except LF1)	Lamp Type (not included) 19=A15 ,G16.5	Adapter/Canopy Finish Blank=Same as Finial (LF1 only Available in AH Finish) BRZ=Bronze P=White MB=Black	Shade Colors AM=Amber BL=Blue WH=White
--	--	---	---	---	--