

**Description**

The The H5ICATNB recessed housing is designed for residential and light commercial applications. H5ICATNB features full-frame robust construction, feed through listing, Got Nail! bar hangers, and may support the use of higher wattage lamps. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. The H5ICATNB is designed for use in insulated ceilings and may be in direct contact with insulation\*.

The H5ICATNB can save installation time. It is designed without a socket plate, for use with socket supporting trims only. With these trims there is no need to spend time removing the socket plate, and the fixed lamp position of socket supporting trims saves on lamp adjustment time too. May be retrofit with compatible Halo LED lighting systems.

<b>Catalog #</b>		<b>Type</b>
<b>Project</b>		
<b>Comments</b>		<b>Date</b>
<b>Prepared by</b>		

**Specification Features**

**Housing**

- Die-stamped aluminum
- Sealed and gasketed for Air-Tite™ ready installation
- Designed for insulated ceilings in direct contact with insulation\* (May also be installed in non-insulated ceilings)

**Plaster Frame**

- Galvanized steel construction
- The housing can be removed from plaster frame to provide access to the junction box
- Plaster frame features include:
  - Patented regressed locking screw positioned for securing hanger bars from below the ceiling
  - Cutouts for easily crimping hanger bars in position
  - Halo name embossed on plaster frame
  - Pre-installed Air-Tite ready ceiling contact gasket

**Got Nail!™ Bar Hanger Bracket**

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered lumber and laminated beams
- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary
- Automatic leveling flange aligns the housing and lets you hold the housing in place with one hand while driving nails
- Five additional mounting points
- Mounting point on top for hanger wire connection
- Integral T-bar clips snaps onto T-bars - no additional clips required

**q-Channel bars with Pass-N-Thru™**

- q-Channel bars feature an unique inverted “q” interlocking channel for rigidity and stability
- Pass-N-Thru™ feature allows bars to cross-over for tool-less shortening in tight spaces less than 12” without removing from the plaster frame. Push bars together and flex at score hole break points
- Housing can be positioned at any point within 24” joist span
- Bar hangers may be repositioned 90° on the frame

**Slide-N-Side™ Junction Box**

Junction box features include:

- Slide-N-Side™ connectors allow non-metallic sheathed cable for both U.S. and Canada to be installed without tools and without removing knockouts
- Allows wiring connections to be made outside the junction box
- Simply insert the cable directly into the trap after connections are made
- accommodates the following standard non-metallic sheathed cable types: (US) #14/2 , #14/3, #12/2, #12/3 (Canada) #14/2, #14/3, #12/2
- Positioned to accommodate straight conduit runs
- Seven 1/2” trade size conduit knockouts with true pry-out slots
- cULus Listed 26 in3 box volume
- Listed for through branch (8) No. 12 AWG branch circuit 90° C conductors through the box

**Quick Connect™**

- Three 4-port push-in “Quick Connect” wire nuts included in junction box

- Speed installation and increase reliability
- No additional wire nuts required
- Simply strip and insert supply wires

**Socket:**

- Porcelain socket with nickel plated brass screw shell
- Snap-in springs secure socket to socket plate, and may be detached when using socket supporting trims
- Overspray protector included

**Thermal Protector:**

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation


**Trims:**

Halo Fit-All concept offers multiple trim options in a variety of design styles, and functional beam distributions to control beam angle and lumen delivery in accommodating various lamp types including Halogen, CFL and LED

**Compliance**

- cULus Listed 1598 luminaire
- cULus Listed damp location
- cULus Listed for wet location, covered ceiling, with select trims
- cULus Listed for feed through
- cULus Listed for direct contact with insulation and combustible material\*
- Air-Tite code compliant. Certified under ASTM E283; not exceeding 2.0 cfm (0.944 L/s) air leakage rate tested at a 1.57 psf (75 Pa) pressure differential
- RoHS compliant
- Options to meet Trade Agreements Act requirements

\*Not to be used in direct contact with spray foam insulation (Consult NEMA LSD57-2013)



**H5ICATNB**


**5” IC, New Construction Housing, No Socket Bracket, 120V**

**FOR USE IN INSULATED CEILINGS**

**FOR DIRECT CONTACT WITH INSULATION\***



**Dimensions**



**Special Features**

- Got Nail!™ bar hangers
- q-Channel bars with Pass-N-Thru™
- Slide-N-Side™ junction box
- Quick Connect™ push wire nuts
- Air-Tite™ code compliant

**Ordering Information**

Sample Number: H5ICATNB 5110WB  
 Order housing, trim and lamp (by others) separately for a complete luminaire.



























**Domestic Preferences<sup>(1)</sup>**

[Blank] = Standard  
 TAA = Trade Agreements Act

**Housing**

H5ICATNB = 5" IC, Air-Tite, New Construction Housing, No Socket Bracket, 120V

**Trims**

Reflectors	Adjustable - Eyeballs & Gimbals	
 <p><b>5020 PAR Reflector</b>                      OD: 6-3/8" [162mm]                      5020P=White Reflector, White Trim                      5020H=Haze Reflector, White Trim                      5020SC=Clear Specular Reflector, White Trim                      5020BL=Black Specular Reflector, White Trim                      5020SN=Satin Nickel Reflector, Satin Nickel Trim                      5020TBZ=Tuscan Bronze Reflector, Tuscan Bronze Trim</p>	 <p><b>5060 Adjustable Gimbal 20° Tilt, Self-flange</b>                      OD: 6-3/8" [162mm]                      5060P=White Gimbal, White Trim</p>	 <p><b>5162 Drop Opal Plastic Lens, Self-flange</b>                      OD: 6-5/8" [168mm]                      5162WH=Drop Opal Plastic Lens with Reflector, White Plastic Self-flange</p>
 <p><b>5021 Full Reflector</b>                      OD: 6-3/8" [162mm]                      5021H=Haze Reflector, White Trim                      5021SC=Clear Specular Reflector, White Trim                      5021SN=Satin Nickel Reflector, Satin Nickel Trim                      5021TBZ=Tuscan Bronze Reflector, Tuscan Bronze Trim</p>	 <p><b>5070 Adjustable Eyeball 30° Tilt, Self-flange</b>                      OD: 6-3/8" [162mm]                      5070P=White Eyeball, White Trim                      5070SN=Satin Nickel Eyeball, Satin Nickel Trim                      5070TBZ=Tuscan Bronze Eyeball, Tuscan Bronze Trim</p>	 <p><b>5230 Squirrel Frost Glass Lens, Metal Trim, Self-flange - Showerlight</b>                      OD: 6-7/8" [174mm]                      5230AH=Frost Glass Lens, Aluminum Haze Squirrel Trim                      5230PN=Frost Glass Lens, Polished Nickel Squirrel Trim                      5230SN=Frost Glass Lens, Satin Nickel Squirrel Trim                      5230TBZ=Frost Glass Lens, Tuscan Bronze Squirrel Trim</p>
 <p><b>5120 Full Cone Reflector, Self-flange</b>                      OD: 6-5/8" [168mm]                      5120WH=White Reflector, White Self-flange                      5120SN=Satin Nickel Reflector, Satin Nickel Self-flange                      5120TBZ=Tuscan Bronze Reflector, Tuscan Bronze Self-flange</p>	 <p><b>5071 Adjustable Eyeball 30° Tilt, Self-flange</b>                      OD: 6-1/2" [165mm]                      5071P=White Eyeball, White Trim</p>	 <p><b>5255 Soft Square, Frost Curve Glass Lens, Self-flange - Showerlight</b>                      OD: 7-1/4" [183mm]                      5255WH=Frost Curve Glass Lens with Reflector, White Plastic Self-flange                      5255SN=Frost Curve Glass Lens with Reflector, Satin Nickel Plastic Self-flange                      5255TBZ=Frost Curve Glass Lens with Reflector, Tuscan Bronze Plastic Self-flange</p>
 <p><b>5121 Shallow Full Cone Reflector, Self-flange</b>                      OD: 6-5/8" [168mm]                      5121WH=White Reflector, White Oversized Self-flange</p>	 <p><b>5130 Eyeball 35° Tilt, Self-flange</b>                      OD: 6-5/8" [168mm]                      5130WH=White Eyeball, White Trim</p>	 <p><b>5145 Open Wet Location, Shallow Reflector, Self-flange - Showerlight*</b>                      OD: 6-5/8" [168mm]                      5145WH=White Self-flanged                      5145SN=Satin Nickel Self-Flanged                      5145TBZ=Tuscan Bronze Self-Flanged</p>
<p><b>Baffles</b></p>  <p><b>5001 PAR Metal Baffle Splay</b>                      OD: 6-3/8" [156mm]                      5001P=White Baffle, White Trim                      5001MB=Black Baffle, White Trim                      5001SN=Satin Nickel Baffle, Satin Nickel Trim                      5001TBZ=Tuscan Bronze Baffle, Tuscan Bronze Trim</p>	 <p><b>5135 Eyeball 35° Tilt, Self-flange</b>                      OD: 6-5/8" [168mm]                      5135WH=White Eyeball, White Trim, Self-flanged</p>	 <p><b>5146 Open Wet Location Full Reflector, Self-flange - Showerlight*</b>                      OD: 6-5/8" [168mm]                      5146WH=White Self-flanged                      5146SN=Satin Nickel Self-Flanged                      5146TBZ=Tuscan Bronze Self-Flanged</p>
 <p><b>5014 Shallow Metal Baffle, Self-flange</b>                      OD: 6-5/8" [168mm]                      5014P=White Baffle, White Trim                      5014MB=Black Baffle, White Trim</p>	 <p><b>5165 Gimbal 35° Tilt, Self-flange</b>                      OD: 6-5/8" [168mm]                      5165WH=White Gimbal, White Trim                      5165BK=Black Gimbal, Black Trim                      5165SN=Satin Nickel Gimbal, Satin Nickel Trim                      5165TBZ=Tuscan Bronze Gimbal, Tuscan Bronze Trim</p>	<p><b>Open, Splay &amp; Wall Wash</b></p>  <p><b>5000 PAR Metal Splay, Self-flange</b>                      OD: 6-3/8" [162mm]                      5000P=White Splay, White Trim                      5000SN=Satin Nickel Splay, Satin Nickel Trim                      5000TBZ=Tuscan Bronze Splay, Tuscan Bronze Trim</p>
 <p><b>5016 Coilex® Baffle with Reflector</b>                      OD: 6-3/8" [162mm]                      5016W=White Baffle, White Trim                      5016P=Black Baffle, White Trim</p>	 <p><b>5222 Regressed Angle Cut Adjustable Gimbal 30° Tilt, Self-flange</b>                      OD: 6-5/8" [168mm]                      5222WB=White Baffle and Gimbal, White Trim                      5222BB=Black Baffle and Gimbal, White Trim                      5222SC=Specular Clear Reflector and Gimbal, White Trim                      5222H=Haze Reflector and Gimbal, White Trim</p>	 <p><b>5176 Open, Self-flange</b>                      OD: 6-5/8" [168mm]                      5176WH=White Self-flange                      5176SN=Satin Nickel Self-flange                      5176TBZ=Tuscan Bronze Self-flange</p>
 <p><b>5125 Full Cone Baffle, Self-flanged</b>                      OD: 6-5/8" [168mm]                      5125WB=White Baffle, White Self-flange                      5125BB=White Baffle, Black Self-flange                      5125BKBB=Black Baffle, Black Self-flange</p>	 <p><b>5150 Low Profile, Frosted Dome Glass Lens, Self-flange - Showerlight</b>                      OD: 6-5/8" [168mm]                      5150WH=Frost Dome Glass Lens with Reflector, White Plastic Self-flange                      5150SN=Frost Dome Glass Lens with Reflector, Satin Nickel Plastic Self-flange                      5150TBZ=Frost Dome Glass Lens with Reflector, Tuscan Bronze Plastic Self-flange</p>	 <p><b>5186 Open Splay, Self-flange</b>                      OD: 6-5/8" [168mm]                      5186WH=White Self-flange                      5186SN=Satin Nickel Self-flange                      5186TBZ=Tuscan Bronze Self-flange</p>
 <p><b>5126 Shallow Full Cone Baffle, Self-flanged</b>                      OD: 6-5/8" [168mm]                      5126WB=White Baffle &amp; Self-flanged                      5126BB=Black Baffle &amp; White Self-flanged</p>	<p><b>Lenses &amp; Wet Location Showerlights</b></p>  <p><b>5051 Frosted Glass Lens - Showerlight</b>                      OD: 6-7/16" [164mm]                      5051PS=Frosted Glass Lens, White Trim</p>	<p><b>Accessory</b></p> <p><b>GA-ATH5-6PK</b>=T6-Pack AIR-TITE Ceiling aperture gaskets. Seals gaps around ceiling cut out.</p>

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

\*Outdoor rated lamp only (purchase separately)