

Metalux

Selectable Lumen and CCT Products



Field selectable technology empowers you to take control. Go selectable to choose your way, every time. Adjust color temperatures (CCT) and lumen outputs with the flip of a switch!



Flexibility at Your Fingertips

Multiple Light Choices, One Fixture.



SELECTABLE COLORS (CCT)

Choose from a wide range of color temperatures to set the ideal lighting scene.



SELECTABLE LUMENS

Select between the preset lumen outputs to create your optimal lighting experience.

Why Selectable?

Distributor Benefits

- Simplify stock needed
- Less shelf space required
- Working capital reductions
- Product availability



Contractor Benefits

- Install less fixture types per job to save time and money
- Less back and forth with the customer increasing service efficiency
- Eliminate call backs or make easy changes if the customer requires. No Electrician required to change the color or lumens - conveniently located on top.



Click for page

MMS

Pg 2

SFS

Pg 3

ARS

Pg 4

CZS

Pg 5

CZSB-S

Pg 6

CGTS

Pg 7

FPS

Pg 8

SRC-S

Pg 9

GRSCT3

Pg 10

SNX

Pg 11

Click for page

SLSTP

Pg 12

ST

Pg 13

EZBY

Pg 14

SPHB

Pg 15

UHBS2

Pg 16

APVTS

Pg 17

VT3S

Pg 18

AWS

Pg 19

NWS

Pg 20

RBG


Pg 21

Metalux

MMS Multi-mount Selectable Panel



The MMS Multi-Mount Selectable Panel is a versatile selectable panel that can mount directly to the ceiling or wall without the cost and labor of a surface mount kit. In addition, it can be recessed or suspended (with kit) to make it the "go to" panel for any mounting requirement. The MMS comes standard with (5) selectable CCT in the more decorative smaller form factors and (3) selectable CCT in the more commercial larger form factors- all in standard 90 CRI superior color quality.



Product Benefits

- Multi-Mount ability reduces labor time and cost for surface mount applications by removing the need for additional surface mount kit
- Versatile mounting allows for surface, recessed, surface, or wall
- Selectable Color Temperatures in 90 CRI Standard: 2x2/1x4/2x4: 3500K, 4000K, 5000K
1x1/1x2/6"x4: 2700K, 3000K, 3500K, 4000K, 5000K
- Selectable Lumens- Low, Medium, High settings
- 0-10V continuous dimming to 5% increases energy savings

Certifications and Ratings



Applications


Office • Education • Healthcare • Retail

SFS

Surround Selectable Architectural Drop Lens LED

The Surround is a modern illuminated fixture that elevates the look of any commercial space. The Surround comes standard with (4) selectable CCT's in 80+CRI and is offered with (3) selectable lumen packages in low, medium, and high. The innovative 1.5" wide ribbed lens design delivers a smooth fully luminous aesthetic matching light distribution from standard troffers and panels.

Click on product to learn more



Product Benefits

- Surround offers a modern contemporary design at a great value
- Versatile mounting allows for mounting in existing T-grid or surface/suspension with additional kit
- (5) Form factors to cover troffer and linear ceilings: 1x2, 2x2, 2x4, 1x4, and 1x8
- 4 CCT Selectable Color in 80 CRI: 3000K, 3500K, 4000K, 5000K
- Selectable Lumens- Low, Medium, High settings from 1,500-8,500
- 0-10V continuous dimming to 5% increases energy savings



Applications

Office • Education • Healthcare • Retail

Certifications and Ratings



Metalux

ARS Achieva Selectable LED Center Basket



The Achieva™ Recessed Selectable center basket offers selectable lumen output and color temperature with a simple, easy to access toggle switch. The ultra slim 1.5" design fits into the shallowest of plenums and offers an upgraded center basket aesthetic. Constructed with Cooper Lighting's latest selectable technology platform, the Achieva delivers unprecedented light level and CCT flexibility, energy savings, slim housing design, and sustainable packaging options.



Product Benefits

- Selectable lumens and CCT for design and stock friendly applications
- Selectable CCT in 3500K, 4000K, 5000K in 80 or 90 CRI
- Selectable lumens in low, medium, and high up to 8,000 lumens with standard and HO selectable options
- Shallow 1.5" housing stays below the T-grid height for shallow plenum designs
- Single Carton or Multi-pack options for less onsite waste

Certifications and Ratings



Applications

Office • Education • Healthcare • Retail

CZS

Cruze ST Selectable LED Troffer

The Cruze™ Selectable troffer offers selectable lumen output and color temperature with a simple, easy to access toggle switch. The latch-less design, matte white paint and multiple lens options deliver architectural appeal and specification rich features. Cruze Selectable is an ideal choice for offices, schools, hospitals, and retail merchandising areas.

Click on product to learn more

**Product Benefits**

- Selectable CCT in 3000K, 3500K, 4000K in >80 CRI
- Selectable lumens in Low, Medium, and High up to 6,500 lumens
- Ideal for replacing 2-4 lamp fluorescent troffers
- 0-10V dimming with 120-277V (UNV) standard
- Suitable for recessed, surface, or suspension mounting
- DLC Compliant and UL Damp rated with a 5 year warranty
- Latch-less design provides clean architectural look and feel

**Applications**

Office • Education • Healthcare • Retail

Certifications and Ratings

Metalux

CZSB-S

Cruze SB Selectable Troffer



The CZSB Selectable offers below the plenum access to the LED, driver and CCT and lumen select switches. Choose from curved or square lens to enhance and refresh your space. Use the CZSB-S in any general-purpose lighting application, providing project and stock flexibility to take orders and deliver quickly. Use the CZSB Selectable in offices, schools, hospital and retail spaces.

Click on product to learn more



Product Benefits

- Selectable CCT in 3000K, 3500K, 4000K in >80 CRI
- Selectable lumens – Low, Medium, and High up to 6,400 lumens
- Door-frame assembly for easy room-side maintenance and install
- Curved and square lens options for an upgraded look and efficacy up to 146 LPW
- Integrated sensor systems for additional energy savings
- DLC Compliant efficacy up to 146 LPW and 5-year warranty

Certifications and Ratings



damp location



Applications

Office • Education • Healthcare • Hospitality • Retail

CGTS

Lumen and CCT Select LED Panel

The contractor go-to selectable panel providing customers an affordable panel that fits in shallow plenums with room to spare. Three selectable lumen levels (high, medium, low) and three selectable color temperatures (3500K, 4000K, 5000K) are available using simple switches on the fixture. Use CGTS for commercial office spaces, schools, healthcare, and retail merchandising areas.

Click on product to learn more



Product Benefits

- 2-1/8" overall fixture height so fits in shallow plenums with room to spare
- Acrylic micro-optics provide uniform illumination from corner to corner
- Back-lit, durable design provides immediate opportunities to replace fluorescent fixtures with an LED solution
- Mounting flexibility for multiple applications with recessed grid, hard ceiling, surface, and suspended options available
- Integral WaveLinx LITE controls option or factory installed 8 Watt emergency LED driver option in stock allows for fast product delivery



Applications

Office • Education • Healthcare • Retail

Certifications and Ratings




Metalux

FPS

Lumen and CCT Select LED Panel



This edge lit selectable panel provides the high performance and aesthetic appeal of a flat panel while also providing the flexibility to adapt to the changing needs of a space, setting, or environment. Two large switches enable three selectable lumen levels (high, medium, low) and three selectable color temperatures (3000K, 3500K, and 4000K). FPS is an excellent lighting solution for commercial office spaces, schools, healthcare and retail merchandising areas.



Click on product to learn more



Product Benefits

- Ultra thin approx. 2 inch fixture height so fits in shallow plenums with room to spare
- Integral clips come standard so faster installation speed
- Edge lit design provides immediate opportunities to replace fluorescent fixtures with an LED solution
- Mounting flexibility for multiple applications with recessed grid, hard ceiling, surface, and suspended options available

Certifications and Ratings



Applications

Office • Education • Healthcare • Retail

SRC-S

SkyRidge Selectable Spec Grade Troffer

The SRC Selectable offers selectable CCT and lumen with a single easy to access toggle switch. The unique design and lightguide technology deliver architectural appeal and specification features. Use the SRC Selectable in offices, schools and retail spaces.

Click on product to learn more



Product Benefits

- Selectable CCT in 3000K, 4000K, 5000K in >80 CRI
- Selectable lumens – Low, Medium, and High up to 6,700 lumens
- Advanced optical control with optimal illumination
- High performance efficacy up to 151 lumens per watt
- Over 60% energy savings when compared to a fluorescent troffers
- DLC Compliant efficacy and 5-year warranty



Applications

Office • Education • Healthcare • Retail

Certifications and Ratings



Metalux

GRSCT3

GRLED Selectable Troffer



The GRLED Selectable offers below the plenum access to the LED, driver and CCT and lumen select switches.. With multiple lens options, GRLED Selectable works in any general-purpose lighting application, providing project and stock flexibility to take orders and deliver quickly. Use the GRLED Selectable in offices, schools, retail and residential spaces.



Click on product to learn more



Product Benefits

- Selectable CCT in 3000K, 3500K, 4000K in >80 CRI
- Selectable lumens – Low, Medium, and High up to 7,000 lumens
- Door-frame lens assembly for easy room-side access
- Easy installation and maintenance
- Replaces up to 4-lamp fluorescent troffers
- 0-10V dimming with 120-277V (UNV) standard
- DLC Compliant with 5-year warranty

Certifications and Ratings



Applications

Office • Education • Healthcare • Retail

SNX

Lumen and CCT Select LED Configurable Strip

A versatile, high-performance selectable linear commercial LED striplight series with breakthrough fixture efficacy, multiple distributions and numerous configurations. The SNX provides application flexibility with selectable lumens and CCT. The SNX is suitable for general area lighting, storage/utility areas, coves, shops, task, high bay and low bay lighting applications.

Click on product to learn more



Product Benefits

- 2', 4' and 8' lengths with single continuous lens for design flexibility
- Flat, round and square lens options for design and application flexibility
- General, narrow and wide distributions options to address various mounting heights and applications
- Integrated sensor available for code compliance and IoT value-added applications



Applications

Warehouse • Manufacturing • Retail

Certifications and Ratings



Metalux

SLSTP

Lumen and CCT Select LED Strip



Commercial grade LED strip that balances performance, aesthetics, and cost. It is available in 2', 4' or 8' lengths with 3500K, 4000K or 5000K selectable CCT options and selectable lumens up to 12,000 lumens of light output. SLSTP is ideal for warehouse, retail, office or retrofit applications making them the ideal choice for stock and design build opportunities.



Click on product to learn more



Product Benefits

- 2', 4' and 8' lengths with single continuous lens (all lengths) for design flexibility
- Easy access selectable switches on the outside of the fixture for simple in field adjustment
- Frosted lens with linear prisms for uniform light distribution and wide area coverage
- UNV and NUV (120-347V) input with 0-10V dimming down to 10%, then off

Certifications and Ratings



damp location



Applications

Warehouse • Retail • Office

ST

CCT Select LED Strip

LED selectable strip that features 0-10V dimming and 3500K, 4000K, and 5000K CCT selectable options. Use the ST to replace fluorescent strip lights for increased energy savings and rebates. The ST is the ideal strip light for commercial, industrial, retail, and residential applications.

Click on product to learn more



Product Benefits

- Tool-less channel cover, integrated LEDs and wireless access from below for simple installation and maintenance
- Surface, chain or toggle mount for new construction or retrofit
- Classic single or double lens tube appearance for one for one replacement of 2 or 4 lamp LFL strips



Applications

Warehouse • Retail • Office

Certifications and Ratings



Metalux

EZBY

Select High Bay



The EZBY is affordable without sacrificing performance, making it the perfect high-output solution for upgrading your lighting today. A versatile high-bay that delivers up to 30,000 lumen and CCT select, the EZBY comes with 6ft cord, mounting ring, IP65 rating and sensor ready port. Use the EZBY for general warehouse, manufacturing or gymnasiums.



Product Benefits

- Selectable lumen up to 30K lumen
- Selectable CCT: 3000K, 4000K, 5000K
- Sensor ready port for quick plug and play install
- 120-347 volt, 0-10V dimming Class A driver
- Polycarbonate lens with IK08 impact rating
- IP65 rated and wet location cULus listed
- Mounting Ring included

Certifications and Ratings



Applications

Light Commercial • Large Open Areas • Warehouse • Barns • Residential

SPHB

Lumen Select LED High Bay

A compact, dual lensed high bay with lumen and CCT select features. Sensor ready, the SPHB delivers 12,000, 18,000, and 24,000 lumens in one single housing, making inventory complexity a thing of the past. In addition, the SPHB also offers up to 60,000 lumens for those higher mounting applications. The dual lensing with superior optical control delivers optimal performance while reducing high angle glare.

Click on product
to learn more



Product Benefits

- Inventory complexity - one fixture replaces 12 different configurations
- Sensor ready for easy, off-the-shelf field installation
- Dual functioning, high impact polycarbonate lens protects the LEDs while delivering optimal performance
- Compact design for easy, one-person install



Applications

Industrial • Commercial • Retail • Manufacturing •
Gymnasium • Multi-purpose • Grocery •
High Bay/Low Bay Applications

Certifications and Ratings



Metalux

UHBS2

Selectable LED High Bay



The innovative and high efficiency UHBS2 has 3 power levels, 5 CCT and 3 optical distributions, giving you the ultimate flexibility for any application by replacing 90 possible configurations with only 1! NSF certified, IP65 and NEMA 4X rated, the UHBS2 is great for manufacturing, retail, warehouse or industrial spaces.



Click on product to learn more

Product Benefits

- Selectable Distribution - Narrow, Medium, or Wide
- 5 CCT Color Select - 3000/3500/4000/5000/6500K
- Sensor ready port for quick plug and play install
- 120-347 volt, 0-10V dimming Class A driver
- NEMA 4X, IP65 and NSF rated
- Polycarbonate lens with IK08 impact rating
- 6kV rated (ANSI C82.77-5-2015) and FCC class A compliant



Certifications and Ratings



Applications

Industrial • Commercial • Retail • Manufacturing • Warehouse • Gymnasium • Multi-purpose • Grocery • High Bay / Low Bay Applications

APVTS

Lumen and CCT Select LED Vaportite

The APVTS Series combines the rugged, wet location rated construction of a vaportite with selectable CCT and lumen output. The APVTS's optical performance is ideal for interior and exterior applications including canopy, storage manufacturing and parking garages.

Click on product to learn more



Product Benefits

- Three color temperature and lumen select provide application versatility
- Impact-resistant durability using IK08 lens diffuser, housing and stainless steel latches
- Faster install and easy maintenance using new two-piece captive lens, electrical and housing design
- Standard 0-10V dimming to 10% for more energy savings
- Available in 4ft and 8ft models for more job and layout flexibility
- IP65 and UL Wet location listed for indoor and outdoor environments



Applications

Industrial • Manufacturing • Gymnasium • Warehouse •
Parking

Certifications and Ratings



Metalux

VT3S

VT3 Vaportite Selectable



The VT3 Selectable is a configurable industrial vaportite with a sealed and gasketed, reinforced fiberglass housing with a high impact diffuser. The VT3S offers selectable CCT and lumen with a single easy to access toggle switch. Use the VT3S for interior and exterior applications including parking garages, food processing, canopy, manufacturing and complex environments.



Click on product
to learn more

Product Benefits

- Selectable CCT in 3000/3500/4000K in >80 CRI
- Selectable lumens – Low, Medium, and High up to 6,500 lumens
- Precision optics in general, wide, or parking garage distribution
- High Impact IK10 Polycarbonate lens option
- Wet Location, IP65-66-67-69 Listed
- NSF International certified for NSF/ANSI Standard 2 – Food Equipment
- DLC Compliant efficacy and 5-year warranty

Certifications and Ratings



Applications

Parking • Cold Storage • Manufacturing • Warehouse •
Canopy • Food Processing • Complex Environments

AWS/AWWS

Achieva Selectable LED Wrap

Selectable and versatile commercial grade wrap solution suitable for ceiling, wall, or suspension mounting. The Achieva Wrap Selectable is offered in 2', 4', and 8' lengths along with selectable color options of 3500K, 4000K, or 5000K or 3000K, 3500K, and 4000K. The AWS also offers selectable lumen options, with up to 13,000 lumens, for a wide range of retrofit applications. Offered in both 80 and 90 CRI, the Achieva delivers flexible high performance lighting for stairwells, corridors, and low bay industrial spaces.

Click on product to learn more



Product Benefits

- Selectable CCT and selectable lumens in standard or HO lumen options
- Narrow 5.5" or Wide 10" polycarbonate IK06 rated lens in 2', 4', or 8' lengths
- Up to 165 lm/w efficiency, ideal for replacing up to 4 lamp fluorescent wraparounds and low-bay linear fluorescents
- 0-10V dimming to 5%, or sensor options available
- Suitable for ceiling, wall, or suspension mounting and row mounting
- Offered in both 90 CRI and 80 CRI color quality as well as options to meet CA Title 24 requirements



Applications

Offices • Education • Healthcare • Retail

Certifications and Ratings



Metalux

NWS

Lumen and CCT Select LED Wrap



Selectable commercial grade wrap solution suitable for ceiling, wall, or suspension mounting. NWS is offered in both 2' and 4' lengths along with selectable color options of 3500K, 4000K, or 5000K and selectable light output with up to 5,000 lumens. NWS is designed to provide soft diffused lines of light in corridors, hallways, stairwells, in addition to other ambient office, education, and healthcare spaces.



Click on product to learn more

Product Benefits

- 2' and 4' lengths with single embossed knockouts for easy continuous row installation
- Modern sleek design with frosted lens blends into any ceiling design
- Selectable switches located inside the housing for easy access when installing
- Selectable integrated microwave sensor option allows for local code compliance and enhanced energy savings

Certifications and Ratings



Applications

Offices • Education • Healthcare • Retail

RGB

Lumen and CCT Select LED Slot

This selectable slot fixture can be strategically placed throughout the space to create pleasing illumination and appealing topology in rows or individual placement. A selectable switch comes standard with three selectable lumen levels (High, Medium, Low) and three selectable color temperatures (3000k, 3500k, 4000k). Customer applications include open and traditional offices, classrooms, coves, corridors, and retail.

Click on product to learn more



Product Benefits

- 4" aperture, 6" grid width providing sleek lines of light
- IP40 rated so tightly sealed lens with no gaps to prevent bugs or debris
- Mounting flexibility for multiple applications with recessed grid, hard ceiling, surface, and suspended options available
- Integrated sensors for IoT connectivity and code compliance are available
- Switch tamper cover included to lock in settings if desired



Applications

Office • Education • Retail

Certifications and Ratings



Notes



Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
LumarkAP
Lumière
McGraw-Edison
Metalux
MWS
NeoRay
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites

Controls Brands

Greengate
Fifth Light
Intelligent Lighting Controls

**Connected Lighting Systems
and Smart Spaces Platform**

WaveLinx
Trellix Infrastructure