

FEATURES

- Dual 120/277 VAC, 60Hz input
- Made of high-impact, mar-resistant, injection-molded thermoplastic
- Two directional PAR18 incandescent gimbal-type lighting heads
- Black finish is available
- Accessorize with canopy or stem and canopy kits
- Maintenance-free lead calcium battery
- Solid-state charger with emergency output short circuit protection
- AC line-latching
- Brownout circuit and low battery voltage circuit

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.  
 COMPLIANCES: UL924 Listed; Damp Location



PC1-10  
 CONTOURS  
 EMERGENCY  
 LIGHT

ORDERING INFORMATION

SAMPLE NUMBER: PC1-10-BLK

Family	Optional Finish	Options and Accessories
PC1-10 =Emergency Light, dual-voltage, 120/277VAC, 60 Hz <sup>1</sup>	BLK = Black [Blank] =White (standard)	PCW =Canopy Kit, White PCB =Canopy Kit, Black PST6 =6" Stem and Canopy Kit PST12 =12" Stem and Canopy Kit GXB =Wire Guard, Wall Mount, AC-Only Exit GXC =Wire Guard, Ceiling-End Wall Mount, AC-Only Exit GXBW =Wire Guard, Wall Mount, Self-Powered Exit GXBC =Wire Guard, Ceiling-End Wall Mount, Self-Powered Exit

NOTES: 1. White standard finish.

