


Project		Catalog #		Type	
Prepared by		Notes		Date	



# HALO

## CEZ3125

3" Canless EZ-Trim  
Lamp-based direct mount  
15W Maximum

### Typical Applications

- Residential • Light Commercial

### Interactive Menu

- Order Information page 2
- Product Specifications page 2
- Product Warranty

### Product Certification




### Product Features



### Top Product Features

- Baffle trim
- Direct mount – does not require recessed housing or junction box
- GU10 lamp base, use with compatible LED lamps (sold by others)
- Air-tite, for use in insulated and non-insulated ceilings
- Suitable for 2x6 residential framing or shallow plenum commercial construction

### Dimensional and Mounting Details



## Order Information

SAMPLE ORDER NUMBER: **CEZ3125GU10WBICAT**

A complete luminaire consists of a Canless EZ-Trim lamp-based direct mount and a compatible lamp (sold by others).

Model	Lamp Base	Trim Type	Certifications
Model	Lamp Base	Trim Type	Certifications
<b>CEZ3125</b> = 3-inch Canless EZ-Trim	<b>GU10</b> = GU10	<b>WB</b> = White flange, white baffle trim	<b>ICAT</b> = IC rated, air-tite
Notes	Notes	Notes	Notes

## Compatible LED Lamps

- MR16 LED, GU10 base
- PAR16 LED, GU10 base
- MR11 LED, GU10 base

## Product Specifications

### Trim

- Durable metal baffle trim

### Lamp Compatibility

- For use with maximum 15W LED lamps
- GU10 lamp base
- Compatible with MR16, PAR16, MR11 LED lamps

### Installation

- Can be installed in 1/2" to 1-1/4" thick ceilings
- Suitable for 2x6 residential framing or shallow plenum commercial construction
- Repositionable junction box
- Heat treated springs hold fixture fitting securely in the ceiling eliminating light leaks
- Can be removed from below the ceiling for service or replacement

### Junction Box

- Pre-galvanized steel driver/junction box with captive hinged junction box cover
- Listed for six #12 AWG 90° C splice conductors: two in, two out plus two ground
- Two 1/2" conduit pry-outs
- Two Slide-N-Side™ non-metallic (NM) wire traps allow wiring outside the box
- Accepts NM cable types: 14-2, 14-3, 12-2, 12-3 (U.S.) and 14-2, 14-3, 12-2 (Canadian)
- Three 4-port push wire nuts with clear caps for quick and reliable mains voltage connections
- Integral mounting holes facilitate direct mounting to building structure or mounting frame

### Compliance

- Type IC thermally protected, suitable for direct contact to air permeable insulation and cULus listed for damp locations
- Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013
- Air-tite per ASTM-E283
- Can be used for State of California Title 24 high efficacy luminaire compliance with CA JA8-2016-E or JA8-2019-E labeled lamps
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- Contains no mercury or lead and RoHS compliant

### Warranty

- One-year limited warranty, consult website for details. [www.cooperlighting.com/legal](http://www.cooperlighting.com/legal)