



Introducing
FLIP-N-KLIP
LOCKING SPRINGS

NEW

NO HOUSING REQUIRED
Repositionable driver j-box included



The HLA Super Adjustable Canless LED Gimbal simplifies installation by mounting directly to drywall or suspended ceilings without the need for a recessed housing or additional junction box, saving time and money.

The revolutionary **Flip-N-Klip Locking Springs** prevent painful spring snap making installation faster, easier, and safer. The HLA Series features 5 field-selectable color temperature options, and the gimbal tilts up to 90° for ultimate aiming and control. Designed to match the look and dimensions of our best-selling HLB Series, HLAs are perfect for accent lighting and task lighting applications.

Product Features

- Round 3", 4", and 6" Super Adjustable Canless LED Gimbals
- Flip-N-Klip Locking Springs prevent painful spring snap
- **Lens & Trim:** Slim metal trim with smooth diffuse lens
- **Color Temperature (CCT):** 5-color Field-SeleCCTable (27/30/35/40/5000K); 90+ CRI
- **Brightness (@3000K):** 610, 660, 990 lumens
- **Dimming:** Dims to 5% (phase cut LE/TE); 120V input
- Matte White Round-to-Square Decorative Overlays (Sold Separately)
- AIR-TITE, wet location-listed, and ENERGY STAR®
- 50,000 hrs of maintenance-free operation in damp or wet locations
- 5-year warranty




0°
DOWNLIGHT



90°
TILT



360°
ROTATION



LEARN MORE



SAFER & SIMPLER

Springs lock upright during installation and removal, automatically clamping securely to the ceiling.



Complete Ordering Table

Catalog Number	Description	Lumens (@3000K)	CRI/CCT	Driver	UPC	Accessories			
						Decorative Overlays	New Construction Mounting Frames	New Construction Smash Plate	Extension Cables
HLA305FS5	3-inch Super Adjustable Canless LED Gimbal	610	90+ CRI, field selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K	120V 60Hz, LE & TE phase cut 100-5% dimming	080083301201	HLA3SDOMW 3-inch Matte White Round-to-Square Overlay	MF3RC 3" Round Mounting Frame with 1/2" Drywall Collar HL3RSMF 3" Round/Square Mounting Frame	SP346RS 3"/4"/6" Round/Square Smash Plate	HLB06FSEC 6-ft. extension cable HLB12FSEC 12-ft. extension cable HLB20FSEC 20-ft. extension cable
HLA406FS5	4-inch Super Adjustable Canless LED Gimbal	660	90+ CRI, field selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K	120V 60Hz, LE & TE phase cut 100-5% dimming	080083301225	HLA4SDOMW 4-inch Matte White Round-to-Square Overlay	MF4RC 4" Round Mounting Frame with 1/2" Drywall Collar HL4RSMF 4" Round/Square Mounting Frame		
HLA609FS5	6-inch Super Adjustable Canless LED Gimbal	990	90+ CRI, field selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K	120V 60Hz, LE & TE phase cut 100-5% dimming	080083301249	HLA6SDOMW 6-inch Matte White Round-to-Square Overlay	MF6RC 6" Round Mounting Frame with 1/2" Drywall Collar HL6RSMF 6" Round/Square Mounting Frame		



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.

NOTE: Due to T20 changes as of July 1st 2019 consult factory for current catalog number and availability for T20 compliant products.