

Catalog #		Date		Prepared by	
Project		Type		Notes	

HALO™

OUTDOOR LIGHTING

LED VAPOR TIGHT



LED VAPOR PROOF | 120-277V INPUT | 4000K | SWITCH ACTIVATED | DIE CAST HOUSING | FROSTED LENS | WET RATED

The Halo Outdoor VT LED Vapor Proof Light provides an indoor/outdoor solution in applications where lighting fixture protection and durability is required. The fixture provides equivalent light output up to 60-watt incandescent and 15-watt CFL fixtures, with high-quality and long lasting illumination. The fixture is vapor tight to protect against dust and moisture. Ideal for patios, garages, storage, and industrial areas. This fixture's traditional look and cool color temperature gives off a similar appearance as older technologies.

TOP PRODUCT FEATURES

UP TO
875 LUMENS



- Durable corrosion resistant die-cast metal housing
- Damage resistant frosted polycarbonate lens
- 5 total 1/2" conduit openings on top and sides
- Ceiling or wall mounted for indoor and outdoor use
- Universal power supply (120-277V, 50/60Hz)
- cULus Listed for wet location use.

PRODUCT CERTIFICATION



TYPICAL APPLICATIONS



LIGHT COMMERCIAL & RESIDENTIAL OUTDOOR

- Patios
- Storage area
- Garages
- Industrial areas




INTERACTIVE MENU

- [Order Information](#) page 2
- [Product Specification](#) page 2
- [Product Warranty](#) page 2
- [Product Dimensions](#) page 2
- [Technical Data](#) page 2

ORDER INFORMATION

Catalog Number	Description	Material no.	UPC	Case Qty	Case Dimensions (in.)			Weight (lbs)
					L	W	H	
VT0840L	HALO OUTDOOR LED VAPOR TIGHT FLOODLIGHT	13605299	080083260560	4	5.51	6.89	11.61	1.83

PRODUCT DIMENSIONS



PRODUCT SPECIFICATIONS

Construction

- Durable die-cast aluminum housing and cage provides protection against vandalism
- Vapor tight IP65 rating protects against dust and moisture
- Versatile mounting options – Wall, Ceiling and Post
- Frosted glass lens provides smooth and even light distribution

- (5) 1/2" NPT Conduit openings

Electrical

- Maintenance-free LEDs with L70 50,000 hours of life
- Universal power supply (120-277V, 50/60Hz)
- Fixture operating temperature range from -20°C to 40°C
- cULus listed for wet locations.
- 4kV surge protection

Optics

- 4000K color temperature
- Fixture produces up to 800 Lumens


Warranty

- Two year limited warranty, consult website for details.
www.cooperlighting.com

TECHNICAL DATA

Catalog Number	Description	Voltage (V)	Power (W)	Lumens	Efficacy	CCT(K)	CRI
VT0840L	HALO Outdoor LED Vapor Tight	120-277V	9.35	875	93.5	4000K	74.4

SUGGESTED MOUNTING HEIGHT



Minimum Footcandles (FC)		0.25 FC					
Mounting Height (Z)		10'		15'		20'	
Catalog Number	Lumens	X	Y	X	Y	X	Y
VT0840L	875	11.3	21.9	11.5	21.9	9.3	14.1

X = Forward Throw
Y = Wall Spread
Z = Mounting Heights

Notes:
Forward throw X = 1/2 Y for wall-mount applications only
See IES files for detailed photometry