

Project		Catalog #		Type	
Prepared by		Notes		Date	



INTERACTIVE MENU

- Ordering Information page 2
- Product Specifications page 2
- Energy and Performance Data page 3

LUMARK

TRX SELECTABLE

Floodlight Luminaire


Product Features & Certifications



QUICK FACTS

- 36 configurations in each SKU
- 3 Wattage selectable: 1,200 – 4,500 lumens
- 3 CCT selectable: 3000K-4000K-5000K, 80 CRI
- 2 beam angle selectable switches: NEMA 4x4 and 5x5 beam angles
- 2 mounting options included per fixture: Knuckle & Trunnion
- 120-347V

DIMENSIONAL DETAILS



STOCK ORDERING INFORMATION

Model Number	Mounting Type	Lumens Wattage	Wattage	Color Temperature	Distribution	Voltage
TRX15S-BZ = Selectable Tracer Flood Light, Knuckle & Trunnion, 15W, Bronze	Knuckle and Trunnion	1,200-2,250 Lms	15-12-8W	Selectable CCT: 3000,4000,5000K / 80CRI	NEMA 4x4 - 5x5 beam angles	120-347V, 50/60Hz
TRX30S-BZ = Selectable Tracer Flood Light, Knuckle & Trunnion, 30W, Bronze	Knuckle and Trunnion	2,250-4,500 Lms	30-24-18W			
TRX15S-BK = Selectable Tracer Flood Light, Knuckle & Trunnion, 15W, Black	Knuckle and Trunnion	1,200-2,250 Lms	15-12-8W			
TRX30S-BK = Selectable Tracer Flood Light, Knuckle & Trunnion, 30W, Black	Knuckle and Trunnion	2,250-4,500 Lms	30-24-18W			

PRODUCT SPECIFICATIONS

CONSTRUCTION

- Die-cast aluminum housing
- Durable surface powder coating spray
- Acrylic Lens

ELECTRICAL

- > 0.9 Power Factor at max wattage
- < 20% total harmonic distortion at max wattage
- Surge Rating 2kV

MOUNTING

- Knuckle (factory installed)
- Trunnion

FINISH

- Bronze
- Black

TYPICAL APPLICATIONS

- Facade
- Wall washing
- Landscape lighting
- Accent
- Sign lighting

SHIPPING DATA

- 8.7" x 6.1" x 6.9" unit carton dimensions
Approx weight 4.1 lbs
- 19.7" x 18.2" x 7.3" master carton dimensions
Approx weight 27.0 lbs
- 6 units per master carton

WARRANTY

- Five-year limited warranty. Consult website for details. www.cooperlighting.com/legal

Configuration	EPA
Yoke Mount (120deg)	0.21

ENERGY AND PERFORMANCE DATA

Power and Lumens

CCT SETTING	15W								
	8W - 4H4V			8W - 5H5V			12W - 4H4V		
	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY
3000K	1291	8.99	144	1300	8.9	146	1934	13.1	147
4000K	1307	8.99	145	1330	8.9	149	1958	13.1	149
5000K	1315	8.99	146	1343	8.9	151	1971	13.1	150

CCT SETTING	15W								
	12W - 5H5V			15W - 4H4V			15W - 5H5V		
	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY
3000K	1958	13.1	149	2330	15.7	148	2332	15.7	149
4000K	2003	13.1	153	2359	15.4	154	2386	15.4	155
5000K	2023	13.1	154	2374	15.6	152	2409	15.6	154

CCT SETTING	30W								
	18W - 4H4V			18W - 5H5V			24W - 4H4V		
	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY
3000K	2774	18.2	152	2785	18.2	153	3604	24.0	150
4000K	2809	18.2	154	2849	18.2	156	3649	24.0	152
5000K	2826	18.2	155	2877	18.2	158	3672	24.0	153

CCT SETTING	30W								
	24W - 5H5V			30W - 4H4V			30W - 5H5V		
	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY	LUMENS	WATTAGE	EFFICACY
3000K	3613	24.0	151	4619	31.6	146	4643	31.6	147
4000K	3697	24.0	154	4676	31.6	148	4751	31.6	151
5000K	3732	24.0	156	4706	31.6	149	4796	31.6	152

4H4V		
CCT	LUMENS	MULTIPLIER
3000K	2330	1.000
4000K	2359	1.012
5000K	2374	1.019

5H5V		
CCT	LUMENS	MULTIPLIER
3000K	2332	1.000
4000K	2386	1.023
5000K	2409	1.033