

Metalux

Elevate

LED Round High Bay



Scan for more.



Performance

Designed with precision dome optics, Elevate puts light where it's needed, reducing wasted lumens and energy



Versatility

truEgress integrated emergency lighting optimized to increase fixture spacing and reduce installation costs




Durability

Round die-cast aluminum housing adds durability and improved thermal control

The Elevate delivers targeted light levels with less fixtures and lower energy consumption

The Elevate Round High Bay is engineered to outperform traditional luminaires in demanding commercial and industrial environments. The durable diecast aluminum construction provides durability, optimal thermal control, and longer system life. Precision optics focus light exactly where it's needed, delivering higher foot-candles with fewer fixtures while reducing both wattage and installation cost. The durable diecast aluminum housing is IP65 rated and built to withstand harsh conditions from -40°C to 65°C. Ideal for manufacturing facilities, distribution centers, large indoor, sports/recreation, big box retail, and multipurpose spaces.



Manufacturing
Warehouse
Industrial
Commercial
Large Indoor
Multi-purpose
Educational



	Features	Benefits	Result
Performance	Precision optics focus light exactly where it's needed	Higher foot-candles with fewer fixtures, reducing both wattage and installation cost	
	Delivering up to 60K lumens downlight and up to 4000 upright lumens	Configurable construction delivers the perfect solution for almost any application	
	TruEgress integrated emergency lighting optimized to increase fixture spacing	Reduces the need for additional emergency lighting and added installation cost	
	UGR as low as 12 without the need for a refractor	Delivers required footcandles without the unsightly glare	
	Numerous integrated control options including WaveLinX	Increased energy savings and faster ROI	
Construction	Product is IP65 and NSF rated	Delivers peace of mind in complex environments	
	Full commercial offering and 5-year limited warranty	Guaranteed quality	
	Diecast Housing with Powder Coat finish	Added Durability and Thermal management	



Energy and Performance Data

EHBR1 (4000/5000K)	Lumen Package	Delivered Lumens							Wattage	Efficacy lm/W						
		Focus	Narrow	Medium	Wide	Aisle	Elliptical	TASM		Focus	Narrow	Medium	Wide	Aisle	Elliptical	TASM
	12	12461	12461	12361	12249	12272	12272	12295	67	187	187	186	184	184	184	185
18	17927	17927	17782	17621	17655	17655	17688	94	191	191	190	188	188	188	189	
24	23759	23759	23567	23354	23398	23398	23443	123	193	193	191	190	190	190	190	
30	30009	30009	29767	29498	29553	29553	29609	157	191	191	189	187	188	188	188	
36	35917	35917	35627	35305	35372	35372	35439	197	182	182	181	179	179	179	180	
42	42030	42030	41691	41314	41392	41392	41470	231	182	182	180	179	179	179	179	
48	48114	48114	47726	47294	47384	47384	47473	266	181	181	179	178	178	178	178	
54	53950	53950	53515	53030	53131	53131	53231	301	179	179	178	176	176	176	177	
60	60196	60196	59710	59170	59282	59282	59394	340	177	177	175	174	174	174	175	

truEgress Lamp Series

High-performance directional/rotational LED egress lamps

- Emergency solutions that reduce install complexity while reducing emergency power load by up to 60%.
- Reduce the number of required emergency fixtures during emergency operation
- Unidirectional narrow-beam precisely illuminates the path of egress
- Advanced fixed optics with 355 degree rotation simplifies installation and aiming
- Multiple EM configurations allow for installation mounting heights from 15ft up to 50ft

