

RL Dual Zone
Smart Wi-Fi® Recessed LED Downlighting
Connected by WiZ Pro

HALO



Connected by
WiZ
PRO

WiFi
CERTIFIED
+
Bluetooth®

16 Million Colors

Tunable White

The party just got twice as nice!

HALO Recessed Baffle Dual Zone LED Downlights smart Wi-Fi® control.

Experience full color & tunable white, wireless dimming, schedules, scenes, rhythms, and SpaceSense™ motion detection thanks to Connected by WiZ Pro technology.


Product Features

- Round Dual Zone Smart Wi-Fi® LED Fixtures (Canless or Recessed LED Trims). Suitable for remodel and new construction installations.
- White tuning (2200K – 6500K) + 16 million color, wireless dimming to 5% (120V input) all via the WiZ App
- Set schedules, scenes, static/dynamic lighting modes, rhythms, music sync, and SpaceSense™ motion sensing technology
- Configure and control lighting quickly with the WiZ App over Wi-Fi®
- Pro Installers can use the WiZ Pro Setup App to manage multiple projects, pair over Bluetooth, and access advanced features in the WiZ Pro Dashboard
- Lens & Trim: Transparent acrylic trim with matte white baffle & curved diffuse lens
- Brightness (nominal): 4" - Downlight: 750 lm; Ring: 70 lm • 5"/6" or 6" Downlights: 1000 lm; Ring: 100 lm
- IC-rated, AIR-TITE, Energy Star, and wet location-listed
- Life: 50,000 hrs of maintenance free operation
- 5-year warranty



LEARN MORE

Connected by



Complete Ordering Table

Canless LED Downlights

Catalog Number	Module	Lumens (Nominal)	CRI/CCT	Driver	Finish	Packaging
RLWZDZC4	4" RL Dual Zone Smart Wi-Fi® Recessed Baffle Canless LED Downlight Connected by WiZ Pro	Zone A: 750 lumens; Zone B: 70 lumens	90+ CRI, Full Color (16 million colors) + Tunable White (2200K to 6500K) via WiZ App	120V 60Hz, wireless dimming to 5%* (do not use with standard dimmers)	Matte White	Plastic-free recyclable
RLWZDZC6	6" RL Dual Zone Smart Wi-Fi® Recessed Baffle Canless LED Downlight Connected by WiZ Pro	Zone A: 1000 lumens; Zone B: 100 lumens	90+ CRI, Full Color (16 million colors) + Tunable White (2200K to 6500K) via WiZ App	120V 60Hz, wireless dimming to 5%* (do not use with standard dimmers)	Matte White	Plastic-free recyclable

LED Trims

RLWZDZT4	4" RL Dual Zone Smart Wi-Fi® Recessed Baffle LED Trim Connected by WiZ Pro	Zone A: 750 lumens; Zone B: 70 lumens	90+ CRI, Full Color (16 million colors) + Tunable White (2200K to 6500K) via WiZ App	120V 60Hz, wireless dimming to 5%* (do not use with standard dimmers)	Matte White	Plastic-free recyclable
RLWZDZT56	5"/6" RL Dual Zone Smart Wi-Fi® Recessed Baffle LED Trim Connected by WiZ Pro	Zone A: 1000 lumens; Zone B: 100 lumens	90+ CRI, Full Color (16 million colors) + Tunable White (2200K to 6500K) via WiZ App	120V 60Hz, wireless dimming to 5%* (do not use with standard dimmers)	Matte White	Plastic-free recyclable

*Wireless dimming only – do not use with standard dimmers

Accessories –

New Construction Mounting Frames/Plates and Extension Cables are available. Refer to spec sheets for more information.

Recessed LED Trims install into HALO recessed new construction and remodel housings/cans.

Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.
NOTE: Due to T20 changes as of July 1st 2019 consult factory for current catalog number and availability for T20 compliant products.



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2025 Cooper Lighting Solutions
All Rights Reserved
Publication No. BR51873325
December 2024

Product availability, specifications, and compliances are subject to change without notice.