



- Full LED product line with nickel cadmium batteries
- All products stocked and priced to sell
- EBPLED & SELW are market leading products – perfect entry at distribution
- [Sure-Lites Distributor Catalog is available](#)

## DISTRIBUTION

- Market leading LED emergency coverage creates lowest total cost solution
- Intuitive catalog logic and bundled features simplify the design process
- Superior options for design build applicationsz

## COMMERCIAL

- Market leading LED emergency coverage creates lowest total cost solution
- Intuitive catalog logic and bundled features simplify the design process
- Ideal for wet locations, extreme temperatures and harsh environments

## INDUSTRIAL

- Full LED portfolio
- Market leading, products with superior aesthetics
- Customizable, specification locking and patent pending features
- Superior aesthetics

## SPECIFICATION

Good

Better

Best

**DISTRIBUTION** 

**COMMERCIAL** 

**INDUSTRIAL** 

**SPECIFICATION** 




Click on products to learn more

APELMINI	APEL	SELW25	SEL50	SEL25	SEL17	SEL60R4	SEL50R7SD/ SEL25R10SD/ SEL60R4SD	SEL60R10SD/ SEL50R14SD/ SEL25R16SD	SELM60R10SD/ SELM50R14SD/ SELM25R16SD	SELM60R4SD	SELMREC	SELA	SELDWA	SELMTG	AEL2	AEL2SD	SELIN	SELDSD
----------	------	--------	-------	-------	-------	---------	--	--	---	------------	---------	------	--------	--------	------	--------	-------	--------

Series	APELMINI	APEL	SELW	SEL	SEL	SEL	SELM	SELMREC	SELA	SELDWA	SELMTG	AEL2	SELIN60SD	SELD	
<b>Material</b>	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate	Sheet Metal	Sheet Metal	Polycarbonate	Die cast AL	Sheet metal	Die Cast AL	Fiberglass	Die Cast AL	
<b>Source</b>	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	LED	
<b>Coverage</b>	17 feet	17 feet	25 feet	17/25/50 feet	25/50/60 feet	25/50/60 feet	25 feet or 60 feet	25, 50 or 60 feet	29 feet	29 or 50 feet	60 feet	25 feet	25, 50 or 60 feet	60 feet	
<b>Battery</b>	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	Nickel cadmium	
<b>Remote Capability</b>	No	No	NA	No	4 to 10 watts	10 to 16 watts	4 to 16 watts	4 to 10 watts	No	NA	5 watts	No	Yes	Yes	
<b>Color</b>	White	White	Ag/BK/WH/BZ	White or Black	White or Black	White or Black	White	White or Black	White or Black	Ag/BK/WH/BZ	White or Black	Ag/BK/WH/BZ	Grey	Ag/BK/Wh	
<b>Temp Range</b>	10° C to 40° C	10° C to 40° C	0° C to 40° C / -20° C to 55° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0° C to 40° C	0C to 40C / -20C to 55C	0C to 40C	-30° C to 55° C	0° C to 40° C	-30° C to 50° C
<b>Self Diagnostics</b>	No	No	No	Option	Option	Standard	Standard	Standard	Standard	Standard	Standard	Option	Standard	Standard	
<b>UL Rating</b>	Damp Location	Damp location	Wet Location	Damp location	Damp location	Damp location	Damp location	Damp location	Damp location	Damp location	Wet location	Damp location	Wet Location	NEMA4x	NEMA 4X / HAZ option
<b>Always On</b>	No	No	No	No	No	No	No	No	No	No	No	Yes	No	No	
<b>Availability</b>	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Q2 2019	Stock	Stock	Stock	

Good Better Best


**DISTRIBUTION** 

**COMMERCIAL** 

**INDUSTRIAL** 

**SPECIFICATION** 

Click on products to learn more



	APX	APC	LPX	CXSD	LPXC	EUS EUR	LPXW Outdoor	EUX	ACE	ELX/ES	UX HAZ
<b>Series</b>	APX	APC/APCH	LPX	CX	LPXC	EU	LPXW	EUX	ACE	ES / ELX	UX
<b>Type</b>	Box	Combo	Box	Box	Combo	Edge Lit	Box	Edge Lit	Circular	Edge Lit	Box
<b>Material</b>	Polycarbonate	Polycarbonate	Polycarbonate	Die Cast	Polycarbonate	Aluminum	Polycarbonate	Aluminum	Aluminum	Aluminum	Die Cast AL
<b>Mounting</b>	Universal		Universal	Universal	Universal	Sur / Rec	Universal	Universal	Universal	Sur / Rec	Universal
<b>Faces</b>	Universal	Universal	Universal	One or Two	Universal	Universal	One or Two	Universal	Universal	One or Two	One or Two
<b>Letter Color</b>	Red or Green	Red or Green	Red & Green	Red & Green	Red & Green	Red or Green	Red or Green	Red or Green	Red & Green	Red or Green	Red & Green
<b>Housing Color</b>	White, Black	White, Black	White, Black	Silver, Black, White	White, Black	Silver	Silver, Black, White	Silver, Black, White	Silver, Black, White	Wh, BK, BZ, BR, AL	Silver, Black, White
<b>Self Diagnostics</b>	N/A	N/A	Option	Standard	Option	N/A	Standard	Option	Standard	Option ELX	Standard
<b>Remote Capacity</b>	Option	Yes	Option	No	Option	No	No	No	No	No	No
<b>UL Rating</b>	Damp location	Damp location	Damp location	Damp location	Damp location	Damp location	Wet location	Damp location	Damp location	Damp location	NEMA4X/HAZ
<b>Availability</b>	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	Stock	MTO	Stock

Good

Better

Best

\$

\$\$


\$\$\$

\$\$\$\$

DISTRIBUTION



COMMERCIAL



INDUSTRIAL



SPECIFICATION



Click on products to learn more

APWR



SRP



SRM



SRPA



	APWR	SRP	SRM	SRPA
<b>Series</b>	APWR	SRP	SRM	SRPA
<b>Material</b>	Plastic	Polycarbonate	Sheet Metal	Polycarbonate
<b>Source</b>	LED	LED	LED	LED
<b>Number of heads</b>	1 or 2	1 or 2	1 or 2	2
<b>Adjustable</b>	Yes	Yes	Yes	Yes, with forward throw
<b>Coverage</b>	15 feet	13 to 60 feet	13 to 60 feet	29 feet
<b>Voltage input</b>	3.6 volts	4.8 through 12 volts	4.8 through 12 volts	4.8 through 6 volt
<b>Color</b>	White, Black	White, Black, Grey	White, Black, Grey	White, Black, Silver, Grey
<b>Temp Range</b>	0° C to 40° C	-30° C to 60° C	-30° C to 60° C	-30° C to 55° C
<b>UL Rating</b>	Wet location	Wet Location	Wet Location	Wet Location
<b>Availability</b>	Stock	Stock	Stock	Stock

Good

Better

Best

- DISTRIBUTION
- COMMERCIAL
- INDUSTRIAL
- SPECIFICATION



Click on products to learn more

	EBPLED7W	EBPLED-7.5WSD	EBPLEDLP-10WSD	EBPLED14W	EBPLED14WSD	EBPLEDC1LV-20W	EBPLEDC1HV-20W
<b>Series</b>	EBPLED7W	EBPLED-7.5WSD	EBPLEDLP-10WSD	EBPLED14W	EBPLED14WSD	EBPLEDC1LV-20W	EBPLEDC1HV-20W
<b>Fixture Compatibility</b>	LED	LED	LED	LED	LED	LED	LED
<b>Input Voltage</b>	120/277 VAC	120/277 VAC	120/277 VAC	120/277 VAC	120/277 VAC	120/277 VAC	120/277 VAC
<b>Power Output</b>	7W	7.5W	10W	14W	14W	20W	20W
<b>Output Voltage</b>	8VDC to 55VDC	15VDC to 50VDC	8VDC to 52VDC	16VDC to 55VDC	16VDC to 55VDC	20VDC to 50VDC	125VDC to 200VDC
<b>Battery</b>	NiCad	NiCad	NiCad	NiCad	NiCad	NiCad	NiCad
<b>Self-Diagnostics</b>	No	Yes	Yes	No	Yes	No	No
<b>Laser Test Capability</b>	Yes	No	No	Yes	Yes	No	No
<b>EZ-Key Battery Disconnect</b>	Yes	No	No	Yes	Yes	No	No
<b>Replaceable Battery</b>	No	No	No	No	Yes	No	No
<b>Temp Range</b>	0°C to 55°C	0°C to 55°C	0°C to 55°C	0°C to 55°C	0°C to 55°C	0°C to 55°C	0°C to 55°C
<b>UL Rating</b>	Field <sup>1</sup>	Factory or Field Install	Factory or Field Install	Field <sup>1</sup>	Field <sup>1</sup>	Factory or Field Install	Factory or Field Install
<b>Availability</b>	Stock	Stock	Stock	Stock	Stock	Stock	Stock

Notes: 1. Model EL7W and EL14W for factory install.