

DESCRIPTION

A series of lampholders employing simple geometric shapes that create bold statements in any application. Toolless lockable tilt and rotation with graduations for precise, repeatable aiming. Three media capable, these 50W PAR20 lampholders are comfortable in applications from Gallery to Specialty Retail. Threaded screw-on bezel provides positive engagement, and removable beveled spacer creates an attractive look when multiple media are not required. Ideal for accent and display lighting applications.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Flexible Track

Die Cast housing. Attaches electrically and mechanically anywhere along track.

B ... Electrical Quick Lock Adapter - Power Trac

Die cast housing. Attaches electrically and mechanically anywhere along track.

C ... Electrical Quick Lock Adapter - Architectural Track

Polycarbonate housing with integral fuse and on-off switch. Attaches electrically and mechanically anywhere along track.

D ... Yoke

Aluminum die cast yoke allows lampholder to rotate 330° and provides 0° to 90° vertical pivot for maximum aiming adjustability.

E ... Lockable Aiming

Lampholder tilt and rotation can be locked in place easily without the use of tools.

F ... Lampholder Body

Machined aluminum cylinders.

G ... Graduated Dials

Graduated dials for precise aiming of fixtures.

Labels


UL/c-UL Listed for use with Halo Architectural Linear and Flexible Track, Halo Power-Trac, and Lazer.



LF10620
LA10620
L10620

Synchro
50W PAR20 Accent

Flexible Track
Architectural Track
Power-Trac



LF
L=5.375" [132mm]
W=3" [76mm]
Max. Extension=
12" [294mm]

L
L=5.375" [132mm]
W=3" [76mm]
Max. Extension=
13" [330mm]


LA
L=5.375" [132mm]
W=3" [76mm]
Max. Extension=
13.1875" [335mm]

	1	06	20	
Track LF=Flexible Track L=Halo Power-Trac LA=Halo Architectural Track	Lamp Type 1=Incandescent	Series 06=Synchro	Lamp 20=PAR20	Finish AH=Aluminum Haze P=White (L and LA only) MB=Black (L and LA only)

• Product is only available in 120 volts.

Color Filters


- F22-20=Red Gel
- F76-20=Red Dichroic
- F72-20=Amber Dichroic
- F75-20=Yellow Dichroic
- F73-20=Green Dichroic
- F71-20=Peach Dichroic
- F74-20=Medium Blue Dichroic
- F77-20=Dark Blue Dichroic
- F78-20=Light Blue Dichroic
- F79-20=Neutral Density
- F80-20=Magenta
- F55-20=Yellow Gel
- F33-20=Medium Blue
- F44-20=Medium Green
- F66-20=Mercury



Color Filters

Beam Modifying Lenses



- LSL-20=Linear Spread Lens
- OSL-20=Overall Spread Lens
- DIF-20=Diffuse Lens



Beam Modifying Lenses

Hex Cell Louver

- LVR-20=Hex Cell Louver



Hex Cell Louver

Remove beveled spacer when 2 or 3 media are used.