

COOPER LIGHTING SOLUTIONS - ALL-PRO™

DESCRIPTION

The ALL-PRO LED Twin Head 2850 series is designed for general outdoor lighting, utilizing a durable polycarbonate housing and frosted lens design. Producing over 2000 lumens, these products are available in flood and motion sensor configurations for a wide variety of applications. The housing employs a simple and fast mounting mechanism and comes in white or bronze finish.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

- Durable polycarbonate housing suitable for wet locations
- One-handed fixture adjustments
- UV stable polycarbonate lens
- Suitable for wall or eave mounting using recessed junction box

Electrical

- 120VAC, 60Hz
- Maintenance-free LEDs with 35,000 hours of life
- Fixture operating temperature range from -30°C to 40°C
- cULus listed
- External supply wiring 75°C minimum
- Motion sensor version available with 180° detection area and up to 70' range. Motion timer adjustable from 2-12 minutes

Optics


- White version produces 2220 lumens using 24.4 watts
- Bronze version produces 2000 lumens using 24.4 watts
- 0.5% diffuse frosted lens for even distribution
- 5000K CCT perfect for security applications output

Warranty


- 5 year limited warranty

DIMENSION - LOW PROFILE MODELS



MOTION




MOUNTING



FLOOD



MOUNTING



TWIN HEAD 2850 SERIES

2000lm Flood and Motion Activated Lighting

Innovation you can rely on™

CERTIFICATION DATA

cULus Listed
Lighting Facts® Approved

TECHNICAL DATA

120V only
-30°C to 40°C Temperature Rating
External Supply Wiring 75° Minimum
Wall and Eave Mount

Model	Product Description	Finish
FT2850L	LED Twin Head Floodlight	Bronze
FT2850LW	LED Twin Head Floodlight	White
MST2850L	LED Twin Head Floodlight with Motion Sensor	Bronze
MST2850LW	LED Twin Head Floodlight with Motion Sensor	White

Cooper Lighting Solutions

1121 Highway 74 South
Peachtree City, GA 30269
P: 770.486.4800
www.cooperlighting.com

Specifications and dimensions subject to change without notice.

PS502056EN
08/3/2017