

DESCRIPTION

The Rival LED Specification Series meets the standards of architectural requirements while providing many options and accessories to customize any installation.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES**Electronic**

- Dual 120/277VAC 60Hz input
- Solid state charger and transfer circuitry (no relays or fuses)
- Momentary test switch; circuit is battery short circuit protected
- Brown out protection, low voltage disconnect
- LED Heads with lumen output equal to 9W incandescent

Battery




- Long life, sealed, maintenance-free, nickel cadmium battery

Housing Construction

- Standard finish, durable white powder coat.
- Steel units fabricated of 20 gauge steel
- Conduit knockouts and rear keyhole mounting knockouts provided

Code Compliance

- Meets or exceeds all current UL 924 requirements, and applicable sections of the Life Safety Code

**10REL72-LED83****10-REL36-LED42**

RIVAL LED SPECIFICATION

STEEL
SPECIFICATION GRADE
EMERGENCY UNIT
LED LAMPS

EMERGENCY LIGHTING

ORDERING INFORMATION

Catalog No.	Heads	Watts per Head	Max. Remote Heads
10REL36-LED42	2	Lumens equal to 9W	2
10REL72-LED82	2	Lumens equal to 9W	6
10REL72-LED83	3	Lumens equal to 9W	5

OPTIONS AND ACCESSORIES**ACCESSORIES**

Description	Code
Cord Sets	
120 Volt	PC3
277 Volt (Specify male plug type)	PC0
Mounting Bracket	BM
Mounting Shelf	SM
Wire Guards	WBXG

OPTIONAL: LED REMOTE HEADS

RFLED401	Single LED Remote Head
RFLED402	Double LED Remote Head