



Save Money



Save Time





















Peace of Mind

The Fail-Safe MRI-ASR is an architectural slot recessed specifically designed for MRI rooms in healthcare facilities and medical spaces because of its non-ferrous construction. Available in 2', 4' and 8' lengths with 2" and 4" apertures, the MRI-ASR has a slim frame design allowing a fully luminous aesthetic with only the illuminated lens being visible. The fixture also has multi-channel MRI filters and a remote driver.



 Save Money
  Save Time
  Peace of Mind

Category	Feature	Benefit	Result
Construction	Non-ferrous construction	Specifically designed for MRI rooms	  
	Aluminum housing with aluminum hardware	Rugged and durable construction	  
	Mechanical lens hold downs	Firmly secures the lens inside the luminaire	  
	Remote driver and electrical filter	Complies with Electromagnetic Interference (EMI) requirements for MRI rooms	  
Performance	UL listed for damp locations and NSF rated	Can be easily cleaned	  
	Five year warranty standard, ten year warranty available	Guaranteed performance	  

Energy and Performance Data by Catalog Number



Fixture	Wattage	Lumens	LPW	Max # of Fixtures per Driver		
				0-10V UNV	0-10V 347V	DALI
MRI-2ASR-2-250-L840-OPL	8.0	506	63.5	9	9	8*
MRI-2ASR-2-500-L840-OPL	17.4	1006	57.8	4	4	4
MRI-2ASR-2-750-L840-OPL	33.3	1441	43.3	2	2	2
MRI-2ASR-4-250-L840-OPL	17.3	1012	58.5	4	4	4
MRI-2ASR-4-500-L840-OPL	40.8	2035	49.9	2	2	2
MRI-2ASR-4-750-L840-OPL	71.2	3224	45.3	1	1	1
MRI-2ASR-8-250-L840-OPL	34.6	2024	58.5	2	2	2
MRI-2ASR-8-500-L840-OPL	81.6	4070	49.9	1	1	1
MRI-2ASR-8-750-L840-OPL	x	x	x	x	x	x
MRI-4ASR-2-250-L840-OPL	6.6	502	76.1	11	11	10*
MRI-4ASR-2-500-L840-OPL	14.3	1044	73.0	5	5	5
MRI-4ASR-2-1000-L840-OPL	29.7	1997	67.2	2	2	2
MRI-4ASR-4-250-L840-OPL	12.7	1005	79.1	6	6	5
MRI-4ASR-4-500-L840-OPL	26.6	2006	75.4	3	3	2
MRI-4ASR-4-1000-L840-OPL	58.4	4018	68.8	1	1	1
MRI-4ASR-8-250-L840-OPL	25.4	2010	79.1	3	3	2
MRI-4ASR-8-500-L840-OPL	53.2	4012	75.4	1	1	1
MRI-4ASR-8-1000-L840-OPL	x	x	x	x	x	x

Note: *Not available for single fixture, must have at least 2.