

# Vandal Resistant LED Vaportite

## Selection Guide

# Fail-Safe

**M**arket focused portfolio with products designed for broad applications

**V**alue - competitive prices with industry leading DLC listings

**P**erformance - market leading performance with connected sensors options delivering value beyond lumens per watt



**Fail-Safe's** Vandal Resistant Vaportite fixtures deliver reliability and robust construction for complex environments, able to withstand high levels of abuse.

Click on products to learn more

Good

Better

Best

		VRVT2	VRVT3	VRVT4S	VRVT4
<b>APPLICABILITY<sup>1</sup></b>	Canopy	★★	★★		
	Parking Garage	★★	★★★		
	Warehouse	★★★	★★★	★	★
	Food Processing	★★	★★★	★★	★★
	Manufacturing	★★	★★	★★★	★★★
	Complex Environments	★	★★★	★★★	★★★
	Natorium	★★	★★★	★★★	★★★
	Vivarium	★★★	★★★	★★★	★★★
<b>FEATURES / PERFORMANCE</b>	Lumen Range	2,000 - 22,000	2,000 - 8,000	9,000 - 18,000	9,000 - 30,000
	Efficacy (Max)	150 lm/W	154 lm/W	165 lm/W	146 lm/W
	Distribution <sup>2</sup>	G, W	G, W, P	G	G
	Sizes	2', 4', 8'	2', 4'	2'	4'
	Housing	Fiberglass/Polyester	Fiberglass/Polyester	Fiberglass	Fiberglass
	Lensing	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb
	Wet Location	Yes	Yes	Yes	Yes
	IP Rating	IP65	IP65, 66, 67	IP65, 66, 67, 69	IP65, 67
	NSF	Yes	Yes	Yes	Yes
	NEMA 4X	None	None	Yes	Yes
	Life (@60K hrs)	L91	L91	L91	L92
	Ambient Range	-40C to 35C	-40C to 50C	-40C to 40C	-40C to 40C
	Emergency	Yes	Yes	Yes	Yes
	Vandal Resistant	Optional	Optional	Optional	Optional
Tamperproof	Standard	Standard	Standard	Standard	
Narrow Spectrum Color LED	Red, Amber, Green	Red, Amber, Green	Red, Amber, Green	Red, Amber, Green	
<b>INTEGRATED CONTROLS</b>	Basic Occupancy	✓	✓	✓	✓
	Stand Alone Daylight / Occupancy	✓	✓	✓	✓
	WaveLinx				

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable  
 2. G=General, W=Wide, P=Parking Garage.