

FEATURES

- Dual 120/277 VAC, 60Hz input
- Made of high-impact, mar-resistant, injection-molded thermoplastic
- Two directional PAR18 incandescent gimbal-type lighting heads
- Black finish is available
- Accessorize with canopy or stem and canopy kits
- Maintenance-free lead calcium battery
- Solid-state charger with emergency output short circuit protection
- AC line-latching
- Brownout circuit and low battery voltage circuit

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.
COMPLIANCES: UL924 Listed; Damp Location




PC1-10
CONTOURS
EMERGENCY
LIGHT

ORDERING INFORMATION

SAMPLE NUMBER: PC1-10-BLK

Family	Optional Finish	Options and Accessories
PC1-10=Emergency Light, dual-voltage, 120/277VAC, 60 Hz ¹	BLK=Black [Blank]=White (standard)	PCW=Canopy Kit, White PCB=Canopy Kit, Black PST6=6" Stem and Canopy Kit PST12=12" Stem and Canopy Kit GXB=Wire Guard, Wall Mount, AC-Only Exit GXC=Wire Guard, Ceiling-End Wall Mount, AC-Only Exit GXBW=Wire Guard, Wall Mount, Self-Powered Exit GXBC=Wire Guard, Ceiling-End Wall Mount, Self-Powered Exit

NOTES: 1. White standard finish.



Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.