

Description

The Classic pendants from Halo offer clean, simple lines that blend with a variety of interior spaces and provide effective task or accent lighting. These line voltage Cylinder Pendants can be ordered with an A19 styled integrated LED solution. It is available in 2700K and 3000K at 90 CRI.

Catalog #		Type
Project		
Comments		Date
Prepared by		

Specification Features

Electrical Quick Lock Adapter - Power Trac

- Polycarbonate housing
- Attaches electrically and mechanically anywhere along Halo Power Trac and Lazer Track.

Canopy - Surface Mount

- Aluminum canopy
- Attaches to standard junction box.

Shade

- White, Amber or Blue cased glass
- The white inner glass casing provides an even diffusion of light throughout the shade

Finial

- Machined brass finial


Cord

- Field adjustable 5' long 18AWG clear-jacketed cord.

Labels

- cCSAus Listed

Dimensions



Ordering Information

Example: L1-CYL-AH-LPM927-AH-AH-AM

Track	Style	Finial Finish	LED Module	Module/Cord
L1 - Halo Power-Trac	CYL - Cylinder	AH - Aluminum Haze	LPM927 - 8W LED, 400 lm, 90 CRI, 2700K	AH - Aluminum Haze
H1 - Surface Mount		BRZ - Bronze	LPM930 - 8W LED, 400 lm, 90 CRI, 3000K	

Adapter/Canopy Finish

- AH - Aluminum Haze
- BRZ - Bronze
- P - White
- MB - Black

Shade Colors

- AM - Amber
- BL - Blue
- WH - White



AM amber



BL blue



WH white

Classic

**Line Voltage
Cylinder Pendant**

LED

**Power-Trac
Surface**