

DESCRIPTION

The Classic pendants family from Halo include 5 different styles with glass or metal shades. Clean simple lines blend with a variety of interior spaces and provide effective task or accent lighting. The shapes include soft cones, cylinders and tall cones of cased glass in white, amber or blue. Metal shades are available in two styles in aluminum haze or bronze finishes. The low voltage Bullet pendants use MR16 or T4 12V lamps.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Linea

Polycarbonate housing. Attaches electrically and mechanically anywhere along Linea track.

B ... Canopy - Surface Mount

Aluminum canopy with integral 12V transformer. Attaches to standard junction box.

C ... Shade

Spun metal shade with decorative perforations at the bottom.

D ... Finial

Machined brass.

E ... Cord

Field adjustable 8' long 18AWG clear-jacketed cord.

Labels


ETL Classified.



LV2MBLT H2MBLT

**Classic Low Voltage
Pendant
Bullet**
35W T4 50W MR16

Linea
Surface



	MBLT		4	
Track LV2=Linea Track H2=Low Voltage Surface Mount	Style MBLT=Bullet	Shade/Finial Finish AH= Aluminum Haze BRZ= Bronze	Lamp Type (not included) 4=12V MR16, T4	Adapter/Canopy Finish Blank=Same as Finial (LV2 is not available in BRZ Finish) BRZ=Bronze (H2 only) P=White MB=Black