

DESCRIPTION

The Classic pendants family from Halo include 5 different styles with glass or metal shades. Clean simple lines blend with a variety of interior spaces and provide effective task or accent lighting. The shapes include soft cones, cylinders and tall cones of cased glass in white, amber or blue. Metal shades are available in two styles in aluminum haze or bronze finishes. The low voltage Soft Cone Pendants use MR16 or T4 12V lamps.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Linea

Polycarbonate housing. Attaches electrically and mechanically anywhere along Linea track.

B ... Canopy - Surface Mount

Aluminum canopy with integral 12V transformer. Attaches to standard junction box.

C ... Shade

White, Amber or Blue cased glass. The white inner glass casing provides an even diffusion of light throughout the shade.

D ... Finial


Machined brass.

E ... Cord

Field adjustable 6' long 18AWG clear-jacketed cord.

Labels

ETL Classified.



**LV2SCN
H2SCN**

**Classic Low Voltage
Pendant
Soft Cone
50W MR16/T4**

Linea
Surface

Track LV2=Linea Track H2=Surface Low Voltage	SCN Style SCN=Soft Cone	Finial Finish AH=Aluminum Haze BRZ=Bronze	4 Lamp Type (not included) 4=12V MR16, T4	Attachment Finish LV2, H2 Blank =Same as Finial P=White MB=Black	Shade Colors AM=Amber BL=Blue WH=White
--	-------------------------------	---	---	--	---