

DESCRIPTION

Round cylinder in choice of white, matte black, silver or bronze finish can be used to blend with or accent varying architectural styles. Choice of reflector types and finishes allows customizing of lighting effects. Adjustable socket cap adjusts without tools to maintain proper filament position and focus when alternate lamp sizes are used. Pendant kits allow unit to be stem mounted on ceilings with up to 45° slope.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Reflector

Alzak® reflector, .050 thick aluminum, with a spun parabolic contour. Positive reflector mounting via keyed holes and screws.

Baffle

Black seamless aluminum Coilex grooved baffle.

Housing

Round seamless .050 spun aluminum housing available in white, bronze or matte black.

Mounting

Mounting canopy installs to ceiling mounted junction box (by others). Insulating pad included in mounting canopy.


Socket

Socket adjusts and locks in position without tools for different size lamps. Medium base porcelain socket with nickel plated brass screw shell.

Labels

cULus listed, standard damp label.

DIMENSIONS



H8600
H8605
1600
3600
4655

Medium Base LED lamps

6-Inch Ceiling or Wall Mount

ORDERING INFORMATION

Housing	Housing Finish	Max Wattage Label	Trims	Finish	Accessories (for ceiling mount)
H8600 =Medium base socket for ceiling mount or suspended H8605 =Medium base socket for wall mount	P =White BZ =Bronze MB =Matte Black SL =Silver	WL8 =8W WL12 =12W WL20 =20W WL25 =25W WL30 =30W	1600 =Reflector (H8600 only) 3600 =Reflector 4655 =Baffle	B =Specular Black (1600 & 3600) GPH =Graphite Haze (1600 & 3600) H =Semi-Specular Clear (1600 & 3600) LI =Specular Clear (1600 & 3600) MW =Matte White WH =Wheat (1600 & 3600) WMH =Warm Haze (1600 & 3600)	H836P =Pendant Kit, White, 36" H836BZ =Pendant Kit, Bronze, 36" H836MB =Pendant Kit, Black, 36"