

DESCRIPTION

A low brightness 6-inch aperture adjustable accent fixture for PAR38 and PAR30L LED lamps. Optics allow the lamp axis to pivot about the center of the aperture at the ceiling line, allowing maximum light output with no flashback. 20° truncated cone allows full range and flexibility of aiming.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Reflector

Spun 0.040" aluminum. Available in a variety of Alzak® finishes. Torsion springs pull trim tight to ceiling. Reflector is keyed to prevent improper orientation relative to lamp. PAR30L lamps can be removed through the reflector.

Trim Ring

Self flanged or molded white trim ring.

Aiming Mechanism

Stable lamp aiming and locking mechanism allows smooth 365° rotation and 35° elevation adjustment. Lamp aiming scale enables consistent setting across multiple fixtures.

Housing

One piece die cast 1-1/2" deep collar. Housing is painted optical matte black to eliminate stray light.

Universal Mounting Bracket

Accepts 1/2" EMT, C Channel, T bar fasteners and hanger bars. Provides 5" total adjustment.

Conduit Fittings

Die-cast screw tight connectors.

Socket

Medium base porcelain socket with nickel plated screw shell.

Insulation Detector

Self-resetting insulation detector opens circuit if insulation is improperly installed.

Labels

cULus listed, damp location.




HA6
6470/6471

12 - 30W
LED PAR38 / PAR30L

6-Inch Adjustable

DIMENSIONS



ORDERING INFORMATION

Housing	Options	Max Wattage Label	Trims	Finish	Option	Accessories
HA6=6" Directional, PAR30L, PAR38	CP=Chicago Plenum	WL10=10W WL12=12W WL20=20W WL25=25W WL30=30W	6471=Self Flanged 6470=Molded Trim Ring	B=Specular Black GPH=Graphite Haze H=Semi-Specular Clear LI=Specular Clear MW=Matte White WH=Wheat WMH=Warm Haze BB=Black Baffle (6470 only) WB=White Baffle (6470 only)	WF=White Painted Flanged (Self Flanged only)	H277=Step Down Transformer, 300VA Max HB26=C Channel Bar Hangers, 26" Long, Pair HB50=C Channel Bar Hangers, 50" Long, Pair RMB-22=Wood Joist Bar Hanger, 22" Long, Pair L200 Series=Optical Lenses for PAR lamps, use with LC30 Lens Clips LC30=Lens Holder for PAR30 Lamps and L200 Series Lens LC38=Lens Holder for PAR38 Lamps and L200 Series Lens