

Streetworks

GLAN Galleon II

Features and Benefits

PERFORMANCE, DELIVERED

Galleon II area and site is the next generation of industry-leading, specification-defining outdoor lighting you could only expect from Galleon. Delivering best-in-class optical distributions, combined with unmatched configurability, Galleon II sets a new standard for high performance lighting solutions in outdoor environments.

PRODUCT FEATURES

- Lumen packages range from 3,300 – 73,500 (33W – 552W)
- Efficacy up to 159 lumens per watt
- 16 optical distributions
- Available in 4, 6 and 9 square housings

PRODUCT BENEFITS




Construction

Cast housing with simplified installation includes factory-installed arms



New Mounting Options

Redesigned pole mount, wall mount, adjustable flood options and an all-new upswept arm option



Integrated Power Tray

Drivers, surge and control modules easily removed for fast serviceability



Improved Performance

Better efficacy, improved thermal management for superior reliability



GLAN Galleon II

QUICK FACTS

- 0-10V dimming driver standard
- IK10 rated
- 3G vibration rated
- 10kV surge standard
- Five year limited warranty

