



STOCK PRODUCT GUIDE

Lighting & Controls

HALO

METALUX

GREENGATE

SURE-LITES

LUMARK

Introducing
MarketPro
Essentials

MARKETPRO
ESSENTIALS

Uniting Affordability
& Performance

VOL. 2 **2025**

At Cooper Lighting Solutions, we deliver industry-leading indoor and outdoor lighting products, lighting controls, smart lighting systems, programs and services.



VISIT OUR

MARKETPRO WEBSITE

Your one-stop shop for tools and resources designed to help grow your business

- ✓ Product Guide
- ✓ E-Commerce Tools
- ✓ Find Utility Rebates
- ✓ Sample Before You Buy
- ✓ Marketing & Training

READILY-AVAILABLE SOLUTIONS FROM OUR TRUSTED BRANDS

The MarketPro program provides our customers with top selling lighting and controls products from industry-preferred brands for their trusted performance, reliability and quality. These products are in-stock and ready to ship to meet your project needs.



In-Stock

Our essential products are in stock and readily-available to ship



Top Brands

Trusted products from HALO, Metalux, Greengate, Sure-Lites and Lumark



Proven Best Sellers

Contractor preferred top selling lighting and controls products



Sample Before You Buy

Try new products risk free



Innovation

State-of-the-art product innovation, direct mount installation, selectable technology and integrated controls



Utility Incentives

Products qualify for ENERGY STAR® and DLC®, saving money and adding value



Quick Solutions

Easily access our most popular, readily available products through our Quick Spec program



Training & Education

Online and instructor-led classes to expand your lighting and controls knowledge



Visit the MarketPro website to download the product guide

COOPERLIGHTING.COM/MARKETPRO

MARKETPRO ESSENTIALS

Stock Lighting Solutions

Uniting Affordability & Performance

INTRODUCING MARKETPRO ESSENTIALS - our go-to products for exceptional value, contractor-preferred options, and trusted performance! We are bridging the gap between cost and quality, as we deliver value with reliable effectiveness.



HALO



METALUX



SURE-LITES



LUMARK

Experience all the benefits of MarketPro **PLUS** exceptional value on your favorite essential products!

-  **FREE Freight**
Free delivery to keep products flowing on and off your shelf
-  **Guaranteed Returns**
One year from purchase
-  **Fast Shipping**
2 days or less



Explore MarketPro Essentials with Ease!

Easily spot the Essential products identified in the **yellow** highlighted tables and the **ES** icon.



| Catalog Number | Description |
|----------------|--------------|
| HLBSL406FSS | 4' Downlight |
| HLBSL609FSS | 6' Downlight |

| Catalog Number | Description |
|-----------------------|------------------------|
| HLBE4069301EMWR-12PK* | 4' Downlight (12-Pack) |
| HLBE4069301EMWR-24PK* | 4' Downlight (24-Pack) |
| HLBE6099301EMWR-12PK* | 6' Downlight (12-Pack) |
| HLBE6099301EMWR-24PK* | 6' Downlight (24-Pack) |



Two easy ways to find MarketPro Essentials!

- Explore all Essentials products on our website
- Easily order all Essentials products on the Prism Portal

OUR BRANDS AND THE MARKETS WE SERVE



RESIDENTIAL

Residential lighting fixtures for single and multi-family new construction and remodel projects.



COMMERCIAL

Lighting and control solutions for healthcare, education, hospitality, retail and office.



INDUSTRIAL

Lighting and control solutions for warehouses, distribution centers and logistic facilities.



OUTDOOR

Lighting that provides easy installation, area safety, and energy savings in commercial and industrial spaces.

We deliver a range of innovative and reliable indoor and outdoor lighting and controls product solutions specifically designed to maximize performance, energy efficiency and cost savings.

- 8 | **HALO**
Recessed & Surface Downlights
- 32 | **METALUX**
Ambient Commercial & Industrial
- 42 | **CONNECTED LIGHTING & CONTROLS**
WaveLinx LITE
WaveLinx CAT
Greengate
- 50 | **SURE-LITES**
Exit & Emergency
- 58 | **LUMARK, LUMARK AP & HALO OUTDOOR**
Outdoor Commercial & Industrial


NEW PRODUCT SPOTLIGHT

At Cooper Lighting Solutions, we build forward-thinking lighting solutions that make people’s lives safer, while making buildings, homes, and cities smarter and more sustainable. Learn about our latest lighting solutions and new MarketPro products.

► Metalux CGRK Retrofit Kit Flat Panel

The CGRK panel retrofit kit is the go-to kit for projects requiring energy savings, simple installation, offering both selectable lumens and selectable color.

PAGE 34



► Metalux EZBY Series High Bay

The EZBY is your contractor go-to high bay. Made for quick turn small to medium projects. Offering both selectable color and lumens with a sensor-ready port, 6ft cord, mounting ring, and robust IP65 rating.

PAGE 39



► Metalux UHBS2 High Bay

The UHBS2 is the next generation round LED high-bay offering 3 optical distributions, selectable color and lumens with a sensor-ready port. UHBS2 is NEMA 4X, IP65 and NSF listed with an IK08 polycarb lens.

PAGE 39



► Lumark CYL Cylinder Wall Mount

The Wall Cylinder has a modern design with effective up/down illumination. Durable waterproof housing resistant to rust and impact can be used outdoors in all weather conditions.

PAGE 60





Canless
Downlighting
p. 9-16



Surface Mount
Downlighting
p. 18-22



Recessed LED and
Traditional Trims
p. 24-27



Under
Cabinets
p. 28



Recessed
Housings
p. 29



Smart Wi-Fi
Lighting
p. 30-31

HALO®

RECESSED LED DOWNLIGHTS


HALO is the industry leader in high-quality recessed downlighting, offering the widest selection of innovative and flexible solutions for your application needs.

HALO CANLESS DOWNLIGHTING


GO CANLESS! Installs Virtually Anywhere!

- Field-Selectable color temperatures
- Mounts to drywall or suspended ceilings (no housing required)
- Remote driver/junction box included
- Rated for insulation contact (IC) & non-IC ceilings

Quick and Easy Installation





MORE FLEXIBILITY!
SAVE TIME AND MONEY!
NO HOUSING NEEDED!



New Construction Mounting Frames and Smash Plate

For Installing Canless Downlights in New Construction


- Use HALO Mounting Frames/Smash Plates on your next new construction project
- Toolless thumbscrews hold remote driver/jbox to the frame during rough in
- **MF Series** - 4" & 6" rounds with 1/2" drywall collar
- **HL Series** - 3", 4", 6", & 8" rounds that convert to squares with corner knockouts
- **Smash Plate** - Our most cost-effective single frame solution that can fit 3", 4", or 6" HALO Canless Fixtures (convert 4" or 6" openings to squares with corner knockouts)



MF Series



HL Series



No hanger bars

Smash Plate

| Catalog Number | Description | UPC |
|----------------|--|--------------|
| MF4RC | 4" Round Mounting Frame with 1/2" Drywall Collar | 080083268009 |
| MF6RC | 6" Round Mounting Frame with 1/2" Drywall Collar | 080083268023 |
| HL3RSMF | 3" Round/Square Mounting Frame | 080083876143 |
| HL4RSMF | 4" Round/Square Mounting Frame | 080083876167 |
| HL6RSMF | 6" Round/Square Canless Mounting Frame | 080083876181 |
| HL8RSMF | 8" Round/Square Canless Mounting Frame | 080083890460 |
| SP346RS | 3"/4"/6" Round/Square Smash Plate | 080083288236 |

SLIM CANLESS DOWNLIGHT Product Selection Guide

| | | Good | Better | Best | |
|----------------------|--|--|----------------------------|-----------------------------------|--|
| | | MarketPro Essentials | | | |
| | | HLBE & HLBSL | HLBPH | HLB | HLBC/HLBC+ |
| FEATURES/PERFORMANCE | Slim 1/2" Thin | ✓ | ✓ | ✓ | ✓ with regressed lens + 2-in-1 (Canless-to-Can) Install Option |
| | Size / Shape | 4", 6" Round | 4", 6" Round | 3", 4", 6", 8", 12" Round, Square | 4", 6" Round, Square ¹ |
| | Lens | Smooth | Smooth | Low-glare Prismatic | Regressed, Low-glare Prismatic |
| | Max Lumens (By size @ 3000K) | 745, 1,025 | 805, 1,015 | 595, 790, 1,020, 2,350, 2,300 | 975, 1,270 (Lumen Select, Dedicated) |
| | Color Temperatures (CCT) | 5 CCT 27/30/35/40/5000K Dedicated: 3000K | 5 CCT 27/30/35/40/5000K | 5 CCT 27/30/35/40/5000K | 5 CCT w/ D2W D2W/27/30/35/40/5000K |
| CONTROL | Dimming | 10% Phase Cut | 5% Phase Cut | 5% Phase Cut, 0-10V ² | 5% Phase Cut, 0-10V |
| | Estimated Life Hours | 35,000 | 50,000 | 50,000 | 50,000 |
| | Input Voltage | 120V | 120V | 120V, 120-277V | 120V, 120-277V |
| ACCESSORIES | Fits Mounting Frames | ✓ | ✓ | ✓ | ✓ |
| | Decorative Overlays ³ | ✓ | ✓ | ✓ | ✓ ¹ |
| | Slide-in-Side™ Wire Traps ⁴ | | ✓ | ✓ | ✓ |
| | Mounting Bar | ✓ ⁵ | ✓ | ✓ | ✓ |

¹ Overlay Trims sold separately. ² Available in QuickLink Low Voltage (Phase Cut or 0-10V) or Smart Wi-Fi® Connected by WiZ Pro versions. ³ Matte Black, Tuscan Bronze, Satin Nickel, and Paintable Matte White. ⁴ Slide-N-Side wire traps eliminate the need to use knockouts in most instances. Pre-wire outside of the jbox, fold down the tab(s), and insert non-metallic sheathed cable into the Slide-N-Side strain relief. ⁵ Mounting Bars are included with HLBSL but are sold separately for the HLBE Bulk Packs (HLBEMOUNT-12PK).

HLBSL & HLBE Slim Lite
CANLESS DOWNLIGHTS - 4" & 6"

- Matches the HLBPH with simplified features for budget-conscious installers
- HLBSL:** 5 Color Field-Selectable in 27/30/35/40/5000K; **HLBE:** dedicated in 3000K
- Only available in dead-front plastic frame and smooth lens
- Includes LED downlight and remote driver/junction box with mounting bar*
- 10% Phase Cut (LE/TE) Dimming, 35,000 hrs, 90+ CRI



| MarketPro Essentials | | Selectable CCT | | | | | | | |
|----------------------|--------------|----------------|-------------|---------|--------|-------|--------------|----------------|--|
| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID | |
| ES HLBSL406FS5 | 4" Downlight | 60W | 2700K-5000K | 120V | 725 | 8 | 080083297221 | 3706754 | |
| ES HLBSL609FS5 | 6" Downlight | 75W | 2700K-5000K | 120V | 915 | 10 | 080083297245 | 3706756 | |

Dedicated CCT & Lumens

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID | |
|--------------------------|------------------------|----------|-------|---------|--------|-------|--------------|----------------|--|
| ES HLBE4069301EMWR-12PK* | 4" Downlight (12-Pack) | 65W | 3000K | 120V | 740 | 10 | 080083265503 | 2405484 | |
| ES HLBE4069301EMWR-24PK* | 4" Downlight (24-Pack) | 65W | 3000K | 120V | 740 | 10 | 080083265527 | 2405484 | |
| ES HLBE6099301EMWR-12PK* | 6" Downlight (12-Pack) | 70W | 3000K | 120V | 1,025 | 13 | 080083265541 | 2405486 | |
| ES HLBE6099301EMWR-24PK* | 6" Downlight (24-Pack) | 70W | 3000K | 120V | 1,025 | 13 | 080083265565 | 2405486 | |

*HLBE: mounting bar 12 packs sold separately (HLBEMOUNT-12PK).

HLB & HLBPH Slim
CANLESS DOWNLIGHTS - 3", 4", 6", 8" & 12"

- An ultra-thin flange and sleek 1/2"-thin downlight design that fits under any obstruction
- HLB:** Die-cast trim & low-glare prismatic lens; **HLBPH:** Dead-front trim & smooth lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID | |
|-------------------|-----------------------------------|----------|----------------|-----------|----------------------------------|----------|--------------|----------------|--|
| HLB3059FS1EMWR | 3" Downlight, Round | 40W | 2700K-5000K | 120V | 575 | 9 | 080083151301 | 2370657 | |
| HLB3S059FS1EMWR | 3" Downlight, Square | 40W | 2700K-5000K | 120V | 595 | 9 | 080083151325 | N/A | |
| HLB4LSFS5 | 4" Downlight, Round | 60W | 2700K-5000K | 120V | 700/850/1000 (Lumen Select) | 10 | 080083297306 | 3706760 | |
| HLB4SP069FS1EMWR | 4" Downlight, Square (Round Hole) | 65W | 2700K-5000K | 120V | 650 | 10 | 080083909667 | 2347583 | |
| HLB6LSFS5 | 6" Downlight, Round | 75W | 2700K-5000K | 120V | 800/1000/1200 (Lumen Select) | 13 | 080083297320 | 3706764 | |
| HLB6S099FS1EMWR | 6" Downlight, Square | 70W | 2700K-5000K | 120V | 975 | 12 | 080083863389 | 2331663 | |
| HLB8169FS1EMWR | 8" Downlight, Round | 100W | 2700K-5000K | 120V | 1,760 | 21 | 080083150601 | 2358047 | |
| HLB4069FSE010MWR | 4" Downlight, Round (0-10V) | 65W | 2700K-5000K | 120-277V | 790 | 11 | 080083912261 | 2351376 | |
| HLB4S069FSE010MWR | 4" Downlight, Square (0-10V) | 65W | 2700K-5000K | 120-277V | 725 | 11 | 080083912308 | N/A | |
| HLB6099FSE010MWR | 6" Downlight, Round (0-10V) | 70W | 2700K-5000K | 120-277V | 1,060 | 15 | 080083912285 | 2351377 | |
| HLB6S099FSE010MWR | 6" Downlight, Square (0-10V) | 70W | 2700K-5000K | 120-277V | 975 | 15 | 080083912322 | N/A | |
| HLB8LS9FSE010MWR | 8" Downlight, Round (0-10V) | 90-150W | 2700K-5000K | 120-277V | 1,400/1,900/2,400 (Lumen Select) | 17/25/32 | 080083083367 | 2358045 | |
| HLB12LS9FSE010MWR | 12" Downlight, Round (0-10V) | 90-150W | 2700K-5000K | 120- 277V | 1,300/1,900/2,300 (Lumen Select) | 17/25/32 | 080083088782 | N/A | |
| HLBPH4069FS1EMWR | 4" Downlight, Round | 65W | 2700K-5000K | 120V | 805 | 10 | 080083190003 | 2385132 | |
| HLBPH6099FS1EMWR | 6" Downlight, Round | 70W | 2700K-5000K | 120V | 1,015 | 14 | 080083190027 | 2385133 | |

HLBC/HLBC+ Slim Regressed
CANLESS DOWNLIGHTS - 4" & 6"


- HLBC:** Set lumens + canless install; **HLBC+:** Lumen Select + 2-in-1 Canless-to-Can install!
- 1/2"-thin fixture with baffle die-cast trim & regressed low-glare prismatic lens
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | Energy Star ID | |
|-------------------------|---|----------|-----------------|----------|-------------------|-----------|--------------|----------------|--|
| HLBC4LS9FSD2W1EMWR | 4" Downlight, 2-in-1 Install | 60-70W | 2700K-5000K+D2W | 120V | 600/900 | 9/13 | 080083263097 | 2406536 | |
| HLBC4LS9FSD2W1EMWR-CA | 4" Downlight, 2-in-1 Install, CA T20 | 60-70W | 2700K-5000K+D2W | 120V | 600/900 | 9/13 | 080083267927 | 2406535 | |
| HLBC4LS9FSD2WE010MWR | 4" Downlight, 2-in-1 Install (0-10V) | 60-70W | 2700K-5000K+D2W | 120-277V | 600/900 | 8.5/13 | 080083263233 | 2406530 | |
| HLBC4LS9FSD2WE010MWR-CA | 4" Downlight, 2-in-1 Install, CA T20, (0-10V) | 60-70W | 2700K-5000K+D2W | 120-277V | 600/900 | 8.5/13 | 080083267965 | 2406529 | |
| HLBC6LS9FSD2W1EMWR | 6" Downlight, 2-in-1 Install | 70-75W | 2700K-5000K+D2W | 120V | 900/1,200 | 11/16 | 080083263219 | 2406539 | |
| HLBC6LS9FSD2W1EMWR-CA | 6" Downlight, 2-in-1 Install, CA T20 | 70-75W | 2700K-5000K+D2W | 120V | 900/1,200 | 11/16 | 080083267941 | 2406538 | |
| HLBC6LS9FSD2WE010MWR | 6" Downlight, 2-in-1 Install (0-10V) | 70-75W | 2700K-5000K+D2W | 120-277V | 900/1,200 | 11.5/16.5 | 080083263257 | 2406534 | |
| HLBC6LS9FSD2WE010MWR-CA | 6" Downlight, 2-in-1 Install, CA T20 (0-10V) | 70-75W | 2700K-5000K+D2W | 120-277V | 900/1,200 | 11.5/16.5 | 080083267989 | 2406532 | |
| HLBC4069FSD2W1EMW | 4" Downlight, Canless Only | 60W | 2700K-5000K+D2W | 120V | 675 (Dedicated) | 8 | 080083263059 | 2406524 | |
| HLBC6099FSD2W1EMW | 6" Downlight, Canless Only | 70W | 2700K-5000K+D2W | 120V | 1,010 (Dedicated) | 12 | 080083263073 | 2406527 | |

CANLESS DOWNLIGHT Product Selection Guide

| Good | | | | | Better | | | | | Best | | | | |
|----------------------------------|--|---|--|--|-------------------------|--|--|---|--|---|--|---|--|--|
| | | | | | | | | | | | | | | |
| MarketPro Essentials | | | | | MarketPro Essentials | | | | | | | | | |
| DOWNLIGHTS | | | | | ADJUSTABLES | | | | | | | | | |
| LT Canless | | | | | CJB/CJB+ Canless/2-in-1 | | | | | RL, RLFR, RL Night Light Canless | | | | |
| HLA Canless | | | | | RA Canless | | | | | RLS Slope Canless | | | | |
| Fixture Types | | Recessed Downlights | | Slim Downlight with Attached Jbox + 2-in-1 Canless-to-Can Versions Available | | Recessed Downlights, Fire Rated Downlight, & Downlight + Night Light | | Gimbal Adjustables (30° Tilt/360° Rotation) | | Gimbal Adjustables (35° Tilt/360° Rotation) | | Regressed Slope Adjustable (9-45° Tilt) | | |
| Sizes (Round) | | 3", 4", 6" | | 4", 6" | | 4", 6" | | 3", 4" | | 4", 6" | | 4", 6" | | |
| Trim & Lens | | Baffle or Smooth Trim w/ Flat Lens | | Slim Trim w/ Flat Smooth Lens | | Baffle Trim w/ Curved Lens (NL has Transparent Trim) | | Low-glare Prismatic or Smooth Lens | | Baffle Trim w/ Flat Lens | | Deep Baffle Trim w/ Integrated Optic | | |
| Max Lumens (By size @ 3000K) | | 570, 645, 785 | | 745, 920 | | 955, 1,300 (Lumen Select, Dedicated) (NL: 780, 1,020) | | 710 | | Lumen Select 4" - 600/900 6" - 600/900 | | 960, 1,630 | | |
| Color Temperatures (CCT) | | 3CCT 27/30/3500K, 30/40/5000K, Dedicated: 3000K | | 5 CCT 27/30/35/40/ 5000K | | 5 CCT w/ D2W D2W/27/30/35/40/ 5000K (NL: 2000K) | | 5 CCT 27/30/35/40/ 5000K | | 5 CCT w/ D2W D2W/27/30/35/ 40/5000K | | 5 CCT 27/30/35/40/ 5000K | | |
| Dimming Phase Cut (LE/TE)/0-10V | | 10% Phase Cut¹ | | 10% Phase Cut | | 5% Phase Cut, 0-10V², ³ (NL: 5% Phase Cut - Both zones) | | 5% Phase Cut | | 5% Phase Cut³ | | 5% Phase Cut | | |
| Estimated Life Hours | | 35,000 | | 35,000 | | 70,000 (RLFR & RLNL: 50,000) | | 50,000 | | 50,000 | | 50,000 | | |
| Input Voltage | | 120V | | 120V | | 120V | | 120V | | 120V | | 120V | | |
| Fits Mounting Frames/Smash Plate | | ✓ | | ✓ | | ✓ | | ✓ | | ✓ | | ✓ | | |
| Decorative Overlays⁴ | | ✓ | | | | (RL only) | | ✓ | | | | | | |
| Slide-in-Side™ Wire Traps⁵ | | | | | | ✓ | | ✓ | | ✓ | | ✓ | | |
| Mounting Bar | | ✓ | | | | ✓ | | ✓ | | ✓ | | ✓ | | |



RL Night Light
CANLESS DOWNLIGHTS & RECESSED LED TRIMS - 4" & 6"

- 2 Modes: Downlight for general illumination and Night Light with gentle glow (2000K)
- Dead-front plastic trim with smooth splay and curved lens
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K); Night Light CCT: Warm glow 2000K
- 5% Dimming (Phase Cut LE/TE), 70,000 hrs, 90+ CRI



Canless LED Downlights with remote/driver/junction box

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|---------------------|----------------------------|----------|---|---------|--------|-------|--------------|----------------|
| RLNL4079FSD2W1EWHDM | 4" Night Light + Downlight | 65W | 2700K-5000K + D2W + Night Light (2000K) | 120V | 780 | 9 | 080083265039 | 2403400 |
| RLNL6109FSD2W1EWHDM | 6" Night Light + Downlight | 70W | 2700K-5000K + D2W+ Night Light (2000K) | 120V | 1,020 | 12 | 080083265053 | 2403403 |

Recessed LED Trims with E26 medium socket adapter, and mounting hardware (4"-friction blades and 5"/6"-torsion springs & friction blades)

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|--------------------|------------------------------------|----------|---|---------|--------|-------|--------------|----------------|
| RLNL4079FSD2W1EWH | 4" Night Light + Downlight Trim | 65W | 2700K-5000K + D2W + Night Light (2000K) | 120V | 775 | 8 | 080083268047 | 2409525 |
| RLNL56109FSD2W1EWH | 5"/6" Night Light + Downlight Trim | 75W | 2700K-5000K + D2W + Night Light (2000K) | 120V | 1,065 | 11 | 080083268061 | 2409524 |

RL Recessed Baffle Trim
CANLESS DOWNLIGHTS - 4" & 6"

- The perfect balance of value and visual comfort, available as a canless direct mount
- Die-cast aluminum baffle trim with curved lens and selectable lumen options
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- LED downlight with remote driver/junction box
- 5% Phase Cut (LE/TE) Dimming, 70,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|-------------------|---------------------|----------|-----------------|---------|-----------------|----------|--------------|----------------|
| RL4LS9FSD2W1EWHDM | 4" Baffle Downlight | 60-70W | 2700K-5000K+D2W | 120V | 600/900 | 7.5/11.5 | 080083258901 | 2403141 |
| RL6069FSD2W1EWHDM | 6" Baffle Downlight | 60W | 2700K-5000K+D2W | 120V | 750 (Dedicated) | 7 | 080083258963 | 2402947 |
| RL6LS9FSD2W1EWHDM | 6" Baffle Downlight | 70-75W | 2700K-5000K+D2W | 120V | 900/1,200 | 10/14 | 080083258987 | 2403144 |

HLA Adjustable Gimbal
CANLESS DOWNLIGHTS - 4"

- Aim lighting where you want it with 360° of rotation and 30° of tilt
- Ideal for shallow plenum spaces - requires only 1-1/2" above the ceiling
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



MarketPro Essentials

| Catalog Number | Description | Replaces Up To | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|-----------------------|----------------------------|----------------|----------------|---------|--------|-------|--------------|----------------|
| ES HLA406FL9FS1EMWR | 4" Adjustable Direct Mount | 60W | 2700K-5000K | 120V | 710 | 11 | 080083882960 | 2341271 |
| ES HLA406VWFL9FS1EMWR | 4" Adjustable Direct Mount | 60W | 2700K-5000K | 120V | 710 | 11 | 080083863600 | 2333844 |

RA Baffle Trim Adjustable Gimbal
CANLESS DOWNLIGHTS - 4" & 6"

- Aim lighting where you want it with 360° of rotation and 35° of tilt
- Regressed baffle for increased cutoff
- 6-Position Switch: 5-Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | Energy Star ID |
|-------------------|--------------------------------|----------|-------------------|---------|-------------------|-------|--------------|----------------|
| RA4LS9FSD2W1EWHDM | 4" Adjustable Baffle Downlight | 65W | 2700K-5000K + D2W | 120V | 600/900 | 9 | 080083283019 | 2351865 |
| RA6LS9FSD2W1EWHDM | 6" Adjustable Baffle Downlight | 65W | 2700K-5000K + D2W | 120V | 600/900 | 9 | 080083283033 | 2351876 |

RLS Slope Recessed Baffle Trim Adjustable
CANLESS DOWNLIGHTS - 4" & 6"

- Tilt the adjustment mechanism from 9° to 45° to match ceiling pitches from 2/12 to 12/12
- Better lighting and improved visual comfort with its integrated optic and regressed light engine
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|--|----------|----------------|---------|--------|-------|--------------|----------------|
| RLS4099FS1EWHDMR | 4" Slope Ceiling Recessed Downlight, white | 70W | 2700K-5000K | 120V | 960 | 11 | 080083190300 | 2382794 |
| RLS6159FS1EWHDMR | 6" Slope Ceiling Recessed Downlight, white | 150W | 2700K-5000K | 120V | 1,630 | 19 | 080083190324 | 2382795 |
| RLS4099FS1EMBDMR | 4" Slope Ceiling Recessed Downlight, black | 70W | 2700K-5000K | 120V | 960 | 11 | 080083293452 | 2382794 |
| RLS6159FS1EMBDMR | 6" Slope Ceiling Recessed Downlight, black | 150W | 2700K-5000K | 120V | 1,630 | 19 | 080083293476 | 2382795 |

RLFR Fire-rated Recessed Baffle Trim
CANLESS DOWNLIGHTS - 4" & 6"

- Prevent the passage of flames & toxic gases for up to 2 hours
- Die-cast aluminum baffle trim and curved lens
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED downlight and remote driver/junction box with mounting bar
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|---------------------------------------|--------|----------|----------------|---------|--------|-------|--------------|----------------|
| RLFRC4FS | 4" Fire Rated Baffle Downlight, white | White | 70W | 2700K-5000K | 120V | 1,000 | 11 | 080083295838 | 3549872 |
| RLFRC4FSMBB | 4" Fire Rated Baffle Downlight, black | Black | 70W | 2700K-5000K | 120V | 900 | 11 | 080083295876 | 3549872 |
| RLFRC6FS | 6" Fire Rated Baffle Downlight, white | White | 75W | 2700K-5000K | 120V | 1,400 | 13 | 080083295852 | 3549873 |
| RLFRC6FSMBB | 6" Fire Rated Baffle Downlight, black | Black | 75W | 2700K-5000K | 120V | 1,200 | 13 | 080083295890 | 3549873 |

HALO®

4" Junction Box Housing

The solution for new construction fire-rated ceilings

Suitable for use in fire-rated ceiling construction that requires up to 2-hour protection per International Building Code Section 714.

Compatible with all 4" HALO LED Trims

Compatible with any HALO Surface Mount Fixture

[CLICK HERE](#) to learn more

JBox Housing - 4"

- For use with all 4" HALO Recessed LED Trims and any HALO Surface Mount Fixture
- Meets UL514A Metallic Outlet Box
- Pass-N-Thru™ hangar bars allow for toolless shortening in tight spaces (7" to 24")
- For installation in insulated contact (IC) and non-IC ceilings
- All-Nail!™ preinstalled nail and integral T-grid clips allow for easy single-person installation



| Catalog Number | Description | Voltage | UPC |
|----------------|--|----------|--------------|
| JB4FR2 | 4" Junction Box Housing for use in standard or fire-rated ceilings | 120-277V | 080083290307 |

1. Use with T24-listed LED trims or surface mount fixtures.
2. Can be used to meet requirement when used with AIR-TITE or wet location-listed LED trim or surface mount fixture.

Source Lighting Education Center

The benchmark for lighting educational facilities and programs for 30 years.



Expand Your Knowledge!

The SOURCE is an excellent resource for training and professional development. As the industry's leading lighting educational facility, the SOURCE offers numerous online and instructor-led courses and workshops for those wanting to expand their lighting and controls knowledge.



- Instructor-led Classes
- Free Online Courses
- Continuing Education
- reSource Articles

To start learning today, visit:
cooperlighting.com/global/resources/source-lighting-education

HALO SURFACE MOUNT DOWNLIGHTING

Suitable for a variety of applications!

- Below the ceiling installation with no plates or clips required
- Designed for square, octagon, pancake or round junction boxes
- Ideal for closets, storage areas, attics and basements

Quick and Easy Installation



HALO SURFACE MOUNT DOWNLIGHT Product Selection Guide

| | | Good Better Best | | | | | |
|----------------------|-----------------------------------|--|---|---|---|---------------------------------------|---|
| | | | | | | | |
| | | MarketPro Essentials | | | | | |
| | | HLCE | HLS | FM | JBD | SMD | SMX |
| FEATURES/PERFORMANCE | Size / Shape | 4", 6" | 4", 6", 9", 9" w/ Motion Round | 8", 11", 15" Round | 4" Round, Square | 4", 6" Round, Square | 4", 6", 8", 14", 18" Round, Square ³ |
| | Trim & Lens | Curved Trim & Lens | Curved Trim with Chamfered Edge & Curved Lens | Full-lensed Flushmount | Interchangeable Flat/Baffle, Round/Square Trims or Full Lens Diffuser | Square-Edge Trim, Flange, & Flat Lens | Thin Frame and Edgeless Luminous Lens |
| | Max Lumens (By size @ 3000K) | 1,000, 1,200 | 785, 935, 1,265 | 920, 1,250, 1,510 | 715 | 740, 800 | Lumen Select 4" - 650/800/1,000 6" - 750/900/1,200 8" - 900/1,200/1,500 14" - 1,200/1,600/2,000 18" - 1,500/2,000/2,500 |
| | Color Temperatures (CCT) | 5 CCT 27/30/35/40/5000K Dedicated: 3000K, 4000K, 5000K | 5 CCT 27/30/35/40/5000K | 3 CCT 30/40/5000K, 5 CCT 27/30/35/40/5000K | 5 CCT 27/30/35/40/5000K | 5 CCT 27/30/35/40/5000K | 5 CCT w/ D2W D2W/27/30/35/40/5000K |
| CONTROL | Dimming Phase Cut (LE/TE) / 0-10V | 10% Phase Cut | 10% Phase Cut ¹ | 10% Phase Cut | 5% Phase Cut | 5% Phase Cut, 0-10V | 5% Phase Cut, 0-10V |
| | Estimated Life Hours | 35,000 | 35,000 | 50,000 | 50,000 | 50,000 | 50,000 |
| | Input Voltage | 120V | 120V | 120V | 120V | 120V | 120V, 120-277V |
| HARDWARE | Decorative Overlays ² | ✓ | ✓ | | ✓ (Round or Square, Flat or Baffle Options) | ✓ | ✓ |

¹ Motion sensing downlights are not dimmable. ² Matte Black, Tuscan Bronze, Satin Nickel, and Paintable Matte White. ³ 4", 6", 8" Squares and 0-10V versions available July 2025

HALO SURFACE MOUNT DOWNLIGHTING

HLCE Disk Lights
SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Damp-rated ultra-thin surface mount disk downlight with fast installation
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K; dedicated in 3000K, 4000K, or 5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit in non-California versions
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI
- NEW! Decorative overlays are available through MarketPro online



| MarketPro Essentials | | Selectable 5-CCT | | | | | | |
|----------------------|---|------------------|-------------|---------|--------|-------|--------------|----------------|
| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
| ES HLCE4079FS1E | 4" Disk Light (Damp-listed) | 70W | 2700K-5000K | 120V | 1040 | 9 | 080083286904 | 3477929 |
| ES HLCE4079FS1E-18P | 4" Disk Light (Damp-listed) (18-Pk) | 70W | 2700K-5000K | 120V | 1040 | 9 | 080083286744 | 3477930 |
| ES HLCE4079FS1E-CA | 4" Disk Light (Damp-listed), CA T20 | 70W | 2700K-5000K | 120V | 1040 | 9 | 080083286942 | 3477931 |
| ES HLCE4079FS-18P-CA | 4" Disk Light (Damp-listed) (18-Pk), CA T20 | 70W | 2700K-5000K | 120V | 1040 | 9 | 080083286829 | 3477931 |
| ES HLCE6129FS1E | 6" Disk Light (Damp-listed) | 75W | 2700K-5000K | 120V | 1220 | 10 | 080083286928 | 3477933 |
| ES HLCE6129FS1E-18P | 6" Disk Light (Damp-listed) (18-Pk) | 75W | 2700K-5000K | 120V | 1220 | 10 | 080083286768 | 3477934 |
| ES HLCE6129FS1E-CA | 6" Disk Light (Damp-listed), CA T20 | 75W | 2700K-5000K | 120V | 1220 | 10 | 080083286966 | 3477932 |
| ES HLCE6129FS-18P-CA | 6" Disk Light (Damp-listed) (18-Pk), CA T20 | 75W | 2700K-5000K | 120V | 1220 | 10 | 080083286843 | 3477932 |

| MarketPro Essentials | | Dedicated CCT & Lumens | | | | | | |
|-----------------------|---|------------------------|-------|---------|--------|-------|--------------|----------------|
| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
| ES HLCE4079301EWH-18P | 4" Disc Light (Damp-listed) (18-Pack) | 70W | 3000K | 120V | 815 | 10.8 | 080083276844 | 2470915 |
| ES HLCE407930-18P-CA | 4" Disk Light (Damp-listed) (18-Pk), CA T20 | 70W | 3000K | 120V | 815 | 10.8 | 080083276929 | 2470916 |
| ES HLCE4079401EWH-18P | 4" Disc Light (Damp-listed) (18-Pack) | 70W | 4000K | 120V | 810 | 10.3 | 080083287246 | 2839424 |
| ES HLCE407940-18P-CA | 4" Disk Light (Damp-listed) (18-Pk), CA T20 | 70W | 4000K | 120V | 810 | 10.3 | 080083287321 | 2839423 |
| ES HLCE4079501EWH-18P | 4" Disc Light (Damp-listed) (18-Pack) | 70W | 5000K | 120V | 820 | 10.4 | 080083287406 | 2839422 |
| ES HLCE6099301EWH-18P | 6" Disc Light (Damp-listed) (18-Pack) | 75W | 3000K | 120V | 940 | 13.6 | 080083276868 | 2470917 |
| ES HLCE609930-18P-CA | 6" Disk Light (Damp-listed) (18-Pk), CA T20 | 75W | 3000K | 120V | 940 | 13.6 | 080083276943 | 2470918 |
| ES HLCE6099401EWH-18P | 6" Disc Light (Damp-listed) (18-Pack) | 70W | 4000K | 120V | 990 | 13.2 | 800083287260 | 2839426 |
| ES HLCE609940-18P-CA | 6" Disk Light (Damp-listed) (18-Pk), CA T20 | 70W | 4000K | 120V | 990 | 13.2 | 080083287345 | 2839425 |
| ES HLCE6099501EWH-18P | 6" Disk Light (Damp-listed) (18-Pk) | 70W | 5000K | 120V | 985 | 13.1 | 080083287420 | 2839427 |

HLS Disk Lights
SURFACE MOUNT DOWNLIGHTS - 4", 6", & 9"

- Wet-rated ultra-thin disk light with chamfered rim (9" motion sensing version available)
- Installs in most 3-1/2" or 4" ceiling junction and pancake boxes (or retrofits into housings)
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit in non-California versions
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI
- NEW! Decorative overlays are available through MarketPro online



Selectable 5-CCT

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|--|----------|-------------|---------|--------|-------|--------------|----------------|
| HLS4079FS1E-6BP | 4" Disk Light (6-Pk) | 65W | 2700K-5000K | 120V | 750 | 9 | 080083286980 | 3531006 |
| HLS4079FS1E-12BP | 4" Disk Light (12-Pk) | 65W | 2700K-5000K | 120V | 750 | 9 | 080083287000 | 3531006 |
| HLS6099FS1E-6BP | 6" Disk Light (6-Pk) | 70W | 2700K-5000K | 120V | 900 | 10.6 | 080083287024 | 3531008 |
| HLS6099FS1E-12BP | 6" Disk Light (12-Pk) | 70W | 2700K-5000K | 120V | 900 | 10.6 | 080083287048 | 3531008 |
| HLS9129FS1E | 9" Disk Light | 75W | 2700K-5000K | 120V | 1,200 | 16.1 | 080083287062 | N/A |
| HLS9129FS1E-CA | 9" Disk Light, CA T20 | 75W | 2700K-5000K | 120V | 1,200 | 16.1 | 080083287086 | N/A |
| HLSMS9129FS1E | 9" Disk Light with Motion Sensor | 75W | 2700K-5000K | 120V | 1,200 | 16 | 080083287109 | N/A |
| HLSMS9129FS1E-CA | 9" Disk Light with Motion Sensor, CA T20 | 75W | 2700K-5000K | 120V | 1,200 | 16 | 080083287123 | N/A |

FM Full-lensed
FLUSHMOUNTS - 8", 11", & 15"

- LED flushmount installs in most 3-1/2" or 4" junction boxes or retrofits 5" and 6" recessed housings
- Round die-formed lens design with 360-degrees of light distribution
- 3 Color Field-Selectable in 30/40/5000K (8" fixture) or 5 Color Field-Selectable in 27/30/35/40/5000K (11" & 15" fixtures)
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit
- 10% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|----------------|----------|----------------|---------|--------|-------|--------------|----------------|
| FM89S1EWHR | 8" Flushmount | 70W | 3000K-5000K | 120V | 920 | 10 | 080083256587 | 2399871 |
| FM119S1EWHR | 11" Flushmount | 75W | 2700K-5000K | 120V | 1,250 | 18 | 080083257706 | 2399874 |
| FM159S1EWHR | 15" Flushmount | 100W | 2700K-5000K | 120V | 1,510 | 14 | 080083257720 | 2399877 |

JBD Slim
SURFACE MOUNT DOWNLIGHTS - 4"

- Ultra-thin surface mount downlight with smooth flat lens
- Ceiling or wall mounting in compatible 4" junction boxes or recessed housings
- Interchangeable round, square, and full-lensed designer trims in multiple finishes
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit in non-California versions
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|--|--------|----------|----------------|---------|--------|-------|--------------|----------------|
| JBD4079FS1EWH | 4" Slim Light w/ Round Matte White Trim | White | 65W | 2700K-5000K | 120V | 715 | 10 | 080083283514 | 2567962 |
| JBD4079FS1EWH-CA | 4" Slim Light w/ Round Matte White Trim , CA T20 | White | 65W | 2700K-5000K | 120V | 715 | 10 | 080083285631 | 2567961 |

Accessories (optional)

| Catalog Number | Description | Finish | UPC |
|----------------|-----------------------|---------------|--------------|
| JBD4TRMMW | 4" Round Flat Trim | Matte White | 080083283538 |
| JBD4TRMMB | 4" Round Flat Trim | Matte Black | 080083283590 |
| JBD4TRMSN | 4" Round Flat Trim | Satin Nickel | 080083283552 |
| JBD4TRMTBZ | 4" Round Flat Trim | Tuscan Bronze | 080083283576 |
| JBD4STRMMW | 4" Square Flat Trim | Matte White | 080083285679 |
| JBD4STRMMB | 4" Square Flat Trim | Matte Black | 080083285730 |
| JBD4STRMSN | 4" Square Flat Trim | Satin Nickel | 080083285693 |
| JBD4STRMTBZ | 4" Square Flat Trim | Tuscan Bronze | 080083285716 |
| JBD4TRMMWB | 4" Round Baffle Trim | Matte White | 080083291311 |
| JBD4TRMMBB | 4" Round Baffle Trim | Matte Black | 080083291373 |
| JBD4TRMSNB | 4" Round Baffle Trim | Satin Nickel | 080083291335 |
| JBD4TRMTBZB | 4" Round Baffle Trim | Tuscan Bronze | 080083291359 |
| JBD4STRMMWB | 4" Square Baffle Trim | Matte White | 080083291397 |
| JBD4STRMMBB | 4" Square Baffle Trim | Matte Black | 080083291458 |
| JBD4STRMSNB | 4" Square Baffle Trim | Satin Nickel | 080083291410 |
| JBD4STRMTBZB | 4" Square Baffle Trim | Tuscan Bronze | 080083291434 |
| JBD4DIFF | 4" Full Lens Diffuser | Diffuser | 080083283613 |

Smooth Flat Trims

JBD4TRMMW

Paintable

Matte White

JBD4TRMMB

Matte Black

JBD4TRMSN

Satin Nickel

JBD4TRMTBZ

Tuscan Bronze

JBD4STRMMW

Paintable

Matte White

JBD4STRMMB

Matte Black

JBD4STRMSN

Satin Nickel

JBD4STRMTBZ

Tuscan Bronze

Regressed Baffle Trims

JBD4TRMMWB

Paintable

Matte White

JBD4TRMMBB

Matte Black

JBD4TRMSNB

Satin Nickel

JBD4TRMTBZB

Tuscan Bronze

JBD4STRMMWB

Paintable

Matte White

JBD4STRMMBB

Matte Black

JBD4STRMSNB

Satin Nickel

JBD4STRMTBZB

Tuscan Bronze

JBD4DIFF

Full Lens Diffuser

SMD Square Edge
SURFACE MOUNT DOWNLIGHTS - 4" & 6"

- Round or square surface mount downlight with squared edge design
- Ceiling or wall mounting in compatible junction boxes or retrofit into recessed housings
- 5 Color Field-Selectable in 27/30/35/40/5000K
- Includes LED Downlight, jbox mounting and wiring hardware, and housing retrofit kit
- 5% Dimming (Phase Cut), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|-----------------------------------|----------|----------------|---------|--------|-------|--------------|----------------|
| SMD4R07FS5 | 4" Surface Mount, Round | 65W | 2700K-5000K | 120V | 737 | 8 | 080083305667 | 3892052 |
| SMD4S07FS5 | 4" Surface Mount, Square | 65W | 2700K-5000K | 120V | 741 | 8 | 080083305681 | 3892050 |
| SMD6R07FS5 | 6" Surface Mount, Round | 75W | 2700K-5000K | 120V | 800 | 8 | 080083305742 | 3892058 |
| SMD6S07FS5 | 6" Surface Mount, Square | 75W | 2700K-5000K | 120V | 710 | 8 | 080083305766 | 3892054 |
| SMD4R07FS5-6PK | 4" Surface Mount, Round (6-Pack) | 65W | 2700K-5000K | 120V | 737 | 8 | 080083305704 | 3892052 |
| SMD4S07FS5-6PK | 4" Surface Mount, Square (6-Pack) | 65W | 2700K-5000K | 120V | 741 | 8 | 080083305728 | 3892050 |
| SMD6R07FS5-6PK | 6" Surface Mount, Round (6-Pack) | 75W | 2700K-5000K | 120V | 800 | 8 | 080083305780 | 3892058 |
| SMD6S07FS5-6PK | 6" Surface Mount, Square (6-Pack) | 75W | 2700K-5000K | 120V | 710 | 8 | 080083305803 | 3892054 |

SMX Edgeless
SURFACE MOUNT DOWNLIGHTS - 4", 6", 8" 14" & 18"

- A bright fully luminous lens face and sleek edgeless design blends effortlessly into any ceiling
- Ceiling or wall mounting in compatible junction boxes or recessed housings
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes j-box mounting and wiring hardware
- 5% Dimming (Phase Cut or 0-10V), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | Energy Star ID |
|----------------|-----------------------------------|----------|-------------------|----------|-------------------|----------|--------------|----------------|
| SMX4RLSFS2W | 4" Surface Mount, Round | 65-90W | 2700K-5000K + D2W | 120V | 650/800/1000 | 7/8/11 | 080083292202 | 3701850 |
| SMX6RLSFS2W | 6" Surface Mount, Round | 75-100W | 2700K-5000K + D2W | 120V | 750/900/1200 | 7/9/13 | 080083292240 | 3701854 |
| SMX8RLSFS2W | 8" Surface Mount, Round | 90-120W | 2700K-5000K + D2W | 120V | 900/1200/1500 | 10/12/16 | 080083294039 | 3701851 |
| SMX14RLSFS2W | 14" Surface Mount, Round | 90-150W | 2700K-5000K + D2W | 120V | 1200/1600/2000 | 16/21/26 | 080083292141 | N/A |
| SMX14SLSFS2W | 14" Surface Mount, Square | 90-150W | 2700K-5000K + D2W | 120V | 1200/1600/2000 | 16/21/26 | 080083292349 | N/A |
| SMX14RLSFS010 | 14" Surface Mount, Round (0-10V) | 90-150W | 2700K-5000K | 120-277V | 1200/1600/2000 | 16/21/26 | 080083292424 | N/A |
| SMX14SLSFS010 | 14" Surface Mount, Square (0-10V) | 90-150W | 2700K-5000K | 120-277V | 1200/1600/2000 | 16/21/26 | 080083292509 | N/A |
| SMX18RLSFS2W | 18" Surface Mount, Round | 90-150W | 2700K-5000K + D2W | 120V | 1500/2000/2500 | 17/24/30 | 080083292165 | N/A |
| SMX18SLSFS2W | 18" Surface Mount, Square | 90-150W | 2700K-5000K + D2W | 120V | 1500/2000/2500 | 17/24/30 | 080083292363 | N/A |
| SMX18RLSFS010 | 18" Surface Mount, Round (0-10V) | 90-150W | 2700K-5000K + D2W | 120-277V | 1500/2000/2500 | 17/24/30 | 080083292448 | N/A |
| SMX18SLSFS010 | 18" Surface Mount, Square (0-10V) | 90-150W | 2700K-5000K + D2W | 120-277V | 1500/2000/2500 | 17/24/30 | 080083292523 | N/A |



Superior solutions for functionality and delivery!



Stay ahead of demanding project schedules

We've consolidated all legacy quick shipment programs (i.e. Rapid Response, Quick Ship, Rapid Ship) into one program. Quick Spec is your solution for fast-moving construction projects that require quick access to information, a broad portfolio of lighting and control products plus **shipping in 10 days or less.**



QUICK INFORMATION

Save time finding important information, assets, and tools for your projects.



QUICK SOLUTIONS

Tap into a broad portfolio of spec grade products in one location.



QUICK SHIPPING

The 10-day lead time on select products caters to fast-moving construction projects.



Look for the Quick Spec logo above the MarketPro product tables identifying qualified products.

| Catalog Number | Description | Replaces Up To | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | MarketPro Product ID |
|-----------------------|-----------------------------|-------------------------|----------------|----------|-------------------|---------|--------------|----------------------|
| LMH01218-UM-L-B4750-U | Luminaire 1218-UM-L-B4750-U | 4-75W, 0-10V, 1700W MAX | 4000K-5000K | 120-277V | 11,000-16,000 | 80-124 | 080083274741 | S-JKMP1 |
| LMH01824-UM-L-B4750-U | Luminaire 1824-UM-L-B4750-U | 6-75W, 0-10V, 1700W MAX | 4000K-5000K | 120-277V | 16,000-24,000 | 119-156 | 080083274742 | S-JKMP2 |
| LMH02436-UM-L-B4750-U | Luminaire 2436-UM-L-B4750-U | 8-75W, 0-10V, 1700W MAX | 4000K-5000K | 120-277V | 24,000-36,000 | 150-246 | 080083274743 | S-JKMP3 |

CLICK HERE to learn more about Quick Spec.

RL Recessed Baffle
LED TRIMS - 3", 4", & 5"/6"

- Delivers long life, exceptional performance, selectable lumens, and installs into almost any recessed housing
- Die-cast aluminum baffle trim and curved lens reduces glare and provides a traditional downlight appearance
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (3" & 4" - friction blades and 5"/6" - torsion springs & friction blades)
- 5% Dimming (Phase Cut LE/TE), 70,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|-------------------|----------|-----------------|---------|--------------------------|--------|--------------|----------------|
| RL3059FSD2W1EWH | 3" Baffle Trim | 60W | 2700K-5000K+D2W | 120V | 610 | 6.4 | 080083257669 | 2402944 |
| RL4LS9FSD2W1EWH | 4" Baffle Trim | 60-70W | 2700K-5000K+D2W | 120V | 600/900 (Lumen Select) | 7/11 | 080083257683 | 2402940 |
| RL56069FSD2W1EWH | 5"/6" Baffle Trim | 60W | 2700K-5000K+D2W | 120V | 700 | 8 | 080083818525 | 2356074 |
| RL56LS9FSD2W1EWH | 5"/6" Baffle Trim | 70-75W | 2700K-5000K+D2W | 120V | 900/1,200 (Lumen Select) | 8.5/14 | 080083818549 | 2354587 |



LA Recessed Baffle Adjustable Gimbal
LED TRIMS - 4" & 5"/6"

- Adjustable retrofit aims lighting where you want it with 360° of rotation and 35° of tilt
- Regressed dead-front plastic baffle trim for improved cutoff
- Available in dedicated 3000K only
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (4"-friction blades; 5"/6"-torsion springs - only fits housings with spring receivers)
- 10% Dimming (Phase Cut LE/TE), 35,000 hrs, 90+ CRI



MarketPro Essentials

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|------------------------------|----------|-------|---------|--------|-------|--------------|----------------|
| ES LA4069301EWH | 4" Adjustable Gimbal Trim | 60W | 3000K | 120V | 610 | 9 | 080083818143 | 2325616 |
| ES LA56069301EWH | 5"/6" Adjustable Gimbal Trim | 60W | 3000K | 120V | 635 | 9 | 080083818242 | 2325606 |



RA Recessed Adjustable Gimbal Baffle
LED TRIMS - 3", 4", & 5"/6"

- Adjustable retrofit aims lighting where you want it with 360° of rotation and 35° of tilt and installs in almost any recessed housing
- Regressed die-cast aluminum baffle trim reduces glare and improves cutoff
- 6-Position Switch: 5 Color Field-Selectable (27/30/35/40/5000K) + Dim-to-Warm (3000K dims to 1800K)
- Included: Adjustable LED Trim, E26 medium socket adapter, and mounting hardware (4" - friction blades; 5"/6" - torsion springs & friction blades)
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|------------------------------|----------|-------------------|---------|------------------------|-------|--------------|------------------|
| RA3059FSD2W1EWH | 3" Adjustable Gimbal Trim | 60W | 2700K-5000K + D2W | 120V | 570 | 6 | 080083900954 | 2252183, 2277232 |
| RA4LS9FSD2W1EWH | 4" Adjustable Gimbal Trim | 60W | 2700K-5000K + D2W | 120V | 600/900 (Lumen Select) | 6/9 | 080083282975 | 2567964 |
| RA56LS9FSD2W1EWH | 5"/6" Adjustable Gimbal Trim | 60W | 2700K-5000K + D2W | 120V | 600/900 (Lumen Select) | 6/9 | 080083282999 | 2567965 |



HU11 LED Under Cabinet
 9", 18", 24", & 36"

- Sleek, low-profile LED under cabinet with less than 1" profile
- 3 Color Field-Selectable in 27/30/4000K
- 5% Dimming (Phase Cut LE/TE), 50,000 hrs, 90+ CRI



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|-------------------|----------|----------------|---------|--------|-------|--------------|----------------|
| HU1109D9SP | 9" Under Cabinet | 17W INC | 2700K-4000K | 120V | 300 | 5 | 080083875788 | 2341224 |
| HU1118D9SP | 18" Under Cabinet | 33W INC | 2700K-4000K | 120V | 560 | 8 | 080083875863 | 2341217 |
| HU1124D9SP | 24" Under Cabinet | 44W INC | 2700K-4000K | 120V | 785 | 11 | 080083875948 | 2341218 |
| HU1136D9SP | 36" Under Cabinet | 56W INC | 2700K-4000K | 120V | 1,125 | 16 | 080083876020 | 2341219 |

Traditional Recessed Trims
 4", 5", & 6"

- Traditional recessed trims install into recessed housings, are offered in a variety of styles, and accept different lamp types
- Trims shape light to minimize glare and reduce ceiling brightness
- Open trims focus the downlighting beam to provide uniform distribution
- Can be used in new construction or remodel housings



| Catalog Number | Description | Lamp Source | UPC |
|----------------|--|------------------------|--------------|
| 4001WB | 4" Step Baffle - Plastic | Halogen, INC, LED, CFL | 080083745869 |
| 993W | 4" Coilex Baffle | Halogen, INC, LED, CFL | 080083628483 |
| 5001P | 5" Metal Splay Baffle | Halogen, INC, LED, CFL | 662400602729 |
| 5125WB | 5" Full Cone Baffle | Halogen, INC, LED, CFL | 080083743162 |
| 300P | 6" Open - Socket Supporting | Halogen, INC, LED, CFL | 662400302421 |
| 30WAT | 6" Air-Tite Baffle | Halogen, INC, LED, CFL | 662400603320 |
| 310W | 6" Coilex Baffle | Halogen, INC, LED, CFL | 080083515882 |
| 456W | 6" Baffle for Slope Ceiling | Halogen, INC, LED, CFL | 662400676287 |
| 6100WB | 6" Tapered Metal Baffle, 2-Rings Narrow & Wide | Halogen, INC, LED, CFL | 080083743452 |
| 6125WB | 6" Full Cone Baffle | Halogen, INC, LED, CFL | 080083754465 |

HALO Housing Pallet

HALO Housing Pallet quantities are quick, convenient and easy to order.

E Series Housings - 4", 5", & 6"

Compact and efficient housings for new or retrofit residential or light commercial construction.

- Ideal for residential and light commercial applications
- Compatible with recessed LED trims or E26 socket-based lamps (bulbs)
- Optimized and listed for EISA compliant tungsten-halogen lamps along with incandescent, CFL, and LED lamps with E26 bases
- For installation in insulated contact (IC) and non-IC rated ceilings
- Available in 120V or 120-277V configurations



MarketPro Essentials LED Housings

| Catalog Number | Description | Connection | Voltage | Pallet Quantity | UPC |
|----------------|-------------------------------------|-------------------|----------|------------------|--------------|
| ES E750ICAT | 6" LED New Construction (No Socket) | LED Quick Connect | 120-277V | 144 (24 cartons) | 080083775040 |

MarketPro Essentials Traditional Housings

| Catalog Number | Description | Connection | Voltage | Pallet Quantity | UPC |
|----------------|---|------------|---------|------------------|--------------|
| ES E4ICATSB | 4" New Construction | E26 Socket | 120V | 144 (24 cartons) | 080083751525 |
| ES E5ICATNB | 5" New Construction | E26 Socket | 120V | 144 (24 cartons) | 080083737390 |
| ES E27ICAT | 6" Shallow New Construction | E26 Socket | 120V | 192 (32 cartons) | 080083737604 |
| ES E7ICAT | 6" New Construction | E26 Socket | 120V | 144 (24 cartons) | 080083737727 |
| ES E7ICATNB | 6" LED New Construction (No Socket Bracket) | E26 Socket | 120V | 144 (24 cartons) | 080083737697 |
| ES E7RICAT | 6" Remodel | E26 Socket | 120V | 144 (24 cartons) | 080083737543 |

H Series Housings - 4" & 6"

The industry standard recessed housing for commercial and residential applications.

- Ideal for commercial and residential applications
- Compatible with recessed LED trims or E26 socket-based lamps (bulbs)
- Optimized and listed for EISA compliant tungsten-halogen lamps along with incandescent, CFL, and LED lamps with E26 bases
- For installation in insulated contact (IC) and non-IC rated ceilings
- Available in 120V or 120-277V configurations



LED Housings

| Catalog Number | Description | Connection | Voltage | Pallet Quantity | UPC |
|----------------|---|-------------------|----------|------------------|--------------|
| H245ICAT | 4" LED Ultra-Shallow New Construction (No Socket) | LED Quick Connect | 120-277V | 180 (30 cartons) | 080083770717 |
| H245RICAT | 4" LED Ultra-Shallow Remodel (No Socket) | LED Quick Connect | 120-277V | 192 (32 cartons) | 080083756520 |
| H995ICAT | 4" LED Shallow New Construction (No Socket) | LED Quick Connect | 120-277V | 144 (24 cartons) | 080083616930 |
| H750ICAT | 6" LED New Construction (No Socket) | LED Quick Connect | 120-277V | 120 (20 cartons) | 623961872655 |




Traditional Housings

| Catalog Number | Description | Connection | Voltage | Qty / Single Catalog # | UPC |
|----------------|---|------------|---------|------------------------|--------------|
| H99ICAT | 4" Shallow Remodel | E26 Socket | 120V | 108 (18 cartons) | 080083582259 |
| H7ICAT | 6" New Construction | E26 Socket | 120V | 120 (20 cartons) | 080083609628 |
| H7ICATNB | 6" New Construction (No Socket Bracket) | E26 Socket | 120V | 120 (20 cartons) | 662400612032 |
| H7ICT | 6" New Construction | E26 Socket | 120V | 120 (20 cartons) | 080083609680 |







Circadian Rhythm



16 Million Colors



Tunable White



HALO is now available with WiZ and Matter!

Illuminate spaces with the perfect lighting. Set the mood with 16 million colors + white tuning using the WiZ App or preferred compatible voice assistant.

Introducing Matter, which allows you to control your WiZ fixtures from more than one smart platform, providing ultimate flexibility and an Open Platform.



RL Smart Wi-Fi® Baffle

CANLESS LED DOWNLIGHTS (Connected by WiZ Pro) - 4" & 6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app
- Fixtures provide 16 million colors and tunable white light from 2200-6500K
- Die-cast aluminum baffle trim reduces glare
- Includes LED downlight and remote driver/junction box with mounting bar
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|---|--------|---|---------|--------|-------|--------------|----------------|
| RLWZC409 | 4" Smart Baffle Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 900 | 10 | 080083298006 | 3626861 |
| RLWZC612 | 6" Smart Baffle Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 1,200 | 13 | 080083298020 | 3626862 |



RA Smart Wi-Fi® Baffle

CANLESS LED DOWNLIGHTS (Connected by WiZ Pro) - 4" & 6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app. Fixtures provide 16 million colors and tunable white light from 2200-6500K.
- Die-cast aluminum baffle trim reduces glare
- Includes LED downlight and remote driver/junction box with mounting bar
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|--|--------|---|---------|--------|-------|--------------|----------------|
| RAWZC409 | 4" Smart Adjustable Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 900 | 10.8 | 080083297863 | 3626859 |
| RAWZC610 | 5"/6" Smart Adjustable Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 1,000 | 10.8 | 080083297887 | 3626860 |




HLB Smart Wi-Fi® Slim

CANLESS LED DOWNLIGHTS (Connected by WiZ Pro) - 4" & 6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app
- Fixtures provide 16 million colors and tunable white light from 2200-6500K
- Dead-front plastic frame and smooth lens
- Includes LED downlight and remote driver/junction box with mounting bar
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|---|--------|---|---------|--------|-------|--------------|----------------|
| HLB4069WZRGBWMWR | 4" Smart Slim Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 600 | 9 | 080083255955 | 2408244 |
| HLB6099WZRGBWMWR | 6" Smart Slim Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 960 | 12 | 080083255931 | 2408245 |



RL Smart Wi-Fi® Recessed Baffle

LED TRIMS (Connected by WiZ Pro) - 4" & 5"/6"

- Set up with the WiZ app to wirelessly control lighting via WiZ app
- Fixtures provide 16 million colors and tunable white light from 2200-6500K
- Die-cast aluminum baffle trim reduces glare
- Includes LED Trim, E26 medium socket adapter, and mounting hardware (4" - friction blades and 5"/6" - torsion springs & friction blades)
- Wi-Fi® Control & Dimming to 5% via WiZ app, 50,000 hrs, 90+ CRI



| Catalog Number | Description | Finish | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|------------------|--|--------|---|---------|--------|-------|--------------|----------------|
| RL4069WZRGBWWHR | 4" Smart Baffle LED Trim (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 615 | 8 | 080083256167 | 2397256 |
| RL56069WZRGBWWHR | 5"/6" Smart Slim Canless Downlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 690 | 8 | 080083256143 | 2397259 |



ESF Smart Wi-Fi® Floodlight

OUTDOOR SECURITY (Connected by WiZ Pro)

- Set up with the WiZ app to wirelessly control lighting via WiZ app. Fixtures provide 16 million colors and tunable white light from 2200-6500K.
- Fixtures provide 16 million colors and tunable white light from 2200-6500K
- Includes LED floodlight with sleek design, perfect for outdoor ambiance and security
- Wi-Fi Control & Dimming to 5% via WiZ app, 50,000 hrs, wet-location rated, 88 CRI

| Catalog Number | Description | Finish | Selectable CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|-----------------|--|--------|---|---------|--------|-------|--------------|----------------|
| ESF2ARGBWF-BWiZ | Twin Head Smart Wi-Fi Floodlight (WiZ Pro) | Black | Full Color & Tunable White (2200-6500K) | 120V | 2,235 | 29 | 080083260300 | Pending |
| ESF2ARGBFW-BWiZ | Twin Head Smart Wi-Fi Floodlight (WiZ Pro) | White | Full Color & Tunable White (2200-6500K) | 120V | 2,445 | 29 | 080083260324 | Pending |





Flat Panels
p. 33-34



Troffers
p. 34-35



Strip Lights
p. 36



Wraps
p. 36-37

METALUX

COMMERCIAL LED LIGHTING

Metalux Commercial features a wide selection of affordable yet aesthetically pleasing fixtures with an expanded offering of selectable color temperatures and lumen options.

METALUX FLAT PANELS

CGTS | CGT Series FLAT PANEL

- Affordable contractor LED panel with fixed or selectable configurations
- Fits in shallow plenums with room to spare; Thin 2 1/8 - inch height
- 3 Color Field-Selectable in 35/40/5000K and dedicated in 3500K, 4000K, 5000K
- 3 Field-Selectable Lumens: Low, Medium or High settings
- Ideal for office spaces, education, healthcare and retail merchandising



MarketPro Essentials Selectable CCT & Lumens

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|----------------------|------------------|-------------|----------|-------------|----------|--------------|----------------|
| ES 14CGTS-L3C3 | 1'x4' Recessed Panel | 2-T8 | 3500K-5000K | 120-277V | 3,200-5,100 | 21/31/36 | 080083282517 | S-3EJHF2 |
| ES 22CGTS-L3C3 | 2'x2' Recessed Panel | 3-T8 17W, 2-U6T8 | 3500K-5000K | 120-277V | 2,500-4,900 | 21/29/39 | 080083194728 | PL74TQBZR6SL |
| ES 24CGTS-L3C3 | 2'x4' Recessed Panel | 4-T8 32W | 3500K-5000K | 120-277V | 3,700-6,800 | 27/39/51 | 080083194704 | PL0ULJMKXBCH |

MarketPro Essentials Dedicated CCT & Lumens

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|----------------------|------------|-------|----------|--------|-------|--------------|----------------|
| ES 22CGT3540C | 2'x2' Recessed Panel | 3-T8 | 4000K | 120-277V | 3,582 | 32 | 080083880027 | POYGNM7S |
| ES 24CGT4540C | 2'x4' Recessed Panel | 2-T8, 3-T8 | 4000K | 120-277V | 4,432 | 38 | 080083880102 | PLTEVMIJ |

FPS Series FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- 3 Color Field-Selectable in 30/35/4000K
- Selectable switch to set color temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal for office spaces, schools, healthcare facilities and retail merchandising areas



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|----------------------|------------|----------------|----------|-------------------|----------|--------------|----------------|
| 14FPSL1SCT3 | 1'x4' Recessed Panel | 2-T8 | 3000K-4000K | 120-277V | 2,000-4,100 | 18/27/36 | 080083889440 | PYJV3ZJZ |
| 22FPSL2SCT3 | 2'x2' Recessed Panel | 3-T8 | 3000K-4000K | 120-277V | 1,700-3,500 | 15/22/31 | 080083889402 | PB32RP9H |
| 24FPSL2SCT3 | 2'x4' Recessed Panel | 2-T8, 3-T8 | 3000K-4000K | 120-277V | 3,100-6,300 | 27/40/56 | 080083889365 | PZFJCMXS |

Multi-Mount Selectable
FLAT PANEL

- Visually comforting panel mounts directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit
- Versatile mounting allows for surface, wall, recessed, or suspended with kit
- Selectable Color Temperatures in 90 CRI Standard:
2x2/2x4/1x4: 35/40/5000K | 4' x 6": 27/30/35/40/5000K
- Selectable Lumens: Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|---------------------------|----------|----------------|----------|-------------------|----------|--------------|----------------|
| 4MMS-L3C5-UNV | 4'x6", Direct Mount Panel | 2-T8 32W | 2700K-5000K | 120-277V | 1,680-3,000 | 19/25/33 | 080083292028 | Pending |
| 22MMS-L3C3-UNV | 2'x2', Direct Mount Panel | 3-T8 32W | 3500K-5000K | 120-277V | 2,400-4,800 | 21/28/42 | 080083292042 | Pending |
| 24MMS-L3C3-UNV | 2'x4', Direct Mount Panel | 4-T8 32W | 3500K-5000K | 120-277V | 3,500-6,200 | 28/36/48 | 080083292059 | Pending |
| 14MMS-L3C3-UNV | 1'x4', Direct Mount Panel | 2-T8 32W | 3500K-5000K | 120-277V | 2,620-5,286 | 18/25/38 | 080083292035 | Pending |

CGRK Retrofit Kit
FLAT PANEL

- Luminaire panels and mounting rails shipped separately for quick installation
- 3 Color Field-Selectable in 35/40/5000K with three lumen options for various retrofit applications
- Micro-optics for uniform illumination, extruded aluminum frame for performance and aesthetics
- DLC Premium options for maximum energy savings and rebates, including WaveLinx Lite for enhanced savings



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|---------------------|----------------------------------|------------------|----------------|----------|-------------------|----------|--------------|----------------|
| 14CGRK-L3C3-UNV-MP4 | 1'x4' Backlit Panel Retrofit Kit | 2-T8 | 3500K-5000K | 120-277V | 2,055-4,097 | 14/22/29 | 080083312139 | Pending |
| 22CGRK-L3C3-UNV-MP4 | 2'x2' Backlit Panel Retrofit Kit | 3-T8 17W, 2-U6T8 | 3500K-5000K | 120-277V | 2,062-4,085 | 15/22/29 | 080083312146 | Pending |
| 24CGRK-L3C3-UNV-MP4 | 2'x4' Backlit Panel Retrofit Kit | 4-T8 32W | 3500K-5000K | 120-277V | 2,827-5,009 | 20/27/35 | 080083312153 | Pending |

Surround Frame Selectable
ILLUMINATED FRAME

- Architectural 1.5" illuminated modern frame enhances the look of any space
- Versatile mounting in existing T-grid using ceiling tile as the reflector, suspension also available with kit
- 4 Color Field-Selectable in 30/35/40/5000K
- Selectable Lumens - Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



Center of frame is open

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|-----------------------|----------|----------------|----------|-------------------|----------|--------------|----------------|
| 22SFS-L3C4-UNV | 2'x2', Surround Frame | 3-T8 32W | 3000K-5000K | 120-277V | 1,900-4,600 | 15/25/36 | 080083293124 | Pending |
| 24SFS-L3C4-UNV | 2'x4', Surround Frame | 4-T8 32W | 3000K-5000K | 120-277V | 3,000-6,000 | 23/35/47 | 080083293148 | Pending |

Cruze Selectable CZS | Cruze ST Recessed
TROFFER

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; ribbed, frosted acrylic lens
- 3 Color Field-Selectable in 30/35/4000K and dedicated in 3500K, 4000K
- Ideal choice for commercial, institutional and healthcare facilities



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|----------------|------------|----------------|----------|-------------------|-------|--------------|----------------|
| 14CZSCT3-UNV | 1'x4', Troffer | 2-T8 | 3000K-4000K | 120-277V | 3,000-4,400 | 20-30 | 080083268443 | S-5LPE0V |
| 22CZSCT3-UNV | 2'x2', Troffer | 2-T5, 2-T8 | 3000K-4000K | 120-277V | 2,700-4,075 | 21-31 | 080083268467 | S-QDP2J8 |
| 24CZSCT3-UNV | 2'x4', Troffer | 2-T8, 3-T8 | 3000K-4000K | 120-277V | 3,500-6,500 | 24-47 | 080083268481 | S-MW0TCN |

Achieva™ Recessed Selectable
TROFFER

- Ultra slim 1.5" center basket design fits into the shallowest of plenums
- 3 Color Field-Selectable in 30/35/4000K in 80+ CRI
- 3 Selectable lumens in standard or HO options up to 8,150
- Ideal choice for commercial, institutional and healthcare facilities



MarketPro Essentials

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|------------------------------|-----------------------------|--------------|----------------|----------|-------------------|----------|--------------|-----------------|
| ES 14ARS-L3C3-UNV | 1'x4', Troffer | 2-T8 | 3500K-5000K | 120-277V | 2,800-4,600 | 20/26/33 | 080083282241 | S-N7LRJL |
| ES 22ARS-L3C3-UNV | 2'x2', Troffer | 2-T8, 2-T5 | 3500K-5000K | 120-277V | 2,750-4,300 | 20/26/33 | 080083282128 | S-N0X10I |
| ES 22ARS-L3C3-HO-UNV | 2'x2', Troffer, High Output | 3-T5, 3-T8 | 3500K-5000K | 120-277V | 5,000-6,350 | 37/41/45 | 080083282203 | S-Q6A8TB |
| ES 24ARS-L3C3-UNV | 2'x4', Troffer | 2-T8, 3-T8 | 3500K-5000K | 120-277V | 3,400-6,250 | 24/33/46 | 080083282005 | S-EA9S16 |
| ES 24ARS-L3C3-HO-UNV | 2'x4', Troffer, High Output | 3-T8, 2-T5HO | 3500K-5000K | 120-277V | 6,300-8,150 | 46/52/58 | 080083282081 | S-SHLC4F |
| ES 22ARS-L3C3-UNV-MP4 | 2'x2', Troffer (4-Pack) | 2-T5, 2-T8 | 3500K-5000K | 120-277V | 2,750-4,300 | 20/26/33 | 080083282388 | S-N0X10I |
| ES 24ARS-L3C3-UNV-MP2 | 2'x4', Troffer (2-Pack) | 2-T8, 3-T8 | 3500K-5000K | 120-277V | 3,400-6,250 | 24/33/46 | 080083282364 | S-EA9S16 |

Note: DLC Premium items are noted in bold.

SLSTP Series
STRIP LIGHT

- LED strip light with decorative end caps and toolless lens removal
- Suitable for either single or continuous row application
- 3 Color Field-Selectable in 35/40/5000K and dedicated in 4000K
- Field-Selectable lumens 2,400 - 11,200 or dedicated up to 9300
- Impact resistant polycarbonate lens reduces maintenance



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|------------------|----------------|----------------------|-------------------|----------|-------------------|-------|--------------|----------------|
| 2SLSTPSC-UNV | 2' Single Lens | 2-T8 17W | 3500K-5000K | 120/277V | 2,500 | 22 | 080083174409 | S-YBI5XF |
| 4SLSTPSLC-UNV | 4' Single Lens | 2-T8 32W, 1-T5HO 54W | 3500K-5000K | 120/277V | 2,400-6,000 | 18-46 | 080083174416 | S-OICHU8 |
| 8SLSTPSLC-UNV | 8' Single Lens | 4-T8 32W, 2-T12 75W | 3500K-5000K | 120/277V | 4,300-11,200 | 33-85 | 080083174423 | S-7SKGJW |
| 4SLSTP4040DD-UNV | 4' Single Lens | 2-T8 32W, 1-T5HO 54W | 4000K (dedicated) | 120/277V | 5,200 (Dedicated) | 39 | 080083705825 | PXZQGN9C |

Sensor Kits

| Catalog Number | Description | PIR Sensor | UPC |
|----------------|------------------------------------|-----------------------|--------------|
| SLSTP MS00 KIT | SLSTP Field Installable Sensor KIT | 100%/50% / OFF | 080083254200 |
| SLSTP MS25 KIT | SLSTP Field Installable Sensor KIT | 100%/50% / Low (~30%) | 080083254224 |

ST Series
STRIP LIGHT

- Full-length LED strip light ideal for replacing fluorescent strips
- Superior performance with lumens up to 9,300 and 129 lumens per watt
- 3 Color Field-Selectable in 35/40/5000K
- Continuous row mount aligner included to add-on length as needed
- Low voltage 0-10V dimming to 10%



MarketPro Essentials

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|-----------------------|----------------------|----------------|----------|--------|-------|--------------|----------------|
| ES 2ST2L20SC3 | 2' Dual Lens, Dimming | 2-T8 17W | 3500K-5000K | 120-277V | 2,300 | 19 | 080083241569 | S-UQ028D |
| ES 4ST2L40SC3 | 4' Dual Lens, Dimming | 2-T8 32W, 1-T5HO 54W | 3500K-5000K | 120-277V | 4,800 | 41 | 080083241583 | S-TSP41D |
| ES 8ST2L80SC3 | 8' Dual Lens, Dimming | 4-T8 32W, 2-T12 75W | 3500K-5000K | 120-277V | 9,300 | 74 | 080083242207 | S-5J2ZA0 |

WP Series
WRAP

- Compact LED wrap light delivers value and energy savings
- Perfect retrofit solution for replacing single or 2-lamp fluorescent wraparounds
- Low-profile, highly versatile design; Post-painted die-formed channel
- Prismatic lens ensures even, glare-free light distribution



MarketPro Essentials

| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC |
|----------------|-----------------|----------|-------|----------|--------|-------|--------------|
| ES 4WP3040R | 4' Utility Wrap | 2-T8 32W | 4000K | 120-277V | 4010 | 34 | 080083847167 |



Achieva™ Surface Selectable
WRAP

- Ideal for replacing up to four lamp and low-bay linear fluorescents
- 3 Color Field-Selectable in 35/40/5000K, Field-Selectable lumens: 2,250 - 12,500
- Designed for single or continuous row mount
- Suitable for ceiling, wall, or suspension mounting



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|--------------------------------|--------------------|----------------|----------|-------------------|----------|--------------|----------------|
| 2AWS-L3C3-UNV | 2' Narrow Modern Wrap, Dimming | 2-T8 17W | 3500K-5000K | 120-277V | 2,250-3,084 | 18/21/25 | 080083281244 | S-LXMBTS |
| 4AWS-L3C3-UNV | 4' Narrow Modern Wrap, Dimming | 2-T8 32W | 3500K-5000K | 120-277V | 4,095-5,916 | 31/38/46 | 080083281602 | S-QV8V88 |
| 8AWS-L3C3-UNV | 8' Narrow Modern Wrap, Dimming | 2-T8 96W, 4-T8 32W | 3500K-5000K | 120-277V | 7,845-12,019 | 54/71/83 | 080083281800 | S-864B60 |
| 2AWS-L3C3-UNV | 2' Wide Modern Wrap, Dimming | 3-T8 17W | 3500K-5000K | 120-277V | 2,313-3,170 | 18/21/25 | 080083281541 | S-8BS41V |
| 4AWS-L3C3-UNV | 4' Wide Modern Wrap, Dimming | 3-T8 32W | 3500K-5000K | 120-277V | 4,254-6,013 | 31/38/47 | 080083281701 | S-2PPZXM |
| 8AWS-L3C3-UNV | 8' Wide Modern Wrap, Dimming | 3-T8 96W, 6-T8 32W | 3500K-5000K | 120-277V | 8,296-12,554 | 57/74/85 | 080083281909 | S-0R1G6X |

NWS Series
WRAP

- Ideal for replacing two or three lamp fluorescents up to 96W
- 3 Color Field-Selectable in 35/40/5000K
- Field-Selectable lumens: 2,000 - 5,272
- Surface (wall or ceiling) mount via junction box or direct to surface
- UNV 0-10V dimming to 10%



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|----------------------------|----------|----------------|----------|-------------------|----------|--------------|----------------|
| 2NWS3C3-UNV | 2' Wrap, Dimming | 2-T8 17W | 3500K-5000K | 120-277V | 2,009-2,679 | 15/18/21 | 080083257485 | S-PKU0E2 |
| 4NWS3C3-UNV | 4' Wrap, Dimming | 3-T8 32W | 3500K-5000K | 120-277V | 3,300-4,800 | 28/32/39 | 080083257522 | S-YJTA0N |
| 4NWS3C3MS-UNV | 4' Wrap, Dimming, Sensor * | 3-T8 32W | 3500K-5000K | 120-277V | 3,675-5,016 | 28/32/38 | 080083257607 | S-2V0NL5 |

* Includes integrated microwave motion sensor (MS) option.

WNLED Series
WRAP

- Utility commercial LED linear wrap
- Single or continuous row applications
- Frosted lens offers best-in-class uniform illumination
- Minimizes maintenance common with traditional fluorescents



| Catalog Number | Description | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------------------------|----------------|-----------------|-------|----------|--------|-------|--------------|----------------|
| 4WNLED-LD4-40SL-F-UNV-L840-CD1-U | 4' Linear Wrap | 2-T12, 2-T8 32W | 4000K | 120/277V | 4,006 | 30 | 080083756889 | PK3W95DW |





High Bays
p. 39 & 41



Vaportites
p. 40

METALUX

INDUSTRIAL LIGHTING

Metalux Industrial offers a selection of economical and energy-efficient high-bay and vaportite lighting solutions designed for a wide variety of applications.

METALUX HIGH BAYS

UHBS2 High Performance LED HIGH BAY

- Compact, 12" and 14" round die cast aluminum housing
- Field selectable distribution - Narrow, Medium, or Wide
- Up to 36,000 selectable lumens with 5 Color Selectable CCT - 30/35/40/50/6500K
- Sensor ready port for quick plug and play install
- 120-347V input, 0-10V dimming with 6kV surge protection



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------------|--------------|-----------------------------|----------------|----------|-------------------|----------|--------------|-----------------|
| UHBS2-1218-MV-L8C5-U | Round, White | 4-T5HO 54W, 400MH | 3000K-6500K | 120-347V | 12,000-18,000 | 79-122W | 080083301836 | S-DVZ2KB |
| UHBS2-2436-MV-L8C5-U | Round, White | 8-T5HO 54W, 10T8 32W, 750MH | 3000K-6500K | 120-347V | 24,000-36,000 | 153-239W | 080083301843 | S-JVQHNC |

Note: DLC Premium items are noted in bold.

UHBS Sensor Remote

| Catalog Number | Description | UPC |
|----------------|----------------------------|--------------|
| UHBS-SENSOR-PK | UHBS Sensor Remote Control | 080083260249 |

SPHB Selectable Series HIGH BAY

- 2 Compact, lightweight designs for easy install
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor Ready port for quick plug and play install
- Great for industrial, manufacturing, gymnasium, and warehouse



Selectable lumen output and color temperature with an easy to access toggle switch.



MarketPro Essentials

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|---|-------------|------------------------|----------------|----------|-------------------|-------------|--------------|----------------|
| ES SPHB-1224SE-M-UNV-L84050-CD-SP1-U | Med. Distr | 6-T5HO, 8-T8, 400W MH | 4000K-5000K | 120-277V | 12,000-24,000 | 82/123/166 | 080083289264 | Pending |
| ES SPHB-2436SE-M-UNV-L84050-CD-SP1-U | Med. Distr | 8-T5HO, 10-T8, 750W MH | 4000K-5000K | 120-277V | 24,000-36,000 | 162/209/251 | 080083289288 | Pending |

Accessories

| Catalog Number | Description | UPC |
|-----------------|-------------------------------|--------------|
| Y-TOGGLE-10-2PK | Mounting Toggle and 10' Cable | 080083259557 |
| Y-TOGGLE-30-2PK | Mounting Toggle and 30' Cable | 080083259571 |

EZBY Series HIGH BAY

- Up to 30,000 selectable lumens and 3000/4000/5000K selectable CCT
- Sensor ready port for quick plug and play install
- Mounting ring included for rapid install
- 120-347V input, 0-10V dimming



MarketPro Essentials

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|--------------------|--------------|---------------------------------|----------------|----------|-------------------|----------|--------------|----------------|
| EZBY-1830C3-MV-BLK | Round, Black | 8 T8 or 6 T5HO lamps or 750W MH | 3000K-5000K | 120-347V | 18,000-30,000 | 122-185W | 080083305889 | Pending |

LHBS Series
HIGH BAY

- Economical industrial high bay/low bay LED linear luminaire
- CCT (4000/5000K) and lumen select for greater flexibility
- Standard diffused lens provides added protection and glare control
- Energy-efficient, one-for-one replacement of linear fluorescent and HID fixtures
- Perfect for industrial, manufacturing, gymnasium and warehouse applications



| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|------------------------|-------------------|------------------------|----------------|----------|-------------------|---------|--------------|-----------------|
| LHBS-1218-UNV-L84050-U | Lensed HB Select* | 4-T8, 3-T5HO, 175W MH | 4000K-5000K | 120-277V | 13,000-18,000 | 85-124 | 080083274741 | S-J1KSFT |
| LHBS-1824-UNV-L84050-U | Lensed HB Select* | 6-T5HO, 8-T8, 400W MH | 4000K-5000K | 120-277V | 18,800-24,000 | 119-156 | 080083275625 | S-24YMLJ |
| LHBS-2436-UNV-L84050-U | Lensed HB Select* | 8-T5HO, 10-T8, 750W MH | 4000K-5000K | 120-277V | 24,388-36,000 | 155-246 | 080083276141 | S-EUK8B9 |

* Medium Distribution. Note: DLC Premium items are noted in bold.

APVT Series
VAPORTITE

- Durable polycarbonate housing with integral metal gear tray
- 4ft and 8ft sizes with CCT and lumen select capability
- UL Wet location, IP65 and operating temp -20C to 40C
- Stainless steel latches, single conduit hub, and mounting included



MarketPro Essentials

| Catalog Number | Description | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|-------------------------|----------------------|----------------------|----------------|----------|-------------------|-------|--------------|----------------|
| ES 4APVTLD-SL3C3 | 4' Selectable Output | 3-T8 32W, 2-T5HO 54W | 3500K-5000K | 120-277V | 3,000-6,000 | 21-46 | 080083264216 | S-M39BJL |
| ES 8APVTLD-SL3C3 | 8' Selectable Output | 4-T8 32W, 3-T5HO 54W | 3500K-5000K | 120-277V | 8,500-12,000 | 59-94 | 080083266333 | S-3EH2VC |



| | | MarketPro Essentials | | MarketPro Essentials | |
|----------------------------|----------------------|----------------------|------|----------------------|-------|
| | | EZBY | LHBS | SPHB | UHBS2 |
| APPLICABILITY ¹ | Big Box Retail | ★ | ★ | ★★ | ★★ |
| | Sports / Recreation | ★ | ★★ | ★★ | ★★ |
| | Warehouses | ★★★ | ★★★ | ★★★ | ★★★ |
| | Manufacturing | ★★ | ★★ | ★★★ | ★★★ |
| | Cold Storage | ★★ | ★ | ★★★ | ★★ |
| | Complex Environments | ★ | | ★ | ★★ |

| FEATURES / PERFORMANCE | Lumen Range | 18,000 - 28,000 | 12,000 - 36,000 | 12,000 - 36,000 | 12,000-36,000 |
|------------------------|----------------------|---------------------|---|------------------------------------|-----------------------------------|
| | Selectable Lumens | 18,000-30,000 | 12,000-18,000 or 18,000-24,000 or 24,000-36,000 | 12,000 - 24,000 or 24,000 - 36,000 | 12,000-18,000 or 24,000-36,000 |
| | Efficacy (Max) | 150 lm/W | 160 lm/W | 158 lm/W | 169 lm/W |
| | CRI | 80 | 80 | 80 | 80 |
| | Distribution | Wide (120-deg) only | M | M | Selectable Optics (N, M, or W) |
| | Sizes | 13.4 | 13' x 2' & 4' | 12" x 18" or 12" x 36" | 12"/14.1" |
| | Housing ² | Diecast | CRS | CRS | Diecast |
| | Lensing | Acrylic | Acrylic | Polycarbonate | Polycarbonate |
| | Uplight | None | None | None | None |
| | Life (@ 60K hrs) | L91 | L84 | L86 | L91 |
| | Ambient Range | -20C to 50C | -20C to 50C | -40C to 45C | -40C to 50C |
| | Emergency | Remote | None | Optional | Remote |
| | Ratings | IP65 | Damp | Damp, IP5X | IP65, NEMA, 4X, NSF, Wet Location |
| | DLC | Premium | Premium | Premium | Premium |

| INTEGRATED CONTROLS | Basic Occupancy | | ✓ | |
|---------------------|----------------------------------|-------------|---|---|
| | Stand Alone Daylight / Occupancy | Sensor Port | ✓ | ✓ |
| | WaveLinx | | ✓ | ✓ |
| | | | | |


Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
2. CRS=Cold-rolled Steel, Extruded= Extruded Aluminum, Diecast=Diecast Aluminum.

Compatible Controls

Warehouse facilities must meet requirements of ASHRAE Standard 90.1 2010. The High Bay Fixture Mount Sensor solves this by meeting and exceeding those requirements.

OEF High Bay Fixture Mount Sensor

See page 49



WaveLinx LITE
p. 44-45



WaveLinx CAT
p. 46-47



GREENGATE
Switches
p. 48



GREENGATE
Sensors
p. 48-49

CONNECTED LIGHTING & CONTROLS

Meet lighting codes, save energy and reduce installation costs for all of your lighting and control needs with WaveLinx, Greengate switches, dimmers and sensors.



A smarter way to save energy is here!


Save 60%
in lighting
energy
with WaveLinx

WaveLinx is a Cooper Lighting Solutions smart digital lighting system. The WaveLinx solution provides standalone/grouped occupancy sensing, manual/personal dimming control, daylighting and more.

One system for all your spaces

Wireless for Single Spaces

Eliminate low voltage wiring with wireless connected luminaires and control devices for single rooms, areas, or parking spaces.




[CLICK HERE](#) to learn more about our WaveLinx LITE solution.

See [page 44](#) for our WaveLinx LITE products.

Wired for Single & Connected Spaces

Simply connect the WaveLinx CAT5 based lighting control devices to control the lights in a single room or area.



[CLICK HERE](#) to learn more about our WaveLinx CAT solution.

See [page 46](#) for our WaveLinx CAT products.



OCS Dual Technology Ceiling Sensor

This digital ceiling sensor provides improved performance vs other dual tech sensors by utilizing both passive infrared (PIR) and acoustic detection reducing the risk of interference or false triggers.

Standalone Functionality

Utilize in standalone spaces that require simple on/off control through excellent out of box performance.

Digital Programing


Customize the sensor performance utilizing the industry leading WaveLinx LITE mobile app to adjust sensor parameters.

Networkable Funtionality


Combine with other WaveLinx LITE products to form a mesh network of control devices for use as part of a group of devices.

OPTIONAL Customize settings with the WaveLinx LITE mobile app

Standalone -Line Voltage




Standalone -Low Voltage



WaveLinx LITE mobile app

Wireless



OCS Ceiling Mount Dual Tech WaveLinx LITE SENSOR

- Combines Passive Infrared (PIR) and acoustic technologies, improving accuracy of detection
- Standalone sensors capable of providing on/off functionality with out of the box installation
- Change settings without the need for ladders through the WaveLinx LITE Mobile App
- Pair with WaveLinx LITE devices to create a mesh network for use with other WaveLinx LITE control products



| Catalog Number | Description | Finish | Voltage | Detection Type | Coverage | UPC | DLC Product ID |
|----------------|--|--------|------------|------------------|-------------|--------------|----------------|
| OCS-L-D-06 | Dual Tech, Low Voltage Ceiling Sensor 600 sq ft. | White | 24VDC | Dual Technology* | 600 sq ft. | 080083298143 | NM8502RF5T1 |
| OCS-L-D-12 | Dual Tech, Low Voltage Ceiling Sensor 1200 sq ft. | White | 24VDC | Dual Technology* | 1200 sq ft. | 080083298150 | NM8502RF5T1 |
| OCS-L-D-20 | Dual Tech, Low Voltage Ceiling Sensor 2000 sq ft. | White | 24VDC | Dual Technology* | 2000 sq ft. | 080083300624 | NM8502RF5T1 |
| OCS-L-D-06-MV | Dual Tech, Line Voltage Ceiling Sensor 600 sq ft. | White | 120/277VAC | Dual Technology* | 600 sq ft. | 080083298181 | NM8502RF5T1 |
| OCS-L-D-12-MV | Dual Tech, Line Voltage Ceiling Sensor 1200 sq ft. | White | 120/277VAC | Dual Technology* | 1200 sq ft. | 080083298198 | NM8502RF5T1 |
| OCS-L-D-20-MV | Dual Tech, Line Voltage Ceiling Sensor 2000 sq ft. | White | 120/277VAC | Dual Technology* | 2000 sq ft. | 080083300648 | NM8502RF5T1 |

*PIR and Acoustics.



WTK Wireless Tilemount WaveLinx LITE SENSOR KIT

- Enable 0-10V luminaires to be controlled by the WaveLinx LITE system
- 120-277VAC with 3 amp relay and 0-10V continuous dimming
- Mounting heights of 8 to 15ft (2.4 to 4.5m)
- Provides PIR and photocell capabilities
- Installs into 1/2-3/4" (12-19mm) ceilings or octagonal junction boxes



| Catalog Number | Description | Finish | Voltage | UPC | DLC Product ID |
|----------------|------------------------------------|--------|----------|--------------|----------------|
| WTK | WaveLinx LITE Tilemount Sensor Kit | White | 120-277V | 080083293261 | NM8502RF5T1 |

RSP WaveLinx LITE SWITCHPACK

- 20A rated relay
- 0-10v dimming control
- Plenum-rated design with easy junction box mounting
- Universal voltage input (120, 277 and 347 VAC)
- Suitable for plug load control



| Catalog Number | Description | Voltage | UPC | DLC Product ID |
|----------------|---------------------------------|----------|--------------|----------------|
| RSP-L-010-347 | WaveLinx LITE Wireless, Dimming | 120/347V | 080083288229 | NM8502RF5T1 |

WWL Wallstation WaveLinx LITE WALLSTATION

- Multi-scene selection, and zone programmable
- Suitable for standard single or multi-gang NEMA wall box
- Line voltage (120-277VAC) and battery powered options
- Configurable through software - no physical adjustments



Line Voltage Wallstation

| Catalog Number | Description | Finish | Voltage | UPC | DLC Product ID |
|----------------|-----------------------------------|--------|----------|--------------|----------------|
| WWL3-W | Wallstation, 3 Button | White | 120-277V | 080083283170 | NM8502RF5T1 |
| WWL3-RL-W | Wallstation, 3 Button Raise/Lower | White | 120-277V | 080083282449 | NM8502RF5T1 |
| WWL5-RL-W | Wallstation, 5 Button Raise/Lower | White | 120-277V | 080083283149 | NM8502RF5T1 |

Wireless Battery Powered Wallstation

| Catalog Number | Description | Finish | Voltage | UPC | DLC Product ID |
|----------------|-----------------------------------|--------|---------|--------------|----------------|
| WWBL3-W | Wallstation, 3 Button, | White | N/A | 080083256600 | NM8502RF5T1 |
| WWBL3-RL-W | Wallstation, 3 Button Raise/Lower | White | N/A | 080083256198 | NM8502RF5T1 |
| WWBL5-RL-W | Wallstation, 5 Button Raise/Lower | White | N/A | 080083256181 | NM8502RF5T1 |

WST WaveLinx CAT WALLSTATION

- On/Off, Raise/Lower and Scene Presets with 1, 3, 5 and 6 button option
- Draws power from CAT communications bus to simplify wiring
- Clean and elegant with a custom button engraving option to enhance occupant experience
- Button actions are configurable through the WaveLinx app
- Remotely upgradeable firmware



| Catalog Number | Description | Finish | UPC | DLC Product ID |
|----------------|--|--------|--------------|----------------|
| WST-C-1 | WaveLinx CAT Wallstation, 1 Button | White | 080083272433 | N-X04521 |
| WST-C-3 | WaveLinx CAT Wallstation, 3 Button | White | 080083272457 | N-X04521 |
| WST-C-3D | WaveLinx CAT Wallstation, 3 Button Dimming | White | 080083272471 | N-X04521 |
| WST-C-5D | WaveLinx CAT Wallstation, 5 Button Dimming | White | 080083272495 | N-X04521 |

BPI Bluetooth Programing WaveLinx CAT INTERFACE MODULE

- Bluetooth radio used to pair to a mobile device with WaveLinx CAT app
- Two RJ45 ports used to connect to CAT communication bus and other CAT devices
- Draws power from CAT communications bus to simplify wiring
- Remotely upgradeable firmware
- Encrypted authentication to a WaveLinx Mobile App for secure programming



| Catalog Number | Description | UPC | DLC Product ID |
|----------------|-------------------------------------|--------------|----------------|
| BPI-C-L | L BPI-C Bluetooth Program Interface | 080083272693 | N-X04521 |

| Accessories | | |
|----------------|-------------------------------------|--------------|
| Catalog Number | Description | UPC |
| ACC-C-TP-6PK | ACC-C Canbus Termination Plug - 6PK | 080083285846 |

Occupancy Ceiling Sensor WaveLinx CAT INTERFACE MODULE

- Passive Infrared sending technology to detect motion up to 12 ft mounting height
- 600 and 1200 sqft coverage with high sensitivity core
- Built-in photocell to dim or turn off the lights based on daylight coming into the space
- LED Status Indicator for simple troubleshooting
- Draws power from CAT communications bus to simplify wiring



| Catalog Number | Description | Finish | Detection Type | Coverage | UPC | DLC Product ID |
|----------------|---|--------|----------------|--------------|--------------|----------------|
| OCS-C-P12 | OCS-C Occupancy Ceiling Sensor, 1200 sq ft. | White | PIR | 1,200 sq ft. | 080083272297 | N-X04521 |
| OCS-C-P06 | OCS-C Occupancy Ceiling Sensor, 600 sq ft. | White | PIRh | 600 sq ft. | 080083272419 | N-X04521 |

| Accessories | | |
|----------------|-------------------------------------|--------------|
| Catalog Number | Description | UPC |
| ACC-C-TP-6PK | ACC-C Canbus Termination Plug - 6PK | 080083285846 |

RSP Dimming WaveLinx CAT SWITCHPACK

- Control (on/off/dim) commercial fixtures using 20A Relay and an 0-10V dimming output
- Plenum-rated design with easy junction box mounting
- 120/277 VAC Input Voltage
- 24VDC output power to power the CAT bus and CAT devices
- Two RJ45 connectors to daisy chain with other CAT devices using standard CAT5 cabling



| Catalog Number | Description | Voltage | UPC | DLC Product ID |
|----------------|--|----------|--------------|----------------|
| RSP-C-010-Z1 | WaveLinx CAT RSP-C Relay Switchpack - Zone 1 | 120-277V | 080083272518 | N-X04521 |

| Accessories | | |
|----------------|-------------------------------------|--------------|
| Catalog Number | Description | UPC |
| ACC-C-TP-6PK | ACC-C Canbus Termination Plug - 6PK | 080083285846 |

ESP Emergency Dimming WaveLinx CAT SWITCHPACK

- UL924 control device for emergency fixtures
- Control (on/off/dim) commercial fixtures using 20A Relay and an 0-10V dimming output
- Plenum-rated design with easy junction box mounting
- 120/277 VAC Input Voltage
- 24VDC output power to power the CAT bus and CAT devices
- Two RJ45 connectors to daisy chain with other CAT devices using standard CAT5 cabling



| Catalog Number | Description | Voltage | UPC | DLC Product ID |
|----------------|---|----------|--------------|----------------|
| ESP-C-010-Z1 | ESP-C Emergency Relay Switchpack - Zone 1 | 120-277V | 080083272570 | N-X04521 |

| Accessories | | |
|----------------|-------------------------------------|--------------|
| Catalog Number | Description | UPC |
| ACC-C-TP-6PK | ACC-C Canbus Termination Plug - 6PK | 080083285846 |

WBSD 0-10V Decorator Dimmer
WALL SWITCH

- Provides a full-range of linear-slide dimming control of 0-10V compatible light sources
- Allows user to return to previous light level when turning lights ON
- Can be used in single-pole (1 location) and 3-way (multi-location) applications
- Neutral wire is not required for installation of device
- Ideal for light commercial applications; Compatible with decorator style devices and wallplates



| Catalog Number | Description | Finish | Voltage | UPC |
|----------------|------------------------|----------------------------|-----------|--------------|
| WBSD-010DEC-C1 | 0-10V Decorator Dimmer | White, Ivory, Almond | 120V/277V | 080083735266 |
| WBSD-010DEC-C2 | 0-10V Decorator Dimmer | White, Ivory, Light Almond | 120V/277V | 080083735273 |

WBSD 0-10V Preset Slide Dimmer
WALL SWITCH

- Full-travel slide control; LED ready
- Class 1 or Class 2 wiring capabilities
- Can be used in single-pole (1 location) and 3-way (multi-location) applications
- Works with the SP20-RD4 or directly controls the load
- White face assembled on device, Ivory and Light Almond color change kits included



| Catalog Number | Description | Finish | Voltage | UPC |
|----------------|---------------------------|--------|-------------|--------------|
| WBSD-010M-C1 | 0-10V Preset Slide Dimmer | White | 120/277 VAC | 080083834983 |

OSW 0-10V Dimmer with Dual Tech Sensor
SENSOR

- 3-in-1 solution that combines functionality of a switchpack, a sensor and a 0-10V dimmer
- Saves labor costs, reduces installation time and meets energy codes and standards
- Ultrasonic occupancy (US) and passive infrared (PIR) sensing; Daylight harvesting
- Can be used in single-pole (1 location) as well as 3-way (multi-location) applications
- Compatible with Cooper Lighting Solutions' decorator style devices and wallplates



| Catalog Number | Description | Finish | Voltage | Watts | Detection Type | Coverage | UPC |
|----------------|--------------------------|--------|----------|-------------|--------------------|--------------|--------------|
| OSW-D-010-W | 0-10V Dimmer, OCC Sensor | White | 120/277V | 960W/2,200W | PIR and Ultrasonic | 1,000 sq ft. | 080083816071 |

ONW Switch with Sensor
SENSOR

- Passive Infrared (PIR) single level occupancy sensing switch for motion sensing control
- Also a conventional wall switch; Designed for energy savings and convenience
- Detects motion from a heat-emitting source (such as a person entering a room) within its field-of-view and automatically switches lights ON
- Neutral and non-neutral wiring options for installation; Ideal for retrofit applications



| Catalog Number | Description | Finish | Voltage | Watts | Detection Type | Coverage | UPC |
|-------------------|---|--------|----------|---------------|--------------------|--------------|--------------|
| ONW-P-1001-MV-W | PIR Wall Sensor | White | 120/277V | 1,200W/2,200W | PIR | 1,000 sq ft. | 080083523863 |
| ONW-D-1001-MV-W | Dual Tech Wall Sensor | White | 120/277V | 1,200W/2,200W | PIR and Ultrasonic | 1,000 sq ft. | 080083524709 |
| ONW-D-1001-MV-N-W | Dual Tech Wall Sensor, Neutral Required | White | 120/277V | 1,200W/2,200W | PIR and Ultrasonic | 1,000 sq ft. | 080083524594 |

OEF High Bay Fixture Mount Sensor
SENSOR

- Fixture-mount high bay/low bay occupancy sensor with integrated photocell
- Provides 0-10V control and 1-100% continuous dimming
- 2 interchangeable 360° high bay and low bay lenses; specifically designed for LED fixture control
- Easy to program; Quicksnap feature for easy installation
- Suitable for use in standard and cold storage applications



| Catalog Number | Description | Finish | Voltage | Watts | Detection Type | Coverage | UPC |
|----------------|----------------------|--------|----------|-------|----------------|--------------|--------------|
| OEF-P-010V-MV | Fixture Mount Sensor | White | 120/277V | 1200 | PIR | 1,500 sq ft. | 080083758104 |

OCS Ceiling Mount Dual Tech WaveLinx
SENSOR

- Standalone sensors capable of providing on/off functionality with out-of-the-box installation
- Line and low voltage options with in 600 sq. ft., 1200 sq. ft. and 2000 sq. ft. coverage options
- Provides improved performance vs other dual tech sensors by utilizing both passive infrared (PIR) and acoustic detection, reducing risk of interference or false triggers.
- For additional functionalities, including in app easy programming and networking features, see the WaveLinx LITE section.



| Catalog Number | Description | Finish | Voltage | Detection Type | Coverage | UPC | DLC Product ID |
|----------------|--|--------|------------|------------------|-------------|--------------|----------------|
| OCS-L-D-06 | Dual Tech, Low Voltage Ceiling Sensor 600 sq ft. | White | 24VDC | Dual Technology* | 600 sq ft. | 080083298143 | NM8502RF5T1 |
| OCS-L-D-12 | Dual Tech, Low Voltage Ceiling Sensor 1200 sq ft. | White | 24VDC | Dual Technology* | 1200 sq ft. | 080083298150 | NM8502RF5T1 |
| OCS-L-D-20 | Dual Tech, Low Voltage Ceiling Sensor 2000 sq ft. | White | 24VDC | Dual Technology* | 2000 sq ft. | 080083300624 | NM8502RF5T1 |
| OCS-L-D-06-MV | Dual Tech, Line Voltage Ceiling Sensor 600 sq ft. | White | 120/277VAC | Dual Technology* | 600 sq ft. | 080083298181 | NM8502RF5T1 |
| OCS-L-D-12-MV | Dual Tech, Line Voltage Ceiling Sensor 1200 sq ft. | White | 120/277VAC | Dual Technology* | 1200 sq ft. | 080083298198 | NM8502RF5T1 |
| OCS-L-D-20-MV | Dual Tech, Line Voltage Ceiling Sensor 2000 sq ft. | White | 120/277VAC | Dual Technology* | 2000 sq ft. | 080083300648 | NM8502RF5T1 |

*PIR and Acoustics.



Sure-Lites
p. 51-53



All-Pro
p. 54-55



AtLite
p. 56-57

SURE-LITES ALL-PRO | ATLITE EXIT & EMERGENCY

Sure-Lites, All-Pro and AtLite offer reliable and code compliant solutions for all your exit and emergency needs.

SURE-LITES EMERGENCY LIGHTING

Innovative Design. Dependable. ▶▶▶

Sure-Lites offers emergency lighting fixtures, exit signs and battery packs, including Chicago and New York code compliant solutions ideal for commercial and industrial applications.

SELHP EMERGENCY LIGHTING

- Provides emergency lighting for a minimum of 90 minutes
- Up to 100 feet of emergency egress coverage
- Long life LED's with LiFePO4 battery, 3 watts remote capacity
- Labor savings self-diagnostics option
- Wall and ceiling mount



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|----------------------------------|--------|--------------------|----------|----------|-------|--------------|
| SELHP100R3 | 2 Head, LiFePO4 | White | 2 - 24W Hal. Heads | 100 ft. | 120~277V | 2.6W | 080083276721 |
| SELHP100R3SD | 2 Head, LiFePO4, Self Diagnostic | White | 2 - 24W Hal. Heads | 100 ft. | 120~277V | 4.6W | 080083276707 |

SEL Series EMERGENCY LIGHTING

- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™ and injection-molded, high-impact thermoplastic housing
- Long life LED's, no maintenance nickel cadmium battery
- EZ hang feature reduces installation time and cost
- Labor savings self-diagnostics available in SD models



Updated Optics
with higher egress
coverage.



| Catalog Number | Description | Finish | Replaces | Fixture Spacing | Voltage | Watts | UPC |
|----------------|---------------------------------|--------|-------------------|-----------------|----------|------------|--------------|
| SEL17 | 2 Head, NiCad | White | 2-5.4W INC. Heads | 17 ft. | 120-277V | 0.78W | 080083722143 |
| SEL25 | 2 Head, NiCad | White | 2-9W INC. Heads | 35 ft. | 120-277V | 0.6W/0.64W | 080083736669 |
| SEL25SD | 2 Head, NiCad, Self-Diagnostics | White | 2-9W INC. Heads | 25 ft. | 120-277V | 0.67 | 080083723027 |
| SEL50 | 2 Head, NiCad | White | 2-12W INC. Heads | 59 ft. | 120-277V | 1W/1.02W | 080083733347 |
| SEL50SD | 2 Head, NiCad, Self-Diagnostics | White | 2-12W INC. Heads | 50 ft. | 120-277V | 1.19 | 080083733361 |

SELW Outdoor Series EMERGENCY LIGHTING

- Code compliant, wet location for outdoor use; Standard 0°C to 40°C temperature rating
- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™; 25 feet of emergency egress coverage
- Injection-molded, high-impact thermoplastic
- Long life LED's; No maintenance nickel cadmium battery



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--------------------------|--------|----------------|----------|----------|-------|--------------|
| SELW25BZ | 2 Rotatable Heads, NiCad | Bronze | 2-9W INC Heads | 25 ft. | 120-277V | 1.4 | 080083764037 |

LPX Series
EXIT SIGNAGE

- Injection-molded polycarbonate housing
- Field-Selectable for single or double face; red or green illumination
- Snap-out or snap-in chevron directional indicators
- EZ key external battery disconnect



| Catalog Number | Description | Finish | Voltage | Watts | UPC |
|----------------|-----------------------------------|--------|----------|-------------|--------------|
| LPX7 | Self Powered, Univ. Red and Green | White | 120/277V | 0.98W/1.03W | 080083532773 |

LPXC SERIES
EMERGENCY LIGHTING

- Injection-molded polycarbonate housing
- Field-Selectable for single or double face; red or green illumination
- Snap-out or snap-in chevron directional indicators
- EZ key external battery disconnect



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|---|--------|----------------|----------|----------|----------------|--------------|
| LPXC25 | 2 Heads, Univ. Red and Green, Remote Cap. | White | 2-9W INC Heads | 25 ft. | 120/277V | 3.2 W at 277 V | 080083770922 |

CHX Series
EXIT SIGNAGE

- Chicago code compliant exits are ideal for general purpose applications
- Extensive range of field-installed accessories and choice of faces
- Lens installs from side of fixture for convenient maintenance
- Steel canopy allows ceiling or end mounting
- Rear universal pattern knockouts for direct mounting to jbox



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--------------------------------|--------|------------------|----------|----------|-------|--------------|
| CHX61 | AC Powered, Steel | White | 2-12 W INC Heads | N/A | 120/277V | 3 | 080083574629 |
| CHX70 | Self Powered, Steel | White | 2-12 W INC Heads | N/A | 120/277V | 3 | 080083576753 |
| CHX71 | Self Powered, Steel | White | 2-12 W INC Heads | N/A | 120/277V | 3 | 080083567614 |
| CHXC71 | Self Powered Combo Unit, Steel | White | 2-12 W INC Heads | 60 ft. | 120/277V | 3.6 | 080083771271 |

SCX Complete Edge Lit Exit
EXIT SIGNAGE

- Universal mount: surface ceiling, wall, end mount, recessed ceiling and wall mount
- Pivot housing for sloped ceiling or back wall mount
- Single-sided clear and double-sided mirror lens panels included
- Bright red or green LED sources
- Battery backup models provide 90 minutes of emergency run time



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|------------------------------|----------------|----------|----------|----------|-------|--------------|
| SCX70R | Self Powered, Red Aluminum | Satin Aluminum | N/A | N/A | 120/277V | 3.14 | 080083277704 |
| SCX70G | Self Powered, Green Aluminum | Satin Aluminum | N/A | N/A | 120/277V | 2.94 | 080083277728 |

XR Series
EMERGENCY LIGHTING

- Emergency light with minimum of 90 minutes runtime; Chicago and New York City compliant
- 20-gauge sheet metal housing; heads are fully adjustable and 300 lumens each
- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™; No maintenance nickel cadmium battery
- External battery disconnect and EZ Hang feature reduces installation time and cost



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--------------|--------|-----------------|----------|----------|-------|--------------|
| XR6C-LED | Steel, NiCad | White | 2-12W INC Heads | 60 ft. | 120-277V | 1.7 | 080083753215 |

EBP Series
EMERGENCY BATTERY PACKS

- LED Battery Pack automatically switches to emergency mode when AC power fails
- Maintains illumination of a fixture for a minimum of 90 minutes
- UL 924 classified for field retrofit installation
- Labor savings self-diagnostics available in SD models



Fluorescent Emergency Battery Pack

MarketPro Essentials

| Catalog Number | Description | Voltage | Watts | UPC |
|----------------|----------------------------|----------|-------|--------------|
| ES EBPLED7W | LED Emergency Battery Pack | 120/277V | 7 | 080083289844 |
| ES EBPLED14W | LED Emergency Battery Pack | 120/277V | 14 | 080083289868 |

Compact Design. Value Focused. ▶▶▶

All-Pro offers a broad line of compact and affordable LED emergency lighting fixtures designed for commercial and industrial applications.

APEL Series
EMERGENCY LIGHTING

- Emergency light with a minimum of 90 minutes of run time
- No maintenance nickel cadmium battery
- Fully adjustable LED heads maximizes design flexibility
- Components are injection-molded, high impact thermoplastic
- Universal jbox mounting pattern and snap-fit housing



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|---------------|--------|------------------|----------|----------|---------------|--------------|
| APEL | 2 Head, NiCad | White | 2-5.4W INC Heads | 17 ft. | 120/277V | 0.47W at 277V | 080083566501 |

*Egress coverage with APELH2 + remote head units.

AP2SQLED30 Series
EMERGENCY LIGHTING

- Next generation square head emergency light
- Provides up to 30 feet of egress coverage for 90 minutes
- Each adjustable square head outputs 80 lumens
- No maintenance nickel cadmium battery
- Universal jbox mounting pattern and snap-fit polycarbonate housing



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--------------------------|--------|----------------|----------|----------|-----------|--------------|
| AP2SQLED30 | 2 Head, NiCad 30' Egress | White | 2-9W INC Heads | 30 ft. | 120/277V | 2 at 277V | 080083264285 |

APWR Series
EMERGENCY LIGHTING

- Emergency lighting remote heads unit; Allows for 17 feet of emergency egress coverage
- Adjustable heads adjust 80° from vertical with 358° rotation
- Wet location listed and can be used indoors or outdoors
- Injection-molded thermoplastic material
- Universal mounting plate; Flame-resistant and impact-resistant



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|---------------------------------|--------|-------------------|----------|---------|-------|--------------|
| APWR2 | Remote Emergency Lamps, 2 Heads | White | 2-5.4W INC. Heads | 17 ft. | 3.6V | 1W | 080083608584 |

APX Series
EXIT SIGNAGE

- Economical LED exit sign for general purpose applications
- Durable, injection-molded, thermoplastic material resists discoloration
- Field-Selectable red or green LEDs and faces
- Universal configurations (single and double-face); Universal mounting (ceiling, wall and end)




MarketPro Essentials

| Catalog Number | Description | Finish | Voltage | Watts | UPC |
|----------------|------------------------------|--------|----------|---------------|--------------|
| ES APX7RG | Self Powered, Unv. Red/Green | White | 120/277V | 1.05W at 277V | 080083281107 |

APC Combo Series
EMERGENCY LIGHTING

- Economical LED combo unit; Exit and LED emergency lighting heads
- Durable, injection-molded, thermoplastic material resists discoloration
- Field-Selectable red or green LEDs and faces
- Universal configurations (single and double-face); Universal mounting (ceiling, wall and end)
- Low-voltage disconnect, Line-Latched; Brownout circuit



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|-------------------------|--------|-------------------|----------|----------|---------------|--------------|
| ES APC7RG | 2 Heads, Unv. Red/Green | White | 2-5.4W Inc. Heads | 17 ft. | 120/277V | 4.04W at 277V | 080083280827 |

| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--|--------|--------------------|----------|----------|---------------|--------------|
| APCH7RG | 2 Heads, Unv. Red/Green, Remote Cap. | White | 4-5.4W Inc. Heads | 34 ft.* | 120/277V | 3.79W at 277V | 080083280865 |
| APC7RGSQ30 | 2 Sq. Heads, Unv. Red/Green | White | 2 - 10W Inc. Heads | 30 ft | 120/277V | 1.2W at 277V | 080083296859 |
| APCH7RGSQ30 | 2 Sq. Heads, Unv. Red/Green, Remote Cap. | White | 2 - 10W Inc. Heads | 47 ft* | 120/277V | 1.2W at 277V | 080083296873 |

*Egress coverage with APCH + Remote head units.

Durable Design. Built-to-Last. ▶▶▶

AtLite offers durable and dependable emergency lighting and exits for commercial and industrial applications that are also approved for the New York City market.

RCS Combo Series
EXIT SIGNAGE

- New York City compliant LED combo exit sign
- Heavy-duty, 20-gauge steel housing and face plate provides durability
- Energy-efficient, long-life LED's; illuminated by field-replaceable LED strip
- Single or double face with maximum of three heads for ultimate flexibility



| Catalog Number | Description | Finish | Replaces | Voltage | Watts | UPC |
|----------------|-----------------------------------|--------|------------------|----------|-------|--------------|
| RCS182LED | Steel Combo, 1 Face, 2 Heads | White | 2 12W INC. Heads | 120/277V | N/A | 080083574322 |
| RCS183LED | Steel Combo, 1 Face, 3 Heads | White | 3 12W INC. Heads | 120/277V | N/A | 080083574308 |
| RCS282LED | Steel Combo, Double Face, 2 Heads | White | 2 12W INC. Heads | 120/277V | N/A | 080083574315 |
| RCS283LED | Steel Combo, Double Face, 3 Heads | White | 3 12W INC. Heads | 120/277V | N/A | 080083574292 |

Rival RXS Series
EXIT SIGNAGE

- New York City compliant steel LED exit sign
- Heavy-duty, 20-gauge steel housing with canopy
- Energy-efficient, long-life LED's; illuminated by field-replaceable LED strip
- Universal configurations (single- and double-face); Universal mounting (ceiling, wall and end)



| Catalog Number | Description | Finish | Voltage | Watts | UPC |
|----------------|--------------------------------------|--------|----------|-------|--------------|
| RXSN8RU | Steel Exit, Self Powered, Univ. Face | White | 120/277V | 5 | 080083634576 |

REL Series
EMERGENCY LIGHTING

- New York City compliant steel LED emergency light
- Heavy-duty, 20-gauge steel housing and face plate for maximum durability
- Long-lasting, high-efficiency LED heads; maintenance-free nickel cadmium battery
- Brownout protection; low-voltage disconnect



| Catalog Number | Description | Finish | Replaces | Voltage | Watts | UPC |
|----------------|---|--------|-----------------|----------|-------|--------------|
| 10REL36-LED42 | Steel Emergency Light, 2 Heads, 2 Remotes | White | 2 9W INC. Heads | 120/277V | 5 | 080083574353 |
| 10REL72-LED83 | Steel Emergency Light, 3 Heads, 5 Remotes | White | 2 9W INC. Heads | 120/277V | 5 | 080083574339 |

ATLEMINI Series
EMERGENCY LIGHTING


- New York City compliant LED emergency light with 90 minutes of run time
- Jbox and conduit knockouts for easy installation; wall or ceiling mount applications
- Long-lasting, energy-efficient LED heads; maintenance-free nickel cadmium battery
- Available with two or three 80 lumen rotatable heads



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|--------------------------------|--------|-----------|----------|----------|--------|--------------|
| ATLEMINI-2H | Steel Emergency Light, 2 Heads | White | 5.4 W INC | 18 ft. | 120-277V | 0.78 W | 080083836079 |

AUX Edge-Lit Exit Series
EXIT SIGNAGE

- Edge-Lit Exit allows seamless presence in architecturally significant surroundings
- Labor savings self-diagnostics, New York City compliant
- Universal mounting; Universal Lens (clear, mirror, white and single- and double-sided)
- Ordering and installation simplified as all housing and lens options are included



| Catalog Number | Description | Finish | Voltage | Watts | UPC |
|----------------|--|--------|----------|--------------|--------------|
| AUXSSD | Unv. Self Powered, Self-Diag. | Silver | 120/277V | 1.1 at 277 V | 080083703296 |
| AUXSSD6 | Unv. Edge Lit, Self Powered | Silver | 120/277V | 0.9/1.1W | 080083718115 |
| AUXSSD-SP PACK | Unv. Self Powered, Self-Diag., Single Pack | Silver | 120/277V | 1.1 at 277 V | 080083848669 |

ACX Complete Edge Lit Exit
EXIT SIGNAGE

- Surface ceiling, wall, end mount, recessed ceiling and wall mount
- Pivot housing for sloped ceiling or back wall mount
- NYC Compliant 8" letter single-sided clear and double-sided mirror lens panels included
- Battery backup models provide 90 minutes of emergency run time
- NFPA approved field installable directional chevrons included



| Catalog Number | Description | Finish | Replaces | Coverage | Voltage | Watts | UPC |
|----------------|------------------------|----------------|----------|----------|-----------|-------|--------------|
| ACXN0R | Self Powered, Aluminum | Satin Aluminum | N/A | N/A | 120/277 V | 3.14 | 080083277742 |



Wall Mounts
p. 59-60, 62-63



Floodlight
p. 60, 64-65



Ceiling Mount
p. 61



Area/Site
p. 61, 63-64

LUMARK & LUMARK AP OUTDOOR LED LUMINAIRES

Lumark brands offer a wide selection of high-quality product solutions that provide market-leading ease of installation, superior area safety, and maximum energy savings in commercial and industrial spaces.

LUMARK AP WALL MOUNTS

Lumark AP provides high-value outdoor lighting products that are in stock and supported with decades of experience and expertise in the industry.



ASWP Adjustable Slim Wall Pack Luminaire WALL MOUNT

- Adjustable slim wall pack available in small and medium sizes
- 3-color selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages range from 2,100-10,200 lumens
- Internal toggle switches to easily adjust luminaire CCT and lumens
- Integrated button type photocontrol for dusk-to-dawn operation



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|---------------------|----------------------|--------|----------|----------------|----------|-------------------|--------|--------------|-----------------|
| ES ASWPLED1S | Small LED Wall Pack | Bronze | 155W HID | 3000K-5000K | 120-347V | 2,000-4,000 | 15-30W | 080083265169 | S-YWC5DG |
| ES ASWPLED2S | Medium LED Wall Pack | Bronze | 250W HID | 3000K-5000K | 120-347V | 5,000-10,000 | 40-75W | 080083265183 | S-9DIVKW |

Note: DLC Premium items are noted in bold.

WP Wall Pack Series (WPS, WPM & WPL) WALL MOUNT

- Selectable configurations available across 3 housing sizes
- 5-color selectable CCT: 3000, 3500, 4000, 5000, 6500K / 80CRI
- Lumen packages ranging from 4,300 - 21,000 lumens
- Heat and impact resistant borosilicate glass lens
- Die-cast aluminum housing with hinged, removable die-cast aluminum door



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|---------------------|----------------------|--------|----------|----------------|----------|-------------------|----------|--------------|----------------|
| ES WPSLED15S | Small LED Wall Pack | Bronze | 150W HID | 3000K-6500K | 120-347V | 4,300-8,100 | 30-60W | 080083304561 | Pending |
| ES WPMLED26S | Medium LED Wall Pack | Bronze | 350W HID | 3000K-6500K | 120-347V | 10,000-14,900 | 70-100W | 080083304585 | CCCISJ |
| ES WPLLED38S | Large LED Wall Pack | Bronze | 500W HID | 3000K-6500K | 120-347V | 17,300-21,000 | 120-150W | 080083304707 | Pending |

CYL Cylinder
WALL MOUNT

- Selectable light distribution (Uplight/ Downlight/Combined Up + Down)
- 3-color selectable CCT: 3000K, 4000K, 5000K / 80 CRI
- Up to 3,600 lumens
- Universal 120-347V input voltage
- Rugged die-cast aluminum housing and PC lens and glass cover



| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|--------------------|----------------------|--------|----------|----------------|----------|-------------------|--------|--------------|----------------|
| CYL-2D-30W-347V-PC | Wall Mount Luminaire | Black | 70W HID | 3000K-5000K | 120-347V | 1,600-3,600 | 15-30W | 080083304943 | Pending |

LSF Selectable Flood Luminaire
FLOODLIGHT

- Available in 3 housing sizes and multiple lumen packages
- 3-color selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages ranging from 1,700-20,000 lumens
- Knuckle, slipfitter, trunnion and yoke mounting types
- Integrated button type photocontrol for dusk-to-dawn operation



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|------------------------|--------------------------------|--------|----------|----------------|----------|-------------------|---------|--------------|-----------------|
| ES LSF25-KN-PC | Knuckle Mount, Photocontrol | Bronze | 155W HID | 3000K-5000K | 120-347V | 1,700-4,000 | 11-25W | 080083267705 | S-W43YTM |
| ES LSF65-KN-PC | Knuckle Mount, Photocontrol | Bronze | 375W HID | 3000K-5000K | 120-347V | 5,000-10,000 | 25-65W | 080083267729 | S-5HK1XN |
| ES LSF120-SF-PC | Slipfitter Mount, Photocontrol | Bronze | 450W HID | 3000K-5000K | 120-347V | 9,000-20,000 | 50-120W | 080083267743 | S-M4YHAF |
| ES LSF25-YK-PC | Yoke Mount, Photocontrol | Bronze | 155W HID | 3000K-5000K | 120-347V | 1,700-4,000 | 11-25W | 080083267767 | S-W43YTM |
| ES LSF65-YK-PC | Yoke Mount, Photocontrol | Bronze | 375W HID | 3000K-5000K | 120-347V | 5,000-10,000 | 25-65W | 080083267781 | S-5HK1XN |
| ES LSF120-TR-PC | Trunnion Mount, Photocontrol | Bronze | 450W HID | 3000K-5000K | 120-347V | 9,000-20,000 | 50-120W | 080083267804 | S-M4YHAF |

Note: DLC Premium items are noted in bold.

CLCS Canopy Luminaire
CEILING MOUNT

- LED canopy available with fixed output or selectable configurations
- 3-color selectable CCT: 3000K, 4000K, 5000K
- High-performance, energy-efficient illumination
- Energy and maintenance savings up to 86% versus HID solutions
- Ideal for new or existing spaces including bank, retail, drive-thru, covered sidewalks and hospital entryways



Selectable CCT & Lumens

| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|------------------|--------|----------|----------------|----------|-------------------|--------|--------------|--------------------|
| CLCS17S | Small LED Canopy | Bronze | 175W HID | 3000K-5000K | 120-277V | 5,323-7,939 | 39-56 | 080083160006 | P5MUAJIY, P5S4B75K |
| CLCS17S-PC | Small LED Canopy | Bronze | 175W HID | 3000K-5000K | 120-277V | 5,323-7,939 | 39-56 | 080083159727 | P5MUAJIY |
| CLCS40S | Large LED Canopy | Bronze | 400W HID | 3000K-5000K | 120-277V | 12,614-17,427 | 91-123 | 080083160020 | PUT80LSK, PPEWK64B |

Dedicated CCT & Lumens

| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|------------------|--------|----------|-------|----------|--------|-------|--------------|----------------|
| CLCS15 | Small LED Canopy | Bronze | 150W HID | 4000K | 120-277V | 5,671 | 39 | 080083161003 | PAVO9EAO |
| CLCS17 | Small LED Canopy | Bronze | 175W HID | 4000K | 120-277V | 7,956 | 56 | 080083161041 | P3KXJQWI |

LAS Luminaire
AREA/SITE

- Automatic dusk-to-dawn area lighting with included twistlock photocontrol
- 10-position, Field-Selectable lumens across 2 die-cast aluminum housing sizes
- Energy and maintenance savings up to 79% versus HID solutions up to 79%
- Pole mount arm or adjustable slipfitter mounting arm included
- Ideal for parking lots, walkways, building areas and other outdoor areas



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------------|--------------------------------------|--------|------------|-------|----------|-------------------|--------|--------------|-----------------|
| ES LAS45S-T3 | T3 Distr., Adjustable Slipfitter Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083155804 | P1T4HG08 |
| ES LAS45P-T3 | T3 Distr., Pole Mount Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083248360 | P1T4HG08 |
| ES LAS45S-T4 | T4 Distr., Adjustable Slipfitter Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083155828 | PJZT2423 |
| ES LAS45P-T4 | T4 Distr., Pole Mount Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083248384 | PJZT2423 |
| ES LAS45S-T5 | T5 Distr., Adjustable Slipfitter Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083155842 | PW39PQB3 |
| ES LAS45P-T5 | T5 Distr., Pole Mount Arm | Bronze | 450W HID | 4000K | 120-277V | 4,900-20,000 | 30-153 | 080083248704 | PW39PQB3 |
| ES LAS100S-T3 | T3 Distr., Adjustable Slipfitter Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083155866 | PP8AW4F5 |
| ES LAS100P-T3 | T3 Distr., Pole Mount Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083248780 | PP8AW4F5 |
| ES LAS100S-T4 | T4 Distr., Adjustable Slipfitter Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083155880 | POCHU9AS |
| ES LAS100P-T4 | T4 Distr., Pole Mount Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083248803 | POCHU9AS |
| ES LAS100S-T5 | T5 Distr., Adjustable Slipfitter Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083155903 | PMUFIF4F |
| ES LAS100P-T5 | T5 Distr., Pole Mount Arm | Bronze | 1,000W HID | 4000K | 120-277V | 8,200-34,000 | 48-251 | 080083248827 | PMUFIF4F |

Note: DLC Premium items are noted in bold.

LUMARK WALL MOUNTS

Lumark combines value-engineered, specification-grade lighting features with market-leading retrofit installation solutions, to enable contractors to get on and off the job quickly and deliver superior illumination coverage.



AXC Axcent Luminaire WALL MOUNT

- Full cutoff and refractive LED lens models available in small or large
- Hook-N-Lock mechanism for quick, easy installation
- Die-cast aluminum construction with energy-efficient illumination
- Gasketed housing and sealed optical compartment making impervious to contaminants
- Ideal for pathway illumination and floodlighting applications




| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|-----------------------|---------------|----------|-------|----------|--------|-------|--------------|---------------------------|
| AXCS1A | Small Full Cutoff | Carbon Bronze | 70W HID | 4000K | 120-277V | 1,806 | 14 | 080083887965 | S-3SJYCL |
| AXCS2A | Small Full Cutoff | Carbon Bronze | 100W HID | 4000K | 120-277V | 2,561 | 21 | 080083887989 | S-0Y08BE |
| AXCS3A | Small Full Cutoff | Carbon Bronze | 150W HID | 4000K | 120-277V | 3,537 | 27 | 080083888009 | S-H7120V |
| AXCS4A | Small Full Cutoff | Carbon Bronze | 250W HID | 4000K | 120-277V | 5,520 | 44 | 080083888023 | PI16J9U0 |
| AXCS4ARL | Small Refractive Lens | Carbon Bronze | 250W HID | 4000K | 120-277V | 5,858 | 44 | 080083888030 | PPXSGJ9K, PCFKRFBV |
| AXCS5A | Small Full Cutoff | Carbon Bronze | 320W HID | 4000K | 120-277V | 6,300 | 52 | 080083888047 | PCPDYSZM |
| AXCL6A | Large Full Cutoff | Carbon Bronze | 320W HID | 4000K | 120-277V | 7,594 | 56 | 080083811564 | PLXS8Y3B |
| AXCL6ARL | Large Refractive Lens | Carbon Bronze | 320W HID | 4000K | 120-277V | 7,809 | 56 | 080083811649 | PZXNXUOI |
| AXCL8A | Large Full Cutoff | Carbon Bronze | 400W HID | 4000K | 120-277V | 9,696 | 72 | 080083811588 | PG4TJNY3 |
| AXCL8ARL | Large Refractive Lens | Carbon Bronze | 400W HID | 4000K | 120-277V | 9,970 | 72 | 080083811663 | PBA84MB6 |
| AXCL10A | Large Full Cutoff | Carbon Bronze | 400W HID | 4000K | 120-277V | 13,283 | 102 | 080083811601 | P5X06GE7 |
| AXCL12A | Large Full Cutoff | Carbon Bronze | 450W HID | 4000K | 120-277V | 16,823 | 123 | 080083811625 | PD1N4D39 |

Note: DLC Premium items are noted in bold.

AXC Back Box Accessory

| Catalog Number | Description | Finish | UPC |
|----------------|----------------------------|---------------|--------------|
| BB/AXC | Back Box | Carbon Bronze | 080083160709 |
| BB/AXC-PC | Back Box with Photocontrol | Carbon Bronze | 080083160723 |

| Features |
|---|
| Lumen Select pack allows installer to reduce the light output to 75 or 50% |
| Integrated photocontrol provides maximum energy savings while leveraging |
| Four 1/2" NPT conduit entry points for surface mounted conduit |
| Single die-cast aluminum back box to simultaneously accommodate Axcent small and large housings |



LUMARK WALL MOUNTS | AREA/SITE

XTOR Crosstour Luminaire WALL MOUNT

- Architectural style with super bright, energy-efficient LEDs
- Low-profile, rugged die-cast aluminum construction and stainless steel hardware
- Universal back box with sealed and gasketed optical compartment
- Wall, surface, post, bollard, low-level, inverted, floodlight mounting
- Ideal for multi-use facilities, pathway illumination and building entrances



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|----------------|-------------------------------------|---------------|----------|-------|----------|--------|-------|--------------|----------------|
| XTOR1B | Small Full Cutoff | Carbon Bronze | 70W HID | 5000K | 120-277V | 1,418 | 12 | 080083777969 | PRVAZAZR |
| XTOR2B | Small Full Cutoff | Carbon Bronze | 100W HID | 5000K | 120-277V | 2,135 | 18 | 080083778225 | PGP4FYV3 |
| XTOR3B | Small Full Cutoff | Carbon Bronze | 150W HID | 5000K | 120-277V | 2,751 | 26 | 080083778041 | PWFZHYJH |
| XTOR4B | Medium Full Cutoff | Carbon Bronze | 250W HID | 5000K | 120-277V | 4,269 | 38 | 080083778003 | PUJ1NXGY |
| XTOR6B | Large Full Cutoff | Carbon Bronze | 320W HID | 5000K | 120-277V | 6,129 | 58 | 080083774807 | S-X7BH39 |
| XTOR6B-PC1 | Large Full Cutoff with Photocontrol | Carbon Bronze | 320W HID | 5000K | 120-277V | 6,129 | 58 | 080083774845 | S-X7BH39 |
| XTOR6BRL | Large Refractive Lens | Carbon Bronze | 320W HID | 5000K | 120-277V | 6,225 | 58 | 080083774821 | N/A |
| XTOR8B | Large Full Cutoff | Carbon Bronze | 400W HID | 5000K | 120-277V | 8,502 | 81 | 080083774814 | P5557CRH |
| XTOR8B-PC1 | Large Full Cutoff with Photocontrol | Carbon Bronze | 400W HID | 5000K | 120-277V | 8,502 | 81 | 080083774869 | P5557CRH |
| XTOR8BRL | Large Refractive Lens | Carbon Bronze | 400W HID | 5000K | 120-277V | 8,635 | 81 | 080083774852 | N/A |

CTKR Caretaker Luminaire AREA/SITE

- Rugged die-cast housing for durability in security applications
- Uniform distribution with excellent vertical illumination for maximum light coverage
- Wall/pole-mount bracket and integral slipfitter for versatility in mounting
- Versatile universal mounting plate allows quick and easy installation
- Low-cost, low-maintenance solution for residential street lighting, perimeter area lighting, parking areas, loading platforms, boat docks, access drives or pathways



MarketPro Essentials

| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|-------------------|----------------------------------|--------|----------|-------|----------|--------|-------|--------------|-----------------|
| ES CTKRV1B | Area site with PC, UNV Mount Arm | Raw | 150W HID | 4000K | 120-277V | 4,515 | 29 | 080083865390 | P9G7NN3C |
| ES CTKRV2B | Area site with PC, UNV Mount Arm | Raw | 175W HID | 4000K | 120-277V | 7,110 | 50 | 080083865406 | PRSAJP8E |
| ES CTKRV3B | Area site with PC, UNV Mount Arm | Raw | 250W HID | 4000K | 120-277V | 9,741 | 71 | 080083865413 | P3P0FHML |

Note: DLC Premium items are noted in bold.

Accessories

| Catalog Number | Description | Finish | UPC |
|----------------|-------------------------|--------|--------------|
| SR-CARETAKER | Small Acrylic Refractor | Clear | 080083777969 |

PRV Prevail Luminaire
AREA/SITE

- Provides a new level of performance, versatility and value
- Low-profile, architectural design with a die-cast aluminum housing
- Versatile mount arm includes multiple drill patterns, round and square poles
- Simple retrofit installation; Reduces installation time and provides labor savings
- Ideal for general area lighting such as parking lots, walkways, roadways and building areas



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|-----------------|--------------------------|--------|----------|-------|----------|--------|-------|--------------|-----------------|
| PRVS-C25-UNV-T3 | T3 Distr., STD Arm Mount | Bronze | 250W HID | 4000K | 120-277V | 13,183 | 96 | 080083897308 | S-43K2M0 |
| PRVS-C25-UNV-T4 | T4 Distr., STD Arm Mount | Bronze | 250W HID | 4000K | 120-277V | 13,140 | 96 | 080083897322 | S-CXYVFA |
| PRVS-C40-UNV-T3 | T3 Distr., STD Arm Mount | Bronze | 400W HID | 4000K | 120-277V | 17,144 | 131 | 080083897346 | S-YEWL3K |
| PRVS-C40-UNV-T4 | T4 Distr., STD Arm Mount | Bronze | 400W HID | 4000K | 120-277V | 17,087 | 131 | 080083897360 | S-L5W8VA |
| PRVS-C60-UNV-T3 | T3 Distr., STD Arm Mount | Bronze | 450W HID | 4000K | 120-277V | 20,050 | 153 | 080083897384 | S-NS95Z4 |
| PRVS-C60-UNV-T4 | T4 Distr., STD Arm Mount | Bronze | 450W HID | 4000K | 120-277V | 19,984 | 153 | 080083897421 | S-RAGPH4 |

Note: DLC Premium items are noted in bold.

NFFLD Night Falcon Luminaire
FLOODLIGHT

- Cost-effective LED floodlight available in medium or large sizes
- Precision engineered and high-efficiency optics delivers superior uniformity
- Compact, robust die-cast aluminum housing, driver compartment and door
- 6H x 6V NEMA wide distribution
- Ideal for area lighting for security, building facade and signage



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | DLC Product ID |
|---------------------|--------------------|---------------|------------|-------|----------|--------|-------|--------------|-----------------|
| NFFLD-S-C15-T-UNV | Small, Trunnion | Carbon Bronze | 150W HID | 4000K | 120-277V | 5,797 | 51 | 080083760275 | P07DFEU0 |
| NFFLD-S-C15-KNC-UNV | Small, Knuckle | Carbon Bronze | 150W HID | 4000K | 120-277V | 5,797 | 51 | 080083760268 | P07DFEU0 |
| NFFLD-C25-S | Medium, Slipfitter | Carbon Bronze | 250W HID | 4000K | 120-277V | 10,530 | 85 | 080083801244 | P5JBKNFS |
| NFFLD-C25-T | Medium, Trunnion | Carbon Bronze | 250W HID | 4000K | 120-277V | 10,530 | 85 | 080083801220 | P5JBKNFS |
| NFFLD-C40-S | Medium, Slipfitter | Carbon Bronze | 400W HID | 4000K | 120-277V | 16,932 | 128 | 080083801206 | PCHBI5F8 |
| NFFLD-C40-T | Medium, Trunnion | Carbon Bronze | 400W HID | 4000K | 120-277V | 16,932 | 128 | 080083801183 | PCHBI5F8 |
| NFFLD-L-C100-S | Large, Slipfitter | Carbon Bronze | 1,000W HID | 4000K | 120-277V | 33,941 | 252 | 080083800889 | P53SWTBG |
| NFFLD-L-C100-T | Large, Trunnion | Carbon Bronze | 1,000W HID | 4000K | 120-277V | 33,941 | 252 | 080083800902 | P53SWTBG |

Note: DLC Premium items are noted in bold.

NHR Night Harrier
FLOODLIGHT

- Cutting edge innovated design offering years of maintenance-free service
- 3-color selectable CCT: 3000K, 4000K, 5000K
- Lumen packages ranging from 5,500-43,000 lumens
- Slipfitter and trunnion mounting types
- Ideal for area lighting such as facade, wall washing, building and sign lighting



| Catalog Number | Description | Finish | Replaces | Selectable CCT | Voltage | Selectable Lumens | Watts | UPC | DLC Product ID |
|----------------|-------------------------------------|--------|-----------------|----------------|----------|-------------------|---------|--------------|----------------|
| NHRS50UT | 500W Trunnion Mount | Bronze | 70W to 500W HID | 3000K-5000K | 120-277V | 5,500-22,000 | 40-155W | 080083283903 | Pending |
| NHRS50US | 500W Slipfitter Mount | Bronze | 70W to 500W HID | 3000K-5000K | 120-277V | 5,500-22,000 | 40-155W | 080083283910 | Pending |
| NHRS50HT | 500W Trunnion Mount | Bronze | 70W to 500W HID | 3000K-5000K | 347-480V | 5,500-22,000 | 40-155W | 080083283927 | Pending |
| NHRS50HS | 500W Slipfitter Mount | Bronze | 70W to 500W HID | 3000K-5000K | 347-480V | 5,500-22,000 | 40-155W | 080083283934 | Pending |
| NHRS50UT-BPC | 500W Trunnion Mount, Photocontrol | Bronze | 70W to 500W HID | 3000K-5000K | 120-277V | 5,500-22,000 | 40-155W | 080083283941 | Pending |
| NHRS50US-BPC | 500W Slipfitter Mount, Photocontrol | Bronze | 70W to 500W HID | 3000K-5000K | 120-277V | 5,500-22,000 | 40-155W | 080083283958 | Pending |
| NHRS100UT | 1000W Trunnion Mount | Bronze | 500W-1000W HID | 3000K-5000K | 120-277V | 23,000-43,000 | 40-155W | 080083296965 | Pending |
| NHRS100US | 1000W Slipfitter Mount | Bronze | 500W-1000W HID | 3000K-5000K | 120-277V | 23,000-43,000 | 40-155W | 080083296972 | Pending |
| NHRS100HT | 1000W Trunnion Mount | Bronze | 500W-1000W HID | 3000K-5000K | 347-480V | 23,000-43,000 | 40-155W | 080083296989 | Pending |
| NHRS100HS | 1000W Slipfitter Mount | Bronze | 500W-1000W HID | 3000K-5000K | 347-480V | 23,000-43,000 | 40-155W | 080083296996 | Pending |



TGS Series – Twin Head
SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Selectable Lumens | Watts | UPC |
|----------------|-------------------------|--------|----------|-------|---------|-------------------|-------|--------------|
| TGS2S402FRRB | Twin Head Round | Bronze | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913053 |
| TGS2S402FRRW | Twin Head Round | White | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913374 |
| TGS2S402DRRB | Twin Head Round, D2D | Bronze | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913435 |
| TGS2S402DRRW | Twin Head Round, D2D | White | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913459 |
| TGS2S402MRRB | Twin Head Round, Motion | Bronze | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913510 |
| TGS2S402MRRW | Twin Head Round, Motion | White | 180W INC | 4000K | 120V | 1,500-2,500 | 22 | 080083913534 |

TGS Series – Triple Head
SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Selectable Lumens | Watts | UPC |
|----------------|------------------------|--------|----------|-------|---------|-------------------|-------|--------------|
| TGS3S403FRRW | Triple Head Round | White | 270W INC | 4000K | 120V | 2,000-3,000 | 27 | 080083913619 |
| TGS3S403DRRB | Triple Head Round, D2D | Bronze | 270W INC | 4000K | 120V | 2,000-3,000 | 27 | 080083913671 |
| TGS3S403DRRW | Triple Head Round, D2D | White | 270W INC | 4000K | 120V | 2,000-3,000 | 27 | 080083913695 |

TGS Series – Single Head High Output
SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Selectable Lumens | Watts | UPC |
|----------------|--|--------|-------------------|-------|----------|-------------------|-------|--------------|
| TGS5S401DSCB | Single Head High Output Square, D2D | Bronze | 175W Metal halide | 4000K | 120-277V | 2,700-5,800 | 50 | 080083256013 |
| TGS5S401MSCW | Single Head High Output Square, Motion | White | 175W Metal halide | 4000K | 120-277V | 2,700-5,800 | 50 | 080083260065 |

VT Series
VAPOR PROOF

- LED or incandescent options available
- Durable die-cast aluminum housing and cage provides protection against vandalism
- Vapor tight IP65 rating protects against dust and moisture
- Versatile mounting options – Wall, Ceiling and Post
- Frosted glass lens provides smooth and even light distribution



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC |
|----------------|-----------------------------------|--------|----------|-------|----------|--------|-------|--------------|
| VT100G | 100W Incandescent Vapor Tight | Raw | N/A | 2700K | 120V | 1,600 | 100 | 080083757879 |
| VT0840L | 800 Lumen, 4000K, LED Vapor Tight | Raw | 60W INC | 4000K | 120-277V | 800 | 9 | 044427550113 |

ESF Series
SECURITY FLOODLIGHT


- Sleek wrap-around lens design – enhanced aesthetics and low glare
- Two lumen packages available; 1400 and 2400 lumens in 2 color finishes
- Switch activated, Dusk-to-Dawn, and motion activated models available
- 50,000 hour lifespan, Wet Location rated and non-corrosive polycarbonate housing



| Catalog Number | Description | Finish | Replaces | CCT | Voltage | Lumens | Watts | UPC | Energy Star ID |
|----------------|---|--------|----------|-------|---------|--------|-------|--------------|----------------|
| ESF1A4FB | Twin Head Floodlight (1,400 Lumens) | Bronze | 90W INC | 4000K | 120V | 1,400 | 15 | 080083146000 | N/A |
| ESF1A4FW | Twin Head Floodlight (1,400 Lumens) | White | 90W INC | 4000K | 120V | 1,400 | 15 | 080083146024 | N/A |
| ESF1A4DB | Twin Head Floodlight (1,400 Lumens) | Bronze | 90W INC | 4000K | 120V | 1,400 | 15 | 080083146048 | N/A |
| ESF1A4MB | Twin Head Floodlight, Motion (1,400 Lumens) | Bronze | 90W INC | 4000K | 120V | 1,400 | 15 | 080083146086 | N/A |
| ESF1A4MW | Twin Head Floodlight, Motion (1,400 Lumens) | White | 90W INC | 4000K | 120V | 1,400 | 15 | 080083146109 | N/A |
| ESF2A4FB | Twin Head Floodlight (2,300 Lumens) | Bronze | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146123 | N/A |
| ESF2A4FW | Twin Head Floodlight (2,300 Lumens) | White | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146147 | N/A |
| ESF2A4DB | Twin Head Floodlight (2,300 Lumens) | Bronze | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146161 | N/A |
| ESF2A4DW | Twin Head Floodlight, D2D, (2,300 Lumens) | White | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146185 | N/A |
| ESF2A4MB | Twin Head Floodlight, Motion (2,300 Lumens) | Bronze | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146208 | N/A |
| ESF2A4MW | Twin Head Floodlight, Motion (2,300 Lumens) | White | 180W INC | 4000K | 120V | 2,300 | 24 | 080083146222 | N/A |

Maximize Savings with Utility Rebates

Cooper Lighting Solutions Exclusive Utility Rebate Incentive Finder



For details visit:
cooperlighting.com/global/resources/incentive-finder

Look for the DLC, ENERGY STAR and T20 icons that identifies qualified products.

By using our Online Incentive Finder, you can search by state and zip code to find local rebates that save money and add value for your customers. For your convenience, we've identified and included the ENERGY STAR® and DLC® product ID numbers within the MarketPro catalog.



DLC Product ID
S-YB15XF

DLC Premium items are denoted in bold



ENERGY STAR ID
2341271



T20 icon located under the product description

Cooper Lighting Solutions has the largest portfolio of **ENERGY STAR®**-certified recessed downlights and **DesignLights® Consortium (DLC)** - qualified commercial luminaires, meeting high-quality, energy-efficient standards. See below for more information about the compliance codes and standards which identify products that qualify for utility rebates.



This non-profit organization drives the adoption of energy, efficiency and high-performing commercial lighting and controls products. Our products represent the broadest portfolio available.

To find which Cooper Lighting Solutions products are listed, visit www.designlights.org/QPL.



ENERGY STAR® is the trusted, government-backed symbol for energy efficiency helping us save money and protect the environment through energy-efficient products and practices. Visit www.energystar.gov for more information.



Title 20 is a set of energy efficiency regulations established by the California

Energy Commission governing various products and appliances. Products with this logo meet the energy efficiency standards set by the California Energy Commission.

For more information on Title 20, visit www.energy.ca.gov.

DREAM. EXPERIMENT. PLAN.

A more powerful way to design.



Light ARchitect™

See your space in a new light with augmented reality

We've taken the guesswork out of lighting design with Light ARchitect, an augmented reality mobile app that lets you instantly visualize light fixtures in your space.

- Browse state-of-the-art light LED fixtures and choose the ones you want to see in your space
- Adjust the fixture's finish, lumen output, mounting height, color temperature and more
- Virtually turn lights on to get the full effect
- Take screenshots to share and email to clients or colleagues



Light ARchitect is free and available for iOS and Android devices

Download **Light ARchitect**



To learn how Light ARchitect has changed our customers' way of working, visit cooperlighting.com/lightarchitect

Literature, product photography, videos, case studies, logos & more!

Visit Cooperlighting.com and click on the Resources tab. The Resource Center is a central location of supportive product selection tools, inspirational images and downloadable digital resources.

|  |  |  |  |  |
|---|---|--|--|---|
| Product Resources | Inspiration | Tools | Programs | Education |
| <ul style="list-style-type: none">• Brochures & Guides• Spec sheets• Installation sheets and guides | <ul style="list-style-type: none">• Application Photography• Product Photography & Videos• Case studies• Logos | <ul style="list-style-type: none">• Energy Incentive Finder• Photometric IES• Revit Models• Calculators & Audit Tools | <ul style="list-style-type: none">• MarketPro• Quick Spec• Overstock | <ul style="list-style-type: none">• Instructor-led Classes• Free online courses• Continuing education |

Learn. Grow. Visualize.
Explore our one-stop-shop for Cooper Lighting Solutions digital tools.

Explore Our Video Library!

Visit Cooper Lighting Solutions' YouTube page to explore our ever-expanding product video library! Everything you need to know about our innovative product offering can be found here. Get the facts on newly introduced solutions, discover product benefits and watch videos on how to install them. Explore our curated playlists to easily find informative videos by industry-leading brand, market and product category.

youtube.com/cooperlightingsolutions



PRISM PORTAL
Our Central Hub for Distributor Business.

Cooper Lighting Solutions PRISM Portal is a digital hub for authorized partners to self-serve reliable product data, place orders, and manage orders. It offers hassle-free access to price and availability, spec sheets, order tracking, invoices, and more!

- Advanced Product Search at Your Fingertips
- Real-Time Pricing & Availability
- Seamless Online Order Entry
- Comprehensive Order Status Tracking

[CLICK HERE](#) to register for PRISM Portal



Explore the PRISM Portal for Streamlined Business Solutions.

Lighting & Controls

STOCK PRODUCT GUIDE

LIGHTING BRANDS

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
LumarkAP
Lumière
McGraw-Edison
Metalux
MWS
NeoRay
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites

CONTROLS BRANDS

Greengate
Fifth Light
Intelligent Lighting Controls

CONNECTED LIGHTING SYSTEMS AND SMART SPACES PLATFORM

WaveLinx
Trellix Infrastructure



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2025 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. CA5250050_update
June 2025

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.