


Good

Better

Best

Click on products to learn more



		FM CCT	WP	WPLD	LW	CWPLD	WNLED	WSNLED	BCLED	SWLED
APPLICABILITY <sup>1</sup>	Education	★★	★★	★★	★★★	★★★	★★★	★★	★★	★★★
	Office	★	★	★★	★★	★★	★★	★★★	★	★★★
	Healthcare	★	★	★	★	★	★	★★	★★	★
	Retail	★★	★	★	★★	★★	★	★★★	★	★
	Industrial		★		★	★	★★			★★
	Residential	★★★	★★★	★★			★	★		
FEATURES / PERFORMANCE	Sizes	9", 11", 15", 19"	2' and 4', 5.1" wide	2', 4'	4', 6.8" wide	4'	2', 4'	2', 4'	2', 4'	4'
	lm/W (Max)	85	114	110	122	115	118	108	120	150
	Lum (Max)	2,400	3,400	4,700	4,617	5,000	5,000	6,500	4,800	8,000
	Life (@60K)	L70/50K	L70/50K	L70/50K	L82	L70/50K	L88	L87	L82	L91
	Lens	Frost / Acrylic	Prismatic Acrylic	Clear, Poly	White Ribbed Acrylic	Frost, Poly	Frost, Acrylic	Frost + Film, Acrylic	Frost, Smooth	(Vandal Resistant) Frost, Acrylic
	Emergency	No	No	No	Integrated	No	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80+	80/90	80+	80+	80+	80+	80+	80+
	Row Mount	N/A	N/A	No	Yes	Yes	Yes	Yes	Yes	No
	Sensor Location	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	Integrated
	DLC	Energy Star	Standard	Standard	DLC, Title 24 Non-Res	Standard	Standard	Standard	None	Standard
INTEGRATED CONTROLS	Basic Occupancy									✓
	Stand Alone Daylight / Occupancy									✓
	WaveLinx Lite									✓
	WaveLinx									✓
	DLVP									

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable